

KTB GP XX3520 AB S4 6MM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

Flange plates

Flange plates in two thicknesses, for easy replacement of pre-assembl

General ordering data

Version	Klippon TB (Terminal Box), flange plate, straight, Height: 340 mm, Width: 167 mm, Depth: 6 mm, Gland plates: top, Bottom, Basic material: Stainless steel 1.4404 (316L), electropolished, silver
Order No.	8000114130
Type	KTB GP XX3520 AB S4 6MM
GTIN (EAN)	4099986804708
Qty.	1 items

KTB GP XX3520 AB S4 6MM

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	6 mm	Depth (inches)	0.2362 inch
Height	340 mm	Height (inches)	13.3858 inch
Width	167 mm	Width (inches)	6.5748 inch
Net weight	2670 g		

Temperatures

Operating temperature

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General information

Material thickness	6 mm	Installation advice	Screw mounting
Surface finish	electropolished	Basic material	Stainless steel 1.4404 (316L)
Integral fixing	Screwed	Protection class (UL)	Type 3, Type 4X, Type 12
Gland plates	top, Bottom	Flange plate	Yes
Areas of use	Explosive risk zone, Process industry		

General information on accessories

Material thickness	6 mm	Solder eyelet hole diameter (D)	7 mm
Surface finish	electropolished	Basic material	Stainless steel 1.4404 (316L)

Housing earth

Flange plate earthing Continuous M10 earth stud in body enclosure

Classifications

ETIM 8.0	EC000211	ETIM 9.0	EC000211
ETIM 10.0	EC000211	ECLASS 14.0	27-14-24-21
ECLASS 15.0	27-14-24-21		