

## KTB GP 50XX15V CD S4 6MM

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

Flange plates

Flange plates in two thicknesses, for easy replacement of pre-assembl

### General ordering data

|            |  |
|------------|--|
| Order No.  | 8000114139                               |
| Type       | <a href="#">KTB GP 50XX15V CD S4 6MM</a> |
| GTIN (EAN) | 4099986804777                            |
| Qty.       | 1 items                                  |

**KTB GP 50XX15V CD S4 6MM**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**
**Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

|            |        |                 |              |
|------------|--------|-----------------|--------------|
| Depth      | 6 mm   | Depth (inches)  | 0.2362 inch  |
| Height     | 456 mm | Height (inches) | 17.9527 inch |
| Width      | 117 mm | Width (inches)  | 4.6063 inch  |
| Net weight | 2544 g |                 |              |

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

**General information**

|                    |   |                       |                               |
|--------------------|---|-----------------------|-------------------------------|
| Material thickness | 6 mm  | Installation advice   | Screw mounting                |
| Surface finish     | electropolished                                       | Basic material        | Stainless steel 1.4404 (316L) |
| Integral fixing    | Screwed   | Protection class (UL) | Type 3, Type 4X, Type 12      |
| Gland plates       | left, right   | Flange plate          | Yes                           |
| Areas of use       | Process industry, Transportation, Explosive risk zone |                       |                               |

**General information on accessories**

|                    |                 |                                 |                               |
|--------------------|-----------------|---------------------------------|-------------------------------|
| Material thickness | 6 mm            | Solder eyelet hole diameter (D) | 7 mm                          |
| Surface finish     | electropolished | Basic material                  | Stainless steel 1.4404 (316L) |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000211    | ETIM 9.0    | EC000211    |
| ETIM 10.0   | EC000211    | ECLASS 14.0 | 27-14-24-21 |
| ECLASS 15.0 | 27-14-24-21 |             |             |