


PVC DC 2I 1O 4MPP RD WM4 11

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



For safe remote shutdown Rooftop photovoltaic systems can require a disconnection device at the point where the cables enter into the building, that is connected to the power grid in the building. This allows the fire brigade to carry out their work in an emergency without being unnecessarily endangered. When the power supply is restored, the PV Next Fireman Switch automatically reconnects the PV strings.

General ordering data

Version	Photovoltaics, Combiner Box, Fireman's switch, PV Next, 1100 V, 4 MPP's, 2 Inputs / 1 Output per MPP, Remote disconnector, WM4C
Order No.	8000115472
Type	PVC DC 2I 1O 4MPP RD WM4 11
GTIN (EAN)	4099986878853
Qty.	1 items

PVC DC 2I 10 4MPP RD WM4 11

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	132 mm	Depth (inches)	5.1968 inch
Height	239 mm	Height (inches)	9.4094 inch
Width	400 mm	Width (inches)	15.748 inch
Net weight	4850 g		

Temperatures

Ambient temperature	-20 °C...50 °C	Humidity	5...95 %, no condensation
---------------------	----------------	----------	---------------------------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	7a, 7cl
REACH SVHC	Lead 7439-92-1
SCIP	bdab5698-6a20-4370-8e28-8810d882d01a

Included in delivery

Included accessories	Article	Mounting foot
	Quantity	4
	Article	Sealing plug
	Quantity	1

Approvals and norms

Approvals	EN 61439-2, IEC 61439-2, OVE-Directive R 11-1:2022-05-01
-----------	----------------------------------------------------------

Guarantee

Time interval	5 years
---------------	---------

Electrical characteristics

Rated DC voltage	1100 V	
Rated short-term current resistance	Rated current	43.75 A
Current per Maximum Power Point, max. 35 A		
Rated DC current per connection	Current per string, max.	35.00 A

Enclosure

Insulating material	Polyester glass-fibre reinforced, Polycarbonate	Type of mounting	Fixing lugs
Impact resistance	IK08 in accordance with IEC 62208, IK10 in accordance with IEC 62262	Enclosure attachment	Via mounting foots

PVC DC 2I 1O 4MPP RD WM4 11

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Protection class	II	Connection type string	Plug WM4C
General data			
Protection degree	IP65	Installation location	Protected outdoor area (Land and Sea)
Inputs			
Amount of maximum power points (MPP)	4		
Number of conduit inlets	3		
DC Input + & -	<p>Wire connection</p> <p>Cable entry</p>	<p>Type of connection</p> <p>Compatible cable crosssection</p> <p>Wire cross-section, min.</p> <p>Wire cross-section, max.</p> <p>Number of cable entries</p>	<p>WM4C plug-in connector</p> <p>EN 50618:2015</p> <p>4 mm²</p> <p>6 mm²</p> <p>8</p>
Fuse type	Neither fuse cartridge nor holder		
Fuses	No		
Max. number of DC inputs	per Maximum Power Point 2 inputs connected in parallel		
Number of string inputs per MPP	≤ 2		
Number of inputs	8		
Outputs			
Max. number of DC outputs	per Maximum Power Point 1 output		
DC Output + & -	<p>Wire connection</p> <p>Cable entry</p>	<p>Type of connection</p> <p>Compatible cable crosssection</p> <p>Wire cross-section, min.</p> <p>Wire cross-section, max.</p>	<p>WM4C plug-in connector</p> <p>TÜV 2 Pfg 1169/08.07</p> <p>4 mm²</p> <p>6 mm²</p>
Remote disconnector			
Automatic reclosing after voltage drop	Yes		
Number of operating cycles	10000		
Control voltage	100 V AC - 250 V AC 50/60Hz		
Remote disconnector auxiliary contact	<p>Cable entry</p> <p>Wire connection</p>	<p>Number of cable entries</p> <p>Type of connection</p> <p>Flexible, max. H05(07) 1.5 mm² V-K</p> <p>w. wire end ferrule, 1.5 mm² DIN 46228 pt 1, max.</p>	<p>1</p> <p>Screw terminal connectors</p> <p>1.5 mm²</p> <p>1.5 mm²</p>
Remote disconnector control contact	<p>Cable entry</p> <p>Wire connection</p>	<p>Number of cable entries</p> <p>Type of connection</p> <p>Flexible, max. H05(07) 1.5 mm² V-K</p> <p>w. wire end ferrule, 1.5 mm² DIN 46228 pt 1, max.</p>	<p>1</p> <p>Screw terminal connectors</p> <p>1.5 mm²</p> <p>1.5 mm²</p>

PVC DC 2I 10 4MPP RD WM4 11

Weidmüller Interface GmbH & Co. KG
 Klingenbergsstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Type of power circuit disconnection	Under voltage tripping		
Turn-off time	1.5 s		
Current consumption of switch	Type of switch	Fireman switch	
	Current consumption, note	The Peak current only arises for a short time when the capacitors of the fireman switch were previously completely discharged.	
	Current consumption peak	300 mA	
	Current consumption continuous	30 mA	
Number of breaking operation cycles at rated current	300		
Switch disconnector execution	Remote disconnector inside enclosure		
Switching disconnector capacity	DC-PV1, IEC 60947-3		

Classifications

ETIM 8.0	EC003857	ETIM 9.0	EC003857
ETIM 10.0	EC003857	ECLASS 14.0	22-57-02-92
ECLASS 15.0	22-57-02-92		

Tender specification sheets

Long specification	Combiner box for inverters with Fireman switch for the connection to 4 MPP tracker. Suitable for remote disconnection of the DC side by the fire department according to VDE-AR-E2100-712. Max. string voltage Uoc: 1100 VDC MPP1: 2 inputs, connection via WM4 C connector, compatible with cable type TÜV 2 Pfg1169/08.07 / EN 50618:2063 1 output, connection via WM4 C connector, compatible with cable type TÜV 2 Pfg1169/08.07 / EN 50618:2063 MPP2 to 4: identical to MPP1 DC fireman switch: Switching off by undervoltage tripping. Switching off by reaching a temperature of ≥ 100 °C in the housing. Automatic reconnection after the control voltage (230 V AC) is applied again. With signal contact. Connection of the fireman switch control line 230 VAC via M16 cable glands (Clamping range 5-10 mm \varnothing) max. conductor cross-section: 1.5 mm 2 . Connection of the signal contact 24 VDC (max. 300 mA) via M16 cable glands (Clamping range 5-10
--------------------	----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

PVC DC 2I 10 4MPP RD WM4 11

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com


Technical data

mmØ) max. conductor cross-section: 1.5 mm².
Protection class: IP65.
All built into a glass fibre reinforced polyester housing. Dimensions HxWxD: 239x400x132 mm. Approval according to low voltage switchgear IEC 61439-1 and EN 61439-2

PVC DC 2I 1O 4MPP RD WM4 11

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

PVC DC 2I 10 4MPP RD WM4 11

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories**PV Sun Covers****General ordering data**

Type	PV SUNCOVER 20/40/13	Version
Order No.	8000143247	Photovoltaics, Sun cover
GTIN (EAN)	4099987111867	
Qty.	1 ST	

Cutting tools

Cutting tools for conductors up to 8 mm, 12 mm, 14 mm and 22 mm outside diameter. The special blade geometry allows pinch-free cutting of copper and aluminium conductors with minimum physical effort. The cutting tools (KT 8 to KT 22) also come with VDE and GS-tested protective insulation up to 1,000 V in accordance with EN/IEC 60900.

General ordering data

Type	KT 14	Version
Order No.	1157820000	Cutting tools, Cutting tool for one-hand operation
GTIN (EAN)	4032248945344	
Qty.	1 ST	

Tools

- For flexible and solid conductors with special insulating materials
- High-quality stripping for industrial applications (complies with aircraft industry requirements)
- Specially shaped blades enable stripping of special types of insulation and conductor configurations
- Stripping length adjustable via end stop
- Very versatile thanks to interchangeable stripping units
- Stripping results reproduced accurately over and over again
- No damage to the conductor
- A long-lasting, reliable tool thanks to its sturdy design
- Integrated cutting function

PVC DC 2I 10 4MPP RD WM4 11

Weidmüller Interface GmbH & Co. KG
 Klingenbergsstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories**General ordering data**


Type	MULTI-STRIPAX PV	Version
Order No.	1190490000	Photovoltaics, Plug-in connector
GTIN (EAN)	4032248973262	
Qty.	1 ST	

Crosshead screwdriver Phillips

Crosshead screwdriver, Phillips, SDK PH DIN 5262, ISO 8764/2-PH, output to ISO 8764-PH, ChromTop tip, SoftFinish grip

General ordering data

Type	SDK PH3	Version
Order No.	9008500000	Screwdriver, Screwdriver
GTIN (EAN)	4032248056491	
Qty.	1 ST	

Slotted screwdriver

Slotted screwdriver with rounded blade SD DIN 5265, ISO 2380/2, output to DIN 5264, ISO 2380/1. ChromTop tip, SoftFinish grip

General ordering data

Type	SDS 0.6X3.5X100	Version
Order No.	9008330000	Screwdriver, Screwdriver
GTIN (EAN)	4032248056286	
Qty.	1 ST	
Type	SDS 1.0X5.5X150	Version
Order No.	9008350000	Screwdriver, Screwdriver
GTIN (EAN)	4032248056316	
Qty.	1 ST	

PVC DC 2I 10 4MPP RD WM4 11

Weidmüller Interface GmbH & Co. KG
 Klingenbergsstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories**PV-Stick field connectors**

Faster is better. This also applies to the cabling of solar systems. Our handy connectors stay firmly in your grip even in frosty temperatures and can be installed very quickly and easily without a crimping tool.

You don't need crimp contacts and crimping tools and you avoid assembly errors. This saves up to 50% installation time – without affecting quality. The new photovoltaic connectors are TÜV-approved and comply with IEC 62852.

Our "SNAP IN" technology enables safe connections with minimal effort – insert, turn: current!

- 1.500 V DC (DE) / 1,500 V DC (EN)
- SNAP IN technology
- Standard-compliant quality in accordance with IEC 62852
- Ergonomic, prize-winning design
- Fastest PV connector currently available
- Reliable latching

General ordering data

Type	PV-STICK+ VPE10	Version
Order No.	1303450000	Photovoltaics, Plug-in connector
GTIN (EAN)	4050118102468	
Qty.	10 ST	
Type	PV-STICK- VPE10	Version
Order No.	1303490000	Photovoltaics, Plug-in connector
GTIN (EAN)	4050118102529	
Qty.	10 ST	

Accessories

The dust protection cap "Dustcap VSSO" protects the Weidmüller and type 4 solar connectors against dust and dirt.

The "SafetyClip" protects the Weidmüller solar connectors against unintentional opening and can only be released using the special multi-tool.


General ordering data

Type	VSSO WM4 C	Version
Order No.	1254870000	Photovoltaics, Flat design
GTIN (EAN)	4050118047479	
Qty.	100 ST	

PVC DC 2I 1O 4MPP RD WM4 11

Weidmüller Interface GmbH & Co. KG
 Klingenbergsstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories**UV-resistant cable ties**

UV-resistant polyamide 6.6 ensures long durability of our special cable ties even with strong UV radiation. Ideal for continuous outdoor use.

General ordering data

Type	CB-UVR 290/4,5 BK	Version
Order No.	2659350000	Cable ties, 4.5 x 290 mm, Polyamide 66, 220 N
GTIN (EAN)	4050118682816	
Qty.	100 ST	

Y-Connector Cables

The Y cable is used for the parallel connection of several strings in a PV system, e.g. for splitting a line in front of an inverter.
 The cables are available in different connection variants.

General ordering data

Type	PVHYW-XXW+XX06W+15	Version
Order No.	2814180000	Photovoltaics, Y-Connector Cable, 1x WM4 C Male, 2x WM4 C
GTIN (EAN)	4064675298861	Female, 6mm ² , 1500 V
Qty.	1 ST	
Type	PVHYW+XXW-XX06W-15	Version
Order No.	2814190000	Photovoltaics, Y-Connector Cable, 1x WM4 C Female, 2x WM4 C
GTIN (EAN)	4064675298878	Male, 6mm ² , 1500 V
Qty.	1 ST	

Emergency stop button

PVC DC 2I 1O 4MPP RD WM4 11

Weidmüller Interface GmbH & Co. KG
 Klingenbergsstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories**General ordering data**

Type	AC SB E 5A 1POL PO 06KV	Version
Order No.	3077660000	Photovoltaics, Emergency stop button, 1 pole, 600 V AC, 5 A,
GTIN (EAN)	4099987081887	Complete enclosure
Qty.	1 ST	

Sealing sets**General ordering data**

Type	BLINDPLUG SET5 7X28MM	Version
Order No.	3077670000	Photovoltaics, Blind plug
GTIN (EAN)	4099987081894	
Qty.	1 ST	
Type	BLINDPLUG SET50 7X28MM	Version
Order No.	3077650000	Photovoltaics, Blind plug, Accessories, Blind plug, 50 pieces
GTIN (EAN)	4099987081870	
Qty.	1 ST	