


MK 6/5/E**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

To feed through power, signal, and data is the classical requirement in electrical engineering and panel building. The insulating material, the connection system and the design of the terminal blocks are the differentiating features. A feed-through terminal block is suitable for joining and/or connecting one or more conductors. They could have one or more connection levels that are on the same potential or insulated against one another.

General ordering data

| | |
|------------|---|
| Version | Single- and multi-pole terminal strip, Screw connection, medium yellow, 6 mm ² , 41 A, 690 V, Number of connections: 10, Number of levels: 1 |
| Order No. | 7906250000 |
| Type | MK 6/5/E |
| GTIN (EAN) | 4008190576455 |
| Qty. | 20 items |

MK 6/5/E

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (UR) E60693

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 22 mm | Depth (inches) | 0.8661 inch |
| Height | 23 mm | Height (inches) | 0.9055 inch |
| Width | 62.5 mm | Width (inches) | 2.4606 inch |
| Net weight | 47.08 g | | |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|---------------|
| Storage temperature | -25 °C...55 °C | Ambient temperature | -5 °C...40 °C |
| Continuous operating temp., min. | -60 °C | Continuous operating temp., max. | 130 °C |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Material data

| | | | |
|---------------------------|-----|--------|---------------|
| Basic material | KrG | Colour | medium yellow |
| UL 94 flammability rating | 5VA | | |

Rating data IECEx/ATEX

| | | | |
|--------------------------------|-------------------|---------------------------------|-------------------|
| Certificate No. (ATEX) | TUEV18ATEX8209U | Certificate No. (IECEX) | IECEXTUR18.0019U |
| Max. voltage (ATEX) | 440 V | Current (ATEX) | 36 A |
| Wire cross section max. (ATEX) | 6 mm ² | Max. voltage (IECEX) | 440 V |
| Current (IECEX) | 36 A | Wire cross section max. (IECEX) | 6 mm ² |
| Marking EN 60079-7 | Ex eb II C Gb | Ex 2014/34/EU label | II 2 G D |

System specifications

| | | | |
|----------------------|------------------------|--------------------------|----|
| Version | For the mounting rails | End cover plate required | No |
| Number of potentials | 1 | Number of levels | 1 |
| Mounting rail | Mounting plate | | |

Additional technical data

| | | | |
|---------------------|-----------------|--------------------------|----|
| Installation advice | Direct mounting | Explosion-tested version | No |
| Type of mounting | Direct mounting | | |

Conductors for clamping (additional connection)

| | |
|--|------------------|
| Connection type, additional connection | Screw connection |
|--|------------------|

MK 6/5/E

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Conductors for clamping (rated connection)

| | | | |
|---|----------------------|---|----------------------|
| Gauge to IEC 60947-1 | A3 | Wire connection cross section AWG, max. | AWG 10 |
| Connection direction | on side | Tightening torque, max. | 1.2 Nm |
| Tightening torque, min. | 1.2 Nm | Stripping length | 9 mm |
| Type of connection 2 | Screw connection | Type of connection | Screw connection |
| Number of connections | 10 | Clamping range, max. | 6 mm ² |
| Clamping range, min. | 0.33 mm ² | Clamping screw | M 4 |
| Blade size | 4.0 x 0.8 mm | Wire connection cross section AWG, min. | AWG 22 |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 4 mm ² | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.33 mm ² |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 4 mm ² | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.33 mm ² |
| Wire connection cross section, finely stranded, max. | 6 mm ² | Wire connection cross section, finely stranded, min. | 0.33 mm ² |
| Connection cross-section, stranded, max. | 6 mm ² | Connection cross-section, stranded, min. | 0.33 mm ² |
| Torque level with DMS electric screwdriver | 4 | Wire connection cross-section, solid core, max. | 6 mm ² |
| Wire connection cross-section, solid core, min. | 0.33 mm ² | | |

Dimensions

| | |
|------------------|-------|
| Fixing dimension | 13 mm |
|------------------|-------|

General

| | | | |
|---------------------|-----------------|---|----------------|
| Number of poles | 5 | Wire connection cross section AWG, max. | AWG 10 |
| Installation advice | Direct mounting | Wire connection cross section AWG, min. | AWG 22 |
| Standards | IEC 60947-7-1 | Mounting rail | Mounting plate |

Rating data

| | | | |
|--|-------------------|---------------------------------|---------------|
| Rated cross-section | 6 mm ² | Rated voltage | 690 V |
| Rated DC voltage | 690 V | Nominal current | 41 A |
| Current at maximum wires | 41 A | Standards | IEC 60947-7-1 |
| Volume resistance according to IEC 60947-7-x | 0.78 mΩ | Rated impulse withstand voltage | 8 kV |
| Power loss in accordance with IEC 60947-7-x | 1.31 W | Pollution severity | 3 |

UL rating data

| | | | |
|---|--------|---|--------|
| Voltage size B (UR) | 300 V | Current size B (UR) | 30 A |
| Conductor size Factory wiring max. (UR) | 10 AWG | Current size C (UR) | 30 A |
| Voltage size C (UR) | 300 V | Conductor size Factory wiring min. (UR) | 22 AWG |
| Certificate No. (UR) | E60693 | Conductor size Field wiring min. (UR) | 22 AWG |
| Conductor size Field wiring max. (UR) | 10 AWG | | |

Classifications

| | | | |
|-----------|----------|-------------|-------------|
| ETIM 8.0 | EC001284 | ETIM 9.0 | EC001284 |
| ETIM 10.0 | EC001284 | ECLASS 14.0 | 27-14-11-06 |

Technical data

ECLASS 15.0

27-14-11-06
