


HDC KIT HE-QT 10.110**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

HDC kits are standardized kits for assembling complete plug-in connectors.

The HDC kits normally consist of a male insert, a female insert, a plug housing, a bulkhead housing and a cable gland. Weidmüller offers a range of standard connector combinations with metric or PG cable entry threads.

With the SNAP IN connection, the conductor connection level is already open, and the stripped conductor can be simply inserted. In the end position, the patented clamping mechanism closes automatically.

General ordering data

Order No.	8000151874
Type	HDC KIT HE-QT 10.110
GTIN (EAN)	4099987263092
Qty.	1 items

HDC KIT HE-QT 10.110

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



Dimensions and weights

Net weight 424.64 g

Temperatures

Limit temperature -40 °C ... 100 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1, Potassium perfluorobutane sulfonate 29420-49-3
SCIP	bfb1c983-6f18-4ba4-8907-38aad6aee076

General data

Surface finish	Powder coating	Protection degree	IP65
Series	HE		

Version

Number of cable glands	1	Size of cable entries	PG 16
Number of cable entry on top	0	Number of cable entry sideways	1
Type of connection	SNAP IN	Design of locking system	Side-locking clamp on lower side
Installation size	4	Sealing	NBR
BG	4		

General data

Number of poles	10	Connection type PE	Screw connection
Installation size	4	Basic material	diecast aluminium
Series	HE	Rated voltage (DIN EN 61984)	500 V
Rated current (DIN EN 61984)	16 A	BG	4

Version

Blade size, slotted (screw connection)	SD 0.6 x 3.5	Wire connection cross section AWG, max.	AWG 16
Stripping length, rated connection	10 mm	Type of connection	SNAP IN
Installation size	4	Wire connection cross section AWG, min.	AWG 20
Wire cross-section, solid, max.	2.5 mm ²	Wire cross-section, solid, min.	1 mm ²
Wire connection cross section, finely stranded, max.	2.5 mm ²	Wire connection cross section, finely stranded, min.	1 mm ²
Conductor cross-section, max.	2.5 mm ²	Conductor cross-section, min.	1 mm ²
Surface finish	Powder coating	Basic material	diecast aluminium
BG	4		

HDC KIT HE-QT 10.110**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Classifications**

ETIM 8.0	EC002943	ETIM 9.0	EC002943
ETIM 10.0	EC002943	ECLASS 14.0	27-44-02-92
ECLASS 15.0	27-44-02-92		

HDC KIT HE-QT 10.110

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories**SPB**

Various accessories are available for our inserts. This includes coding elements for the inserts.

General ordering data

Type	SPB-M 3	Version	
Order No.	1203600000	Heavy-duty connectors, Accessories, Lock bolts	
GTIN (EAN)	4008190120047		
Qty.	100 ST		