
Data sheet

# CB 780/9 NC

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



CB cable ties for the fastening of cables and markers.

- They are particularly suitable for fastening CLI M, SFX, WKM and WKS cable markers
- IEC 62275: 2006-conformant
- Fracture-resistant polyamide PA 6.6 with flammability rating V2 to UL-94

## General ordering data

| | |
|---|---|
| Version | Cable ties, 9 x 780 mm, Polyamide 66, 700 N |
| Order No. | 7940006074 |
| Type | CB 780/9 NC |
| GTIN (EAN) | 4032248531202 |
| Qty. | 1000 items |

# Data sheet

## CB 780/9 NC

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

# Technical data

### Approvals

| | |
|---|---|
| Approvals |  |
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (UR) | E317499 |

### Dimensions and weights

| | | | |
|---|---|---|---|
| Depth | 1.9 mm | Depth (inches) | 0.0748 inch |
| Height | 780 mm | Height (inches) | 30.7086 inch |
| Width | 9 mm | Width (inches) | 0.3543 inch |
| Net weight | 13.1 g | | |

### Temperatures

| | |
|---|---|
| Operating temperature range | -40...85 °C |

### Environmental Product Compliance

| | |
|---|---|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

### Installation materials

| | | | |
|---|---|---|---|
| UV-resistant | No | For re-opening | No |
| UL 94 flammability rating | V-2 | Operating temperature range, max. | 85 °C |
| Operating temperature range, min. | -40 °C | Halogen | No |
| Cable diameter, max. | 233 mm | Basic material | Polyamide 66 |
| Tensile strength | 700 N | Bundle diameter, max. | 233 mm |
| Tensile strength (Pound-force) | 157 lbf | Bundle diameter, min. | 34 mm |

### Important note

| | |
|---|---|
| Product information | Number of bags in box (pieces): 10<br>Number of items in bag (pieces): 100<br>One delivery unit corresponds to one box quantity, and only multiples of the delivery unit can be ordered. |

### Classifications

| | | | |
|---|---|---|---|
| ETIM 8.0 | EC000046 | ETIM 9.0 | EC000046 |
| ETIM 10.0 | EC000046 | ECLASS 14.0 | 27-14-07-02 |
| ECLASS 15.0 | 27-14-07-02 | | |

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Drawings

