

## FP ENC DR15 68 XC A

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Extensive range of accessories for the FieldPower® boxes.  
Cable seals, terminal rails, locking elements and much more.

### General ordering data

Version	Field Power® terminal rail, Steel, galvanized, 68 mm, for aluminium lid
Order No.	<a href="#">8000046634</a>
Type	FP ENC DR15 68 XC A
GTIN (EAN)	4050118686586
Qty.	5 items

**FP ENC DR15 68 XC A**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	15 mm	Depth (inches)	0.5906 inch
Height	35 mm	Height (inches)	1.378 inch
Width	68 mm	Width (inches)	2.6772 inch
Net weight	9.4 g		

**Temperatures**

Storage temperature Operating temperature

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General specifications**

Installation advice Screws included Basic material Steel, galvanized  
 Colour silver

**General data**

Basic material Steel, galvanized Colour silver  
 Type of mounting Screw mounting Mounting position, installation notice for aluminium lid  
 Installation advice Screws included Version with slot

**Classifications**

ETIM 8.0 EC001285 ETIM 9.0 EC001285  
 ETIM 10.0 EC001285 ECLASS 14.0 27-40-06-02  
 ECLASS 15.0 27-40-06-02

**Drawings**



## FP ENC DR15 68 XC A

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Bits E6,3 - Torx®



The Weidmüller bits are standard bits which are highly popular with users thanks to their good quality, large range and efficiency. The computer-controlled hardening method enables Weidmüller to guarantee a consistently high standard of quality.

The high-quality raw materials used make it possible to reach torques far higher than any of those specified in the relevant DIN standards:

- DIN 526 1 for PH/PZ bits,
- DIN 5263 for slotted bits,
- Camcar standard for TORX bits

That means a long life at high torques and hence ideal conditions for standard situations.

The benefits:

- Suitable for all types of screws. Because of their excellent hardness values of 59-61 HRC, they are suitable for use with both manual and power tools.
- Good wearing resistance and thus a long life expectancy.
- Optimum fit in all DIN screws means low wear and optimum torque transmission.
- Manufactured to meet professional quality criteria according to relevant ISO standards with a consistently high standard of quality.

## General ordering data

Type	BIT E6,3 T20 X 150	Version	
Order No.	<a href="#">2821510000</a>	Mounting tool	
GTIN (EAN)	4064675359050		
Qty.	5 ST		

## DMS PRO



Weidmüller torque screwdrivers have an ergonomic design and are therefore ideal for use with one hand. They can be used without causing fatigue in all installation positions. Apart from that, they incorporate an automatic torque limiter and have a good reproducibility accuracy.

## General ordering data

Type	DMS PRO	Version	
Order No.	<a href="#">1479120000</a>	Mounting tool	
GTIN (EAN)	4050118287011		
Qty.	1 ST		