

KLIPPON POK 252512 M25 E60

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



Fire-resistant terminal boxes E30, E60 and E90
 Robust terminal box for safe power supply of emergency systems in case of fire, emergency lighting in underground, metro, railway and road tunnels up to a maximum of 90 minutes according to DIN 4102-04. The equipped enclosures of the Klippon® POK and Klippon® STB series are suitable wherever corrosion resistance, impact resistance and a high degree of protection is required.

Features:

- Available in a wide variety of designs on customer request
- Tested and approved according to DIN 4102-04 (E30, E60 and E90) - The exact details must be taken from the "Declaration of Manufacturer"
- High quality through the use of proven basic products of the Klippon® brand

General ordering data

Version	Klippon POK (polyester empty enclosure), Enclosures, Height: 250 mm, Width: 255 mm, Depth: 120 mm, Basic material: Glass fibre-reinforced polyester, untreated, grey, Light Grey
Order No.	8000052518
Type	KLIPPON POK 252512 M25 E60
GTIN (EAN)	4064675360391
Qty.	1 items

KLIPPON POK 252512 M25 E60

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	120 mm	Depth (inches)	4.7244 inch
Height	250 mm	Height (inches)	9.8425 inch
Height of lowest version	120 mm	Width	255 mm
Width (inches)	10.0394 inch	Mounting dimension - height	200 mm
Mounting dimension - width	235 mm	Net weight	4364.37 g

Temperatures

Operating temperature	-20 °C...80 °C
-----------------------	----------------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	1d28ada4-1634-4382-8635-45f6353a6574

horizontal assembly

SAKK 10	8	Fuse holder available	No
---------	---	-----------------------	----

Material data

Surface finish	untreated	Basic material	Glass fibre-reinforced polyester
----------------	-----------	----------------	----------------------------------

General data

Colour	grey, Light Grey	Protection degree	IP66
Colour chart (similar)	RAL 7035		

Housing

Basic material	Glass fibre-reinforced polyester	Drill holes side A	2 x M25
Drill holes side B	1 x M25		

Standard features

Reference product	KLIPPON POK 252512 , TS 32X15 2M/ST/ZN , SAKK 10, QL 2 SAKK 10 , KISC M3X20.5/10 EK4 , AP SAKK4/10 KER/WS , MEW 1/32, WS 8/8 MM WS, VG M25-K67, GWDR M25-NP, SKMU M25 - K GR
-------------------	--

Important note

Product information	The fire rating up to E60 acc. to DIN 4102-12 depends on concrete configurations / installations (details see "Declaration of Manufacturer" in "Downloads")
---------------------	---

KLIPPON POK 252512 M25 E60

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

The enclosure is used for functional integrity and serves as a distribution box for cables with 4 potentials.

Classifications

ETIM 8.0	EC002503	ETIM 9.0	EC002503
ETIM 10.0	EC002503	ECLASS 14.0	27-18-05-02
ECLASS 15.0	27-18-05-02		

KLIPPON POK 252512 M25 E60

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

Similar to illustration

