

KEBXHS403020S4B1 AK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Klippon® EBx HS stainless steel enclosures, where the lid is fixed by Hinge and Screws, are offered as high quality products with leading performance characteristics in oil and chemistry hazardous industry. It is certified and complied with the international standards - like ATEX and IECEx approval.

General ordering data

Version	Klippon EBx HS (Essential Box Ex - Hinge Screw), Empty enclosure, Height: 400 mm, Width: 300 mm, Depth: 200 mm, Gland plates: Bottom, Basic material: Stainless steel 1.4404 (316L), Brushed, silver
Order No.	8000071020
Type	KEBXHS403020S4B1 AK
GTIN (EAN)	4064675385004
Qty.	1 items
Local product	Only available in certain countries

KEBXHS403020S4B1 AK

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

General ordering data

Local product Only available in certain countries

Dimensions and weights

Depth	200 mm	Depth (inches)	7.874 inch
Height	400 mm	Height (inches)	15.748 inch
Width	300 mm	Width (inches)	11.811 inch
Mounting dimension - height	360 mm	Mounting dimension - width	260 mm
Net weight	7920 g		

Temperatures

Operating temperature -55 °C...135 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Cable glands, left

M63	3	M75	3
M12	180	M50	8
M16	87	M32	21
M25	36	M20	58
M40	11		

Cable glands, right

M25	36	M63	3
M75	3	M16	87
M40	11	M50	8
M32	21	M20	58
M12	180		

Cable glands, top/bottom

M20	30	M12	95
M63	2	M40	7
M32	9	M25	18
M50	3	M75	2
M16	50		

KEBXHS403020S4B1 AK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Certificate numbers enclosure

Declaration of Conformity No. (DoC LVD)	DE PS265X 210819 001ISS01	Attestation of Conformity No. (AoC)	DE PS265x 210819 000ISS01
Certificate no. empty enclosure (INMETRO)	LMP 21.0601U	Certificate no. Terminal Box (ATEX)	IBExU 21ATEX 1017 X
Certificate no. empty enclosure (ATEX)	IBExU 21ATEX 1016 U	Certificate no. Terminal Box (INMETRO)	LMP 21.0602X
Certificate no. Terminal Box (IECEX)	IECEX IBE 21.0012	Certificate no. empty enclosure (IECEX)	IECEX IBE 21.0006U
Approval conditions	ATEX, IECEX, INMETRO		

General information

Material thickness of cover	1.5 mm	Material thickness of flange	3 mm
Material thickness	1.5 mm	Operating temperature, max.	135 °C
Operating temperature, min.	-55 °C	Lid attachment	M6 hex-head slotted screws SW10 + hinges
Standards	EN 60079-0, IEC 60079-0, EN 60079-7, IEC 60079-7, EN 60079-11, IEC 60079-11, EN 60079-31, IEC 60079-31	Surface finish	Brushed
Impact resistance	7 J ATEX version, 10 J version standard	AF size	10 mm
Protection degree	IP66	Basic material	Stainless steel 1.4404 (316L)
Seal material	Silicone (cover + flange)	Torque for lid screws	2.5 Nm
Integral fixing	4, 6 or 9 stud bolts M6 inner (female) thread	Enclosure attachment	4 or 6, M6 blind thread hole on backside; optionally via additional mounting feet
Flange plate mounting	M6 hexagonal head screws 10 SW	Protection class (UL)	Type 1, Type 4, Type 4X
Number of lid screws	2	Gland plates	Bottom
Access opening: width	243.6 mm	Opening angle lid	125.00 °
Flange plate	Yes	Max. payload	12 kg
Lid	Yes	Access opening: height	349.6 mm
Position PE bolts	Enclosure side C	Areas of use	Chemical industry, Explosive risk zone, Oil and gas industry, Onshore, Process industry, Building systems and technology, Machine construction, Packaging industry

Housing earth

Earth, enclosure, internal	Welded-on M6 stainless-steel earth stud in enclosure body and lid.
----------------------------	--

horizontal assembly

Number of DIN rails and terminals (10 mm ² , horizontal)	4x20	WDU 16 / ZDU 16	4x17
WDU 2,5 / ZDU 2,5 / IDU 2,5	4x41	WDU 35 / ZDU 35	4x12
WDU 4 / ZDU 4	4x34	WDU 6 / ZDU 6	4x25

vertical assembly

WDU 10 / ZDU 10	3x30	WDU 16 / ZDU 16	3x25
WDU 2,5 / ZDU 2,5 / IDU 2,5	3x61	WDU 35 / ZDU 35	3x18

KEBXHS403020S4B1 AK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data**

WDU 4 / ZDU 4

3x51

WDU 6 / ZDU 6

3x38

Important note

Product information

All articles with M6 threaded rivet as standard; UL variants with M10 earth bolt on request

Classifications

ETIM 8.0

EC002503

ETIM 9.0

EC002503

ETIM 10.0

EC002503

ECLASS 14.0

27-18-05-02

ECLASS 15.0

27-18-05-02

KEBXHS403020S4B1 AK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

