

TS35X15 ST POK 1222

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Similar to illustration



The Klippon® POK enclosure range is made from a high-quality glass fibre reinforced polyester and is ideal for applications and environments where corrosion resistance, impact resistance and a high IP protection class are a requirement.

Key features of the extensive product range:

- Available in 17 sizes
- Two standard finishes (colours): grey (similar to RAL 7001 for industrial use) and black (similar to RAL 9011 for harsh environments, Ex)
- Cover with stainless steel screws in cross-head / slotted design
- Moulded gasket made of silicone or chloroprene
- Fixing holes outside the sealed area to ensure high ingress protection of IP66
- Impact resistance up to 7 Joules
- Mounting directly in the enclosure or using an internal mounting plate
- Direct wall mounting possible using fixing holes or mounting feet
- Fastening thread to attach mounting rails and plates
- Up to E60 fire rating dependent on the configuration
- Weidmüller can manufacture and supply this enclosure to match customer specifications - fitted with all necessary terminals and cable glands.

General ordering data

| | |
|------------|--|
| Version | Rail, TS 35, TS 35 x 15, with slot, Steel, galvanic zinc plated and passivated |
| Order No. | 8000073209 |
| Type | TS35X15 ST POK 1222 |
| GTIN (EAN) | 4064675356561 |
| Qty. | 20 items |

TS35X15 ST POK 1222

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 15 mm | Depth (inches) | 0.5906 inch |
| Height | 35 mm | Height (inches) | 1.378 inch |
| Width | 205 mm | Width (inches) | 8.0709 inch |
| Net weight | 145 g | | |

Temperatures

Operating temperature

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General information

| | | | |
|--------------------|--------------|---------------------|-------------------------------------|
| Material thickness | 1.5 mm | Installation advice | Direct mounting |
| Standards | DIN EN 60715 | Surface finish | galvanic zinc plated and passivated |
| Basic material | Steel | Integral fixing | Screwed |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001285 | ETIM 9.0 | EC001285 |
| ETIM 10.0 | EC001285 | ECLASS 14.0 | 27-40-06-02 |
| ECLASS 15.0 | 27-40-06-02 | | |