


MPS 6/03 S LF TN B B**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image****SNAP IN** **General ordering data**

Version	PCB plug-in connector, female plug, Pitch in mm (P): 6.35 mm, Number of poles: 3, 180°, Box
Order No.	8000168328
Type	MPS 6/03 S LF TN B B
GTIN (EAN)	4099987795715
Qty.	64 items
Product data	IEC: 1000 V / 47.2 A / 0.75 - 6 mm ² UL: 600 V / 30 A / AWG 20 - AWG 10
Packaging	Box

MPS 6/03 S LF TN B B

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	43 mm	Depth (inches)	1.6929 inch
Height	20.5 mm	Height (inches)	0.8071 inch
Width	26.5 mm	Width (inches)	1.0433 inch
Net weight	17.06 g		

System Parameters

Product family	OMNIMATE 4.0	Type of connection	Field connection
Wire connection method	SNAP IN with lever	Pitch in mm (P)	6.35 mm
Pitch in inches (P)	0.250 "	Conductor outlet direction	180°
Number of poles	3	L1 in mm	12.70 mm
L1 in inches	0.500 "	Number of rows	1
Pin series quantity	1	Touch-safe protection acc. to DIN VDE 57 106	Safe from finger touch
Touch-safe protection acc. to DIN VDE 0470	IP 20	Protection degree	IP20
Volume resistance	≤5 mΩ	Stripping length	11 mm
Plugging cycles	≥ 25	Plugging force per pole, max.	11.25 N
Pulling force per pole, max.	10 N		

Material data

Insulating material	PA 9T	Colour	black
Colour of operational elements	orange	Colour chart (similar)	RAL 9011
Insulating material group	I	Comparative Tracking Index (CTI)	≥ 600
Moisture Level (MSL)	1	UL 94 flammability rating	V-0
Contact material	Cu-alloy	Contact surface	tinned
Storage temperature, min.	-40 °C	Storage temperature, max.	70 °C
Operating temperature, min.	-50 °C	Operating temperature, max.	125 °C

Conductors suitable for connection

Conductor cross-section (rated connection), min.	0.5 mm ²		
Conductor cross-section (rated connection), max.	6 mm ²		
Solid, min. H05(07) V-U	0.75 mm ²		
Solid, max. H05(07) V-U	4 mm ²		
Flexible, min. H05(07) V-K	0.75 mm ²		
Flexible, max. H05(07) V-K	6 mm ²		
w. plastic collar ferrule, DIN 46228 pt 4, 0.5 mm ² min.			
w. plastic collar ferrule, DIN 46228 pt 4, 4 mm ² max.			
w. wire end ferrule, DIN 46228 pt 1, min.	0.75 mm ²		
w. wire end ferrule, DIN 46228 pt 1, max.	4 mm ²		
Clampable conductor	Cross-section for conductor connection	nominal	0.5 mm ²
		Stripping length	nominal 14 mm
		Recommended wire-end ferrule	H0.5/18 OR
		Stripping length	nominal 12 mm
	Cross-section for conductor connection	nominal	0.75 mm ²
		Stripping length	nominal 14 mm
		Recommended wire-end ferrule	H0.5/16 OR
		Stripping length	nominal 14 mm

MPS 6/03 S LF TN B B

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

	Recommended wire-end ferrule	H0,75/18 W
	Stripping length	nominal 12 mm
	Recommended wire-end ferrule	H0,75/16 W
Cross-section for conductor connection	nominal	1 mm ²
wire end ferrule	Stripping length	nominal 15 mm
	Recommended wire-end ferrule	H1,0/18 GE
	Stripping length	nominal 12 mm
	Recommended wire-end ferrule	H1,0/16 GE
Cross-section for conductor connection	nominal	1.5 mm ²
wire end ferrule	Stripping length	nominal 15 mm
	Recommended wire-end ferrule	H1,5/18D SW
	Stripping length	nominal 12 mm
	Recommended wire-end ferrule	H1,5/16 R
Cross-section for conductor connection	nominal	2.5 mm ²
wire end ferrule	Stripping length	nominal 14 mm
	Recommended wire-end ferrule	H2,5/19T GR
	Stripping length	nominal 13 mm
	Recommended wire-end ferrule	H2,5/16DS BL
Cross-section for conductor connection	nominal	4 mm ²
wire end ferrule	Stripping length	nominal 14 mm
	Recommended wire-end ferrule	H4,0/20T OR
	Stripping length	nominal 12 mm
	Recommended wire-end ferrule	H4,0/18T OR

Rated data acc. to IEC

tested acc. to standard	IEC 60664-1, IEC 61984	Rated current at min. number of poles (Tu = 20 °C)	47.2 A
Rated current, max. number of poles (Tu=20°C)	41 A	Rated current, min. number of poles (Tu=40°C)	42.5 A
Rated current at max. number of poles (Tu = 40 °C)	36.8 A	Rated voltage for surge voltage class (pollution degree II/2)	1000 V
Rated voltage for surge voltage class (pollution degree III/2)	1000 V	Rated voltage for surge voltage class (pollution degree III/3)	800 V
Rated impulse voltage for surge voltage class (pollution degree II/2)	8 V	Rated impulse voltage for surge voltage class (pollution degree III/2)	8 kV
Rated impulse voltage for surge voltage class (contamination degree III/3)	8 kV	Creepage distance, min.	11.2 mm
Clearance, min.	11.2 mm		

Rated data acc. to UL 1059

Rated voltage (Use group B / UL 1059)	600 V	Rated voltage (Use group C / UL 1059)	600 V
Rated voltage (Use group D / UL 1059)	600 V	Rated voltage (Use group F / UL 1059)	1000 V
Rated current (Use group B / UL 1059)	30 A	Rated current (Use group C / UL 1059)	30 A
Rated current (Use group D / UL 1059)	5 A	Wire cross-section, AWG, min.	AWG 20
Wire cross-section, AWG, max.	AWG 10		

MPS 6/03 S LF TN B B**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Important note**

Notes

- Rated current related to rated cross-section & min. No. of poles.
- P on drawing = pitch
- Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.
- Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months

Classifications


ETIM 8.0	EC002638	ETIM 9.0	EC002638
ETIM 10.0	EC002638	ECLASS 14.0	27-46-02-02
ECLASS 15.0	27-46-02-02		

Drawings


Product image



Dimensional drawing



Derating curve



Derating curve

