Data sheet

# MPS 3/13 S LF TN B B

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com





## General ordering data

| | |
|---|---|
| Version | PCB plug-in connector, female plug, Pitch in mm (P): 3.50 mm, Number of poles: 13, 180°, Box |
| Order No. | 8000179413 |
| Type | MPS 3/13 S LF TN B B |
| Qty. | |
| Product data | IEC: 320 V / 15 A / 0.34 - 1.5 mm²<br>UL: 300 V / 8 A |
| Packaging | Box |

# MPS 3/13 S LF TN B B

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

| | | | |
|---|---|---|---|
| Depth | 24.06 mm | Depth (inches) | 0.9472 inch |
| Height | 10 mm | Height (inches) | 0.3937 inch |
| Width | 54.3 mm | Width (inches) | 2.1378 inch |

### Temperatures

| | |
|---|---|
| Ambient temperature | -50 °C...125 °C |

### Material data

| | | | |
|---|---|---|---|
| Insulating material | PA 9T | Colour | black |
| Colour of operational elements | green | Colour chart (similar) | RAL 9011 |
| Insulating material group | I | Comparative Tracking Index (CTI) | ≥ 600 |
| Moisture Level (MSL) | 1 | UL 94 flammability rating | V-0 |
| Contact material | Cu-alloy | Contact surface | tinned |
| Storage temperature, min. | -25 °C | Storage temperature, max. | 55 °C |
| Operating temperature, min. | -50 °C | Operating temperature, max. | 125 °C |

### Conductors suitable for connection

| | | | |
|---|---|---|---|
| Conductor cross-section (rated connection), min. | 0.34 mm² | Conductor cross-section (rated connection), max. | 1.5 mm² |
| Wire connection cross section AWG, min. | AWG 22 | Wire connection cross section AWG, max. | AWG 14 |
| Solid, min. H05(07) V-U | 0.34 mm² | Solid, max. H05(07) V-U | 1.5 mm² |
| Flexible, min. H05(07) V-K | 0.34 mm² | Flexible, max. H05(07) V-K | 1.5 mm² |
| w. plastic collar ferrule, DIN 46228 pt 4, min. | 0.34 mm² | w. plastic collar ferrule, DIN 46228 pt 4, max. | 1 mm² |
| w. wire end ferrule, DIN 46228 pt 1, min. | 0.34 mm² | w. wire end ferrule, DIN 46228 pt 1, max. | 1.5 mm² |
| Outer diameter (insulation), max. | 4.00 mm | | |

### Rated data acc. to IEC

| | | | |
|---|---|---|---|
| Rated current at min. number of poles (Tu = 20 °C) | 15 A | Rated current, max. number of poles (Tu=20°C) | 12 A |
| Rated current, min. number of poles (Tu=40°C) | 13 A | Rated current at max. number of poles (Tu = 40 °C) | 11 A |
| Rated voltage for surge voltage class (pollution degree II/2) | 320 V | Rated voltage for surge voltage class (pollution degree III/2) | 160 V |
| Rated voltage for surge voltage class (pollution degree III/3) | 160 V | Rated impulse voltage for surge voltage class (pollution degree II/2) | 320 V |
| Rated impulse voltage for surge voltage class (pollution degree III/2) | 2.5 kV | Rated impulse voltage for surge voltage class (contamination degree III/3) | 2.5 kV |

### Rated data acc. to UL 1059

| | | | |
|---|---|---|---|
| Rated voltage (Use group B / UL 1059) | 300 V | Rated voltage (Use group C / UL 1059) | 50 V |
| Rated voltage (Use group D / UL 1059) | 300 V | Rated voltage (Use group F / UL 1059) | 320 V |
| Rated current (Use group B / UL 1059) | 8 A | Rated current (Use group C / UL 1059) | 8 A |
| Rated current (Use group D / UL 1059) | 8 A | Rated current (Use group F / UL 1059) | 8 A |

### Important note

| | |
|---|---|
| Notes | • Rated current related to rated cross-section & min. No. of poles.<br>• P on drawing = pitch |

# MPS 3/13 S LF TN B B

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Technical data

- Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.
- In accordance with IEC 61984, OMNIMATE-connectors are connectors without breaking capacity (COC). During designated use, connectors are not allowed to be engaged or disengaged when live or under load
- Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months

### Classifications

| | | | |
|---|---|---|---|
| ETIM 8.0 | EC002638 | ETIM 9.0 | EC002638 |
| ETIM 10.0 | EC002638 | ECLASS 14.0 | 27-46-02-02 |
| ECLASS 15.0 | 27-46-02-02 | | |

# MPS 3/13 S LF TN B B

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Drawings

