

**POK COPL 082306 MSZN****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The Klippon® POK enclosure range is made from a high-quality glass fibre reinforced polyester and is ideal for applications and environments where corrosion resistance, impact resistance and a high IP protection class are a requirement.

Key features of the extensive product range:

- Available in 17 sizes
- Two standard finishes (colours): grey (similar to RAL 7001 for industrial use) and black (similar to RAL 9011 for harsh environments, Ex)
- Cover with stainless steel screws in cross-head / slotted design
- Moulded gasket made of silicone or chloroprene
- Fixing holes outside the sealed area to ensure high ingress protection of IP66
- Impact resistance up to 7 Joules
- Mounting directly in the enclosure or using an internal mounting plate
- Direct wall mounting possible using fixing holes or mounting feet
- Fastening thread to attach mounting rails and plates
- Up to E60 fire rating dependent on the configuration
- Weidmüller can manufacture and supply this enclosure to match customer specifications - fitted with all necessary terminals and cable glands.

**General ordering data**

|            |                                                                                                  |
|------------|--------------------------------------------------------------------------------------------------|
| Version    | Klippon POK (polyester empty enclosure), Earthing plate, Basic material: Steel sheet zinc plated |
| Order No.  | <a href="#">8000191933</a>                                                                       |
| Type       | POK COPL 082306 MSZN                                                                             |
| GTIN (EAN) | 4069165099454                                                                                    |
| Qty.       | 5 items                                                                                          |

**Technical data****Dimensions and weights**

|            |        |
|------------|--------|
| Net weight | 45.9 g |
|------------|--------|

**Temperatures**

|                       |
|-----------------------|
| Operating temperature |
|-----------------------|

**General information**

|                |                         |
|----------------|-------------------------|
| Basic material | Steel sheet zinc plated |
|----------------|-------------------------|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002623    | ETIM 9.0    | EC002623    |
| ETIM 10.0   | EC002623    | ECLASS 14.0 | 27-18-28-14 |
| ECLASS 15.0 | 27-18-28-14 |             |             |