

TABWESTNETZ**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

With our pre-assembled SET's for instrument transformer wiring you save time and storage costs. We offer various application setups including all relevant accessories and including labeling in one complete package.

General ordering data

Version	Test-disconnect terminal, Screw connection, beige, 6 mm², 30 A, Number of connections: 20, Number of levels: 1
Order No.	8000095146
Type	TABWESTNETZ
GTIN (EAN)	4064675888550
Qty.	1 items
Delivery status	Discontinued
Available until	2025-05-06T00:00:00+02:00
Alternative product	TABWESTNETZWECHSELTAFLNS

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	79 mm	Depth (inches)	3.1102 inch
Height	100 mm	Height (inches)	3.937 inch
Width	115.3 mm	Width (inches)	4.5394 inch
Net weight	521 g		

Temperatures

Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	130 °C
----------------------------------	--------	----------------------------------	--------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	Wemid	Colour	beige
Colour of operational elements	Miscellaneous	UL 94 flammability rating	V-0

System specifications

End cover plate required	No	Number of levels	1
Number of clamping points per level	20	Mounting rail	TS 35
N-function	No	PE function	No
PEN function	No		

Additional technical data

Snap-on	Yes	Type of mounting	TS 35
---------	-----	------------------	-------

Conductors for clamping (rated connection)

Connection direction	on side	Type of connection	Screw connection
Number of connections	20	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max.	6 mm ²
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min.	0.5 mm ²	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	6 mm ²
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	0.5 mm ²	Wire connection cross section, finely stranded, max.	10 mm ²
Wire connection cross section, finely stranded, min.	0.5 mm ²	Connection cross-section, stranded, max.	10 mm ²
Connection cross-section, stranded, min. 0.5 mm ²		Wire connection cross-section, solid core, max.	10 mm ²
Wire connection cross-section, solid core, min.	0.5 mm ²		

General

Standards	IEC 60947-7-1	Mounting rail	TS 35
-----------	---------------	---------------	-------

Technical data**Rating data**

Rated cross-section	6 mm ²	Nominal current	30 A
Standards	IEC 60947-7-1	Surge voltage category	III
Pollution severity	3		

Classifications

ETIM 8.0	EC000902	ETIM 9.0	EC000902
ETIM 10.0	EC000902	ECLASS 14.0	27-25-01-09
ECLASS 15.0	27-25-01-09		

Drawings

