

PVC AC 1I 1O SPD2R + RJ45 04**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Version	AC voltage version, Auxiliary and alarm contact, Surge protection II, TN-C-S, TN-S, IT with N, IT without N, TT
Order No.	8000104168
Type	PVC AC 1I 1O SPD2R + RJ45 04
GTIN (EAN)	4099986573475
Qty.	1 items

PVC AC 1I 10 SPD2R + RJ45 04

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	132 mm	Depth (inches)	5.1968 inch
Height	200 mm	Height (inches)	7.874 inch
Width	200 mm	Width (inches)	7.874 inch
Net weight	2866.64 g		

Temperatures

Ambient temperature	-40 °C...50 °C	Humidity	0...85% rel. humidity, no condensation
---------------------	----------------	----------	--

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	bdab5698-6a20-4370-8e28-8810d882d01a

Rated data IEC / EN

Number of poles	4	Signalling contact	250 V 1A 1CO
Rated voltage (AC)	230 V	Low voltage network	TN-C-S, TN-S, IT with N, IT without N, TT
Protection level Up at IN (N-PE)	≤ 1.5 kV	Voltage type	AC
Fuse protection	No	Frequency range, max.	60 Hz
Frequency range, min.	50 Hz	Standards	IEC 61643-11, EN 61643-11
Requirements class, acc. to EN 61643-11	T2	Max. continuous voltage, Uc (AC)	300 V
Discharge current I _{max} (8/20μs) N-PE	65 kA	Discharge current I _n (8/20μs) N-PE	40 kA
Energy coordination (≤10 m)	Type II, Type III	Discharge current I _n (8/20μs) wire-PE	20 kA
Acoustic signal	No	Discharge current I _{max} (8/20μs) wire-PE	50 kA
Protection level Up at IN (L/N-PE)	≤ 1.5 kV	Short-circuit current rating I _{SCCR}	50 kA
Follow-on current extinguishing capability I _{fi}	Follow current need not be taken into account	Integrated back-up fuse	No

AC inputs

Stripping length, rated connection	12 mm	Wire cross-section, solid, max.	6 mm ²
Wire cross-section, solid, min.	0.5 mm ²	Connection cross-section, stranded, max.	6 mm ²
Connection cross-section, stranded, min.	0.34 mm ²	Connection type, AC input cable	PUSH IN
Number of AC inputs	3		

AC outputs

Stripping length, rated connection	12 mm	Wire cross-section, solid, max.	6 mm ²
Wire cross-section, solid, min.	0.5 mm ²	Connection cross-section, stranded, max.	6 mm ²

PVC AC 1I 10 SPD2R + RJ45 04**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data**Connection cross-section, stranded, min. 0.34 mm²**Included in delivery**

Included accessories	Article	Mounting foot
	Quantity	4
	Article	Sealing plug
	Quantity	8

Guarantee

Time interval 5 years

General data

Standards	IEC 61643-11, EN 61643-11	Protection degree	IP65
-----------	---------------------------	-------------------	------

Classifications

ETIM 8.0	EC000941	ETIM 9.0	EC000941
ETIM 10.0	EC000941	ECLASS 14.0	27-17-90-90
ECLASS 15.0	27-17-90-90		

PVC AC 1I 10 SPD2R + RJ45 04

Drawings

