

TAB NS NORD 14**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

With our pre-assembled SET's for instrument transformer wiring you save time and storage costs. We offer various application setups including all relevant accessories and including labeling in one complete package.

General ordering data

Version	Test-disconnect terminal, PUSH IN, beige, 6 mm ² , 30 A, Number of connections: 14, Number of levels: 1
Order No.	8000104257
Type	TAB NS NORD 14
GTIN (EAN)	4099986647664
Qty.	1 items
Delivery status	Discontinued
Available until	2025-05-06T00:00:00+02:00
Alternative product	TABNSNORD14

TAB NS NORD 14

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	79 mm	Depth (inches)	3.1102 inch
Height	100 mm	Height (inches)	3.937 inch
Width	136 mm	Width (inches)	5.3543 inch
Net weight	551 g		

Temperatures

Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	130 °C
----------------------------------	--------	----------------------------------	--------

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	Wemid	Colour	beige
Colour of operational elements	Miscellaneous	UL 94 flammability rating	V-0

System specifications

End cover plate required	No	Number of levels	1
Number of clamping points per level	14	Levels cross-connected internally	No
Mounting rail	TS 35	N-function	No
PE function	No	PEN function	No

Additional technical data

Snap-on	Yes	Explosion-tested version	No
Type of mounting	Snap-on		

Conductors for clamping (rated connection)

Connection direction	top	Type of connection	PUSH IN
Number of connections	14	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max.	6 mm ²
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min.	0.5 mm ²	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	6 mm ²
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	0.5 mm ²	Wire connection cross section, finely stranded, max.	10 mm ²
Wire connection cross section, finely stranded, min.	0.5 mm ²	Connection cross-section, stranded, max.	6 mm ²
Connection cross-section, stranded, min. 0.5 mm ²		Wire connection cross-section, solid core, max.	10 mm ²
Wire connection cross-section, solid core, min.	0.5 mm ²		

TAB NS NORD 14

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

General

Standards	IEC 60947-7-1	Mounting rail	TS 35
-----------	---------------	---------------	-------

Rating data

Rated cross-section	6 mm ²	Nominal current	30 A
Standards	IEC 60947-7-1	Surge voltage category	III
Pollution severity	3		

Classifications

ETIM 8.0	EC000902	ETIM 9.0	EC000902
ETIM 10.0	EC000902	ECLASS 14.0	27-25-01-09
ECLASS 15.0	27-25-01-09		

Drawings

