

## KTB MH 504020 S4EO

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Similar to illustration



The Klippon® TB enclosure range provides excellent performance characteristics, even under the most difficult environmental conditions. In addition, it complies with the stricter requirements of potentially explosive atmospheres found specifically in the process or power generation industries. The Klippon® TB MH enclosure range offers further improvements to a product line that is already successfully leading the market.

The Klippon® TB MH enclosure range has the following advantages:

- Available in 15 sizes and 3 standard depths
- Equipped with up to 4 gland plates
- The gasket is protected against compression
- Completely removable padlock tab
- Cover lock outside the sealed zone
- Improved temperature performance
- IP66/IP67 protection
- Completely removable lid – without a tool
- Earthing stud in the cover and base of the enclosure
- Welded mounting feet
- International approvals

## General ordering data

Version	Klippon TB MH (Terminal Box - Multi Hinge), Empty enclosure, stainless steel enclosure, Height: 508 mm, Width: 406 mm, Depth: 200 mm, Basic material: Stainless steel 1.4404 (316L), electropolished, silver
Order No.	<a href="#">8000108849</a>
Type	KTB MH 504020 S4EO
GTIN (EAN)	4099986755109
Qty.	1 items

## KTB MH 504020 S4EO

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

Approvals



RoHS Conform

## Dimensions and weights

Depth	200 mm	Depth (inches)	7.874 inch
Height	508 mm	Height (inches)	20 inch
Width	406 mm	Width (inches)	15.9842 inch
Net weight	13000 g		

## Temperatures

Operating temperature	-60 °C...135 °C	Note: room temperature (service)	Limited to IP66 protection when used in temperatures greater than 105 °C.
-----------------------	-----------------	----------------------------------	---------------------------------------------------------------------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	64dfc213-93f0-4c79-8ffa-c97fa9dcb873

## Cable glands, left

M63	0	M75	0
M12	60	M50	3
M16	45	M32	5
M25	20	M20	26
M40	4		

## Cable glands, right

M25	20	M63	0
M75	0	M16	45
M40	4	M50	3
M32	5	M20	26
M12	60		

## Cable glands, top/bottom

M20	22	M12	51
M63	3	M40	5
M32	7	M25	18
M50	4	M75	0
M16	39		

## KTB MH 504020 S4EO

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Certificate numbers enclosure

Certificate No. UL Haz.Loc.	E223792	Declaration of Conformatiy No. (DoC LVD)	DE PS261X 160412 001ISS03
Certificate No. UL Ord.Loc.	E243298	Certificate No. UL 508A	E223801
Attestation of Conformatiy No. (AoC)	DE PS261X 160309 001ISS06	Certificate No. UL Terminal Box	E223792
Certificate no. empty enclosure (INMETRO)	LMP 21.0016U	Certificate no. Terminal Box (ATEX)	IBExU14ATEX1050
Certificate no. empty enclosure (ATEX)	IBExU14ATEX1028 U	Certificate no. Terminal Box (INMETRO)	LMP 21.0017
Certificate no. Terminal Box (IECEx)	IECEXIBE14.0013	Certificate no. empty enclosure (IECEx)	IECEX IBE 14.0004U
Approval conditions	ATEX, IECEX, INMETRO, cULus		

## General information

Material thickness of cover	1.5 mm	Material thickness of flange	3 mm
Material thickness of enclosure	1.5 mm	Silicone	Yes
Operating temperature, max.	135 °C	Operating temperature, min.	-60 °C
Lid attachment	4 hinges and M6 hex-head slotted screws SW10	Standards	DIN EN 62208 - Empty enclosure standard, DIN EN 61373 Class 1B**, DIN EN 15085-2, EN 60079-0, EN 60079-7, EN 60079-31, IEC 60079-0, IEC 60079-7, IEC 60079-31
Surface finish	electropolished	Impact resistance	10 J version standard, 7 joules in acc. with IEC 60079-0
Protection degree	IP66, IP67	Basic material	Stainless steel 1.4404 (316L)
Seal material	Silicone	Torque for lid screws	2.5 Nm
Enclosure attachment	4 welded-on mounting feet with 11 mm holes (2 slotted feet and 2 cross-shaped feet)	Seal material of cover	Silicone
Note: protection class	If used in temperature ranges above 105 °C, IP protection is limited to IP 66.	Seal material of flange plate	Silicone
Protection class (UL)	Type 3, Type 4X, Type 12	Number of lid screws	4
Opening angle lid	130.00 °	Flange plate	No
Lid	Yes	Position PE bolts	Enclosure side C

## Housing earth

Earth, enclosure, cover	Welded-on M6 stainless-steel earth stud in enclosure body and lid.	Earth, enclosure, external	Continuous M10 earth stud in body enclosure
Earth, enclosure, internal	Welded-on M6 stainless-steel earth stud in enclosure body and lid.		

## horizontal assembly

WDU 10 / ZDU 10	3x30	WDU 16 / ZDU 16	2x24
WDU 2,5 / ZDU 2,5 / IDU 2,5	4x58	WDU 35 / ZDU 35	2x18
WDU 4 / ZDU 4	3x49	WDU 6 / ZDU 6	3x37

**KTB MH 504020 S4E0**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****vertical assembly**

WDU 10 / ZDU 10	2x39	WDU 16 / ZDU 16	2x32
WDU 2,5 / ZDU 2,5 / IDU 2,5	3x75	WDU 35 / ZDU 35	1x24
WDU 4 / ZDU 4	3x65	WDU 6 / ZDU 6	3x48

**Classifications**

ETIM 8.0	EC002503	ETIM 9.0	EC002503
ETIM 10.0	EC002503	ECLASS 14.0	27-18-05-02
ECLASS 15.0	27-18-05-02		

## KTB MH 504020 S4EO

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Gland plates without earthing studs



Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

Flange plates

Flange plates in two thicknesses, for easy replacement of pre-assembl

## General ordering data

Type	KTB GP XX4020V AB S4 3MM	Version
Order No.	<a href="#">8000112982</a>	Klippon TB (Terminal Box), flange plate, straight, Height: 396 mm,
GTIN (EAN)	4099986799240	Width: 167 mm, Depth: 3 mm, Gland plates: Bottom, top, Basic
Qty.	1 ST	material: Stainless steel 1.4404 (316L), electropolished, silver

## Gland plates with earthing studs



Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

Flange plates

Flange plates in two thicknesses, for easy replacement of pre-assembl

## General ordering data

Type	KTB GP XX4020V AB S4 PE	Version
Order No.	<a href="#">8000114910</a>	Klippon TB (Terminal Box), flange plate, straight, Height: 396 mm,
GTIN (EAN)	4099986797505	Width: 167 mm, Depth: 3 mm, Gland plates: top, Bottom, Basic
Qty.	1 ST	material: Stainless steel 1.4404 (316L), electropolished, silver

## Gland plates made out of stainless steel - 6 mm



Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

Flange plates

Flange plates in two thicknesses, for easy replacement of pre-assembl

## General ordering data

Type	KTB GP XX4020V AB S4 6MM	Version
Order No.	<a href="#">8000114137</a>	Klippon TB (Terminal Box), flange plate, straight, Height: 396 mm,
GTIN (EAN)	4099986804753	Width: 167 mm, Depth: 6 mm, Gland plates: top, Bottom, Basic
Qty.	1 ST	material: Stainless steel 1.4404 (316L), electropolished, silver

## KTB MH 504020 S4E0

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## 500 x 400mm



Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

## Mounting plates

Mounting plates, with and without hole patterns, for longitudinal and transverse mounting of DIN mounting rails or components directly onto the mounting plate.

## General ordering data

Type	KTB MOPL 5040 MSZN	Version
Order No.	<a href="#">8000110196</a>	Klippon TB (Terminal Box), Mounting plate, Height: 453 mm, Width: 345 mm, Depth: 1.5 mm, Basic material: Sheet steel, galvanized, silver
GTIN (EAN)	4099986779341	
Qty.	1 ST	
Type	KTB MOPL 5040 MSZN H	Version
Order No.	<a href="#">8000115916</a>	Klippon TB (Terminal Box), Mounting plate, Height: 453 mm, Width: 345 mm, Depth: 1.5 mm, Basic material: Sheet steel, galvanized, silver
GTIN (EAN)	4099986783041	
Qty.	1 ST	
Type	KTB MOPL 5040 S2N H	Version
Order No.	<a href="#">8000115905</a>	Klippon TB (Terminal Box), Mounting plate, Height: 453 mm, Width: 345 mm, Depth: 1.5 mm, Basic material: Stainless steel 1.4301 (304), untreated, silver
GTIN (EAN)	4099986782945	
Qty.	1 ST	

## Type label holder



Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

## Nameplate holders

There are a variety of designed label holders available for prominent display as required and for additional nameplates as needed.

## General ordering data

Type	TPSDHA KTB 70X70M3 S2 R	Version
Order No.	<a href="#">1279320000</a>	Klippon TB (Terminal Box), Ratings plate holder, Riveted, Height: 70 mm, Width: 70 mm, Depth: 20 mm, Basic material: Stainless steel 1.4301, Stainless steel 1.4301 (304), Mirror polished, silver
GTIN (EAN)	4050118070101	
Qty.	1 ST	

## KTB MH 504020 S4EO

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Installation material



Integrate, expand and customise - the perfect supplement to every application

The fully structured range of system accessories for the new Klippon® TB enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application.

## Mounting hardware kits

Mounting hardware kits are available for quick and easy installation of type label holders, document holders and rain hoods.

The label fastening set – SD is required to install a plastic (Trafolyte) ID or type label. With the aid of this set can you mount the ID or type label directly on the enclosure cover. The label fastening set has been specially developed for this purpose. Only by using this fastening set can you ensure that there will be no leaks into the enclosure or damage to the label.

The universal fastening set – TPSD has been developed to enable secure and quick installation of type label holders, rain covers or document holders, for example. By using this fastening set, the risk of leaks can be minimised, if not avoided.

## General ordering data

Type	SD FIXING SET	Version
Order No.	<a href="#">1285200000</a>	Klippon TB (Terminal Box), Identification plate fixing set, Height: 12
GTIN (EAN)	4050118075472	mm, Width: 12 mm, Depth: 16.4 mm, Basic material: Stainless steel, rust-proof, untreated, silver
Qty.	1 ST	
Type	TPSD FIXING SET KTB	Version
Order No.	<a href="#">1252190000</a>	Klippon TB (Terminal Box), Type plate fixings set, Basic material:
GTIN (EAN)	4050118043969	Stainless steel, rust-proof, untreated, silver
Qty.	20 ST	

## Earthing stud



Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

## Earthing bolt

Earthing bolts to exchange as a complete component in two versions – brass and stainless steel.

## General ordering data

Type	PEBZ M10 KTB BR SET	Version
Order No.	<a href="#">1192680000</a>	Klippon TB (Terminal Box), Earthing stud, Miscellaneous, Height:
GTIN (EAN)	4032248974641	21 mm, Width: 21 mm, Depth: 48.7 mm, Basic material: Brass, untreated, silver
Qty.	1 ST	

## KTB MH 504020 S4EO

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

Type	PEBZ M10 KTB S4 SET	Version
Order No.	<a href="#">1192690000</a>	Klippon TB (Terminal Box), Earthing stud, Miscellaneous, Height: 21
GTIN (EAN)	4032248974658	mm, Width: 21 mm, Depth: 48.7 mm, Basic material: Stainless steel
Qty.	1 ST	1.4404 (316L), untreated, silver

## TS 20



Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

## Terminal rails

The mounting rails are available in two sizes for mounting DIN rails (e.g. electronics, terminals) components in the enclosures.

## General ordering data

Type	TS20/CX10 ST ZN 5040 HOR	Version
Order No.	<a href="#">8000117052</a>	Klippon TB (Terminal Box), Enclosures, with slot, Height: 20 mm,
GTIN (EAN)	4099986829916	Width: 366 mm, Depth: 10 mm, Basic material: Steel, galvanized,
Qty.	20 ST	silver
Type	TS20/CX10 ST ZN 5040 VER	Version
Order No.	<a href="#">8000117039</a>	Klippon TB (Terminal Box), Enclosures, straight, Height: 20 mm,
GTIN (EAN)	4099986829817	Width: 468 mm, Depth: 10 mm, Basic material: Steel, galvanized,
Qty.	20 ST	silver

## Depth 15 mm



Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

## Terminal rails

The mounting rails are available in two sizes for mounting DIN rails (e.g. electronics, terminals) components in the enclosures.

## General ordering data

Type	TS35X15 ST KTB5040 HOR	Version
Order No.	<a href="#">8000116372</a>	Klippon TB (Terminal Box), Enclosures, without slot, Height: 35 mm,
GTIN (EAN)	4099986820807	Width: 345 mm, Depth: 15 mm, Basic material: Steel, galvanic zinc plated and passivated, silver
Qty.	20 ST	
Type	TS35X15 ST KTB5040 VER	Version
Order No.	<a href="#">8000116354</a>	Klippon TB (Terminal Box), Enclosures, without slot, Height: 35 mm,
GTIN (EAN)	4099986820708	Width: 453 mm, Depth: 15 mm, Basic material: Steel, galvanic zinc plated and passivated, silver
Qty.	20 ST	

## KTB MH 504020 S4EO

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Depth 7.5 mm



Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

## Terminal rails

The mounting rails are available in two sizes for mounting DIN rails (e.g. electronics, terminals) components in the enclosures.

## General ordering data

Type	TS35X7.5 ST KTB5040 HOR	Version
Order No.	<a href="#">8000116112</a>	Klippon TB (Terminal Box), Enclosures, without slot, Height: 35 mm,
GTIN (EAN)	4099986820593	Width: 345 mm, Depth: 7.5 mm, Basic material: Steel, galvanic zinc plated and passivated, silver
Qty.	20 ST	
Type	TS35X7.5 ST KTB5040 VER	Version
Order No.	<a href="#">8000116102</a>	Klippon TB (Terminal Box), Enclosures, without slot, Height: 35 mm,
GTIN (EAN)	4099986820487	Width: 453 mm, Depth: 7.5 mm, Basic material: Steel, galvanic zinc plated and passivated, silver
Qty.	20 ST	

## Mounting plates



Mounting plates, with and without hole patterns, for longitudinal and transverse mounting of DIN mounting rails or components directly onto the mounting plate.

## General ordering data

Type	GFSC M5X10 TX20 SET	Version
Order No.	<a href="#">1274150000</a>	Klippon EB (Essential Box), Mounting screw, Height: 13.3 mm, Width:
GTIN (EAN)	4050118063820	8.5 mm, Depth: 8.5 mm, Basic material: Steel, galvanized, galvanic zinc plated and passivated, silver
Qty.	1 ST	

## KTB MH 504020 S4EO

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Installation material



Integrate, expand and customise - the perfect supplement to every application

The fully structured range of system accessories for the new Klippon® TB enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application.

## Mounting hardware kits

Mounting hardware kits are available for quick and easy installation of type label holders, document holders and rain hoods.

The label fastening set – SD is required to install a plastic (Trafolyte) ID or type label. With the aid of this set can you mount the ID or type label directly on the enclosure cover. The label fastening set has been specially developed for this purpose. Only by using this fastening set can you ensure that there will be no leaks into the enclosure or damage to the label.

The universal fastening set – TPSD has been developed to enable secure and quick installation of type label holders, rain covers or document holders, for example. By using this fastening set, the risk of leaks can be minimised, if not avoided.

## General ordering data

Type	FKSC M6X8 D9/SW3	Version
Order No.	<a href="#">0642600000</a>	Klippon TB (Terminal Box), Mounting screw, Basic material: Steel
GTIN (EAN)	4008190058258	
Qty.	50 ST	