

## KTB MH 625020 S4E0

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Similar to illustration



The Klippon® TB enclosure range provides excellent performance characteristics, even under the most difficult environmental conditions. In addition, it complies with the stricter requirements of potentially explosive atmospheres found specifically in the process or power generation industries. The Klippon® TB MH enclosure range offers further improvements to a product line that is already successfully leading the market.

The Klippon® TB MH enclosure range has the following advantages:

- Available in 22 sizes and 3 standard depths
- Equipped with up to 4 gland plates
- The gasket is protected against compression
- Completely removable padlock tab
- Cover lock outside the sealed zone
- Improved temperature performance
- IP66/IP67 protection
- Completely removable lid – without a tool
- Earthing stud in the cover and base of the enclosure
- Welded mounting feet
- International approvals

### General ordering data

|            |  |
|------------|--|
| Version    | Klippon TB MH (Terminal Box - Multi Hinge), Empty enclosure, stainless steel enclosure, Height: 620 mm, Width: 508 mm, Depth: 200 mm, Basic material: Stainless steel 1.4404 (316L), electropolished, silver |
| Order No.  | <a href="#">8000108858</a>   |
| Type       | KTB MH 625020 S4E0   |
| GTIN (EAN) | 4099986754898  |
| Qty.       | 1 items  |

**KTB MH 625020 S4E0**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

|            |         |                 |              |
|------------|---------|-----------------|--------------|
| Depth      | 200 mm  | Depth (inches)  | 7.874 inch   |
| Height     | 620 mm  | Height (inches) | 24.4094 inch |
| Width      | 508 mm  | Width (inches)  | 20 inch      |
| Net weight | 17150 g |                 |              |

**Temperatures**

|                       |                 |                                  |   |
|-----------------------|-----------------|----------------------------------|---|
| Operating temperature | -60 °C...135 °C | Note: room temperature (service) | Limited to IP66 protection when used in temperatures greater than 105 °C. |
|-----------------------|-----------------|----------------------------------|---|

**Environmental Product Compliance**

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status               | Compliant with exemption             |
| RoHS Exemption (if applicable/known) | 6c                                   |
| REACH SVHC                           | Lead 7439-92-1                       |
| SCIP                                 | 64dfc213-93f0-4c79-8ffa-c97fa9dcb873 |

**Cable glands, left**

|     |    |     |    |
|-----|----|-----|----|
| M63 | 5  | M75 | 0  |
| M12 | 75 | M50 | 6  |
| M16 | 60 | M32 | 10 |
| M25 | 26 | M20 | 32 |
| M40 | 8  |     |    |

**Cable glands, right**

|     |    |     |    |
|-----|----|-----|----|
| M25 | 26 | M63 | 5  |
| M75 | 0  | M16 | 60 |
| M40 | 8  | M50 | 6  |
| M32 | 10 | M20 | 32 |
| M12 | 75 |     |    |

**Cable glands, top/bottom**

|     |    |     |    |
|-----|----|-----|----|
| M20 | 28 | M12 | 66 |
| M63 | 4  | M40 | 7  |
| M32 | 9  | M25 | 22 |
| M50 | 6  | M75 | 0  |
| M16 | 30 |     |    |

## KTB MH 625020 S4E0

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

### Certificate numbers enclosure

|   |                             |  |                           |
|---|-----------------------------|--|---------------------------|
| Certificate No. UL Haz.Loc.               | E223792                     | Declaration of Conformatiy No. (DoC LVD) | DE PS261X 160412 001ISS03 |
| Certificate No. UL Ord.Loc.               | E243298                     | Certificate No. UL 508A                  | E223801                   |
| Attestation of Conformatiy No. (AoC)      | DE PS261X 160309 001ISS06   | Certificate No. UL Terminal Box          | E223792                   |
| Certificate no. empty enclosure (INMETRO) | LMP 21.0016U                | Certificate no. Terminal Box (ATEX)      | IBExU14ATEX1050           |
| Certificate no. empty enclosure (ATEX)    | IBExU14ATEX1028 U           | Certificate no. Terminal Box (INMETRO)   | LMP 21.0017               |
| Certificate no. Terminal Box (IECEX)      | IECEXIBE14.0013             | Certificate no. empty enclosure (IECEX)  | IECEX IBE 14.0004U        |
| Approval conditions                       | ATEX, IECEX, INMETRO, cULus |  |                           |

### General information

|                                 |   |                               |   |
|---------------------------------|---|-------------------------------|---|
| Material thickness of cover     | 1.5 mm  | Material thickness of flange  | 3 mm  |
| Material thickness of enclosure | 1.5 mm  | Silicone                      | Yes   |
| Operating temperature, max.     | 135 °C  | Operating temperature, min.   | -60 °C  |
| Lid attachment                  | 4 hinges and M6 hex-head slotted screws SW10  | Standards                     | DIN EN 62208 - Empty enclosure standard, DIN EN 61373 Class 1B**, DIN EN 15085-2, EN 60079-0, EN 60079-7, EN 60079-31, IEC 60079-0, IEC 60079-7, IEC 60079-31 |
| Surface finish                  | electropolished   | Impact resistance             | 10 J version standard, 7 joules in acc. with IEC 60079-0  |
| Protection degree               | IP66, IP67  | Basic material                | Stainless steel 1.4404 (316L)   |
| Seal material                   | Silicone  | Torque for lid screws         | 2.5 Nm  |
| Enclosure attachment            | 4 welded-on mounting feet with 11 mm holes (2 slotted feet and 2 cross-shaped feet) | Seal material of cover        | Silicone  |
| Note: protection class          | If used in temperature ranges above 105 °C, IP protection is limited to IP 66.      | Seal material of flange plate | Silicone  |
| Protection class (UL)           | Type 3, Type 4X, Type 12  | Number of lid screws          | 6   |
| Opening angle lid               | 130.00 °  | Flange plate                  | No  |
| Lid                             | Yes   | Position PE bolts             | Enclosure side C  |

### Housing earth

|                            |  |                            |   |
|----------------------------|--|----------------------------|---|
| Earth, enclosure, cover    | Welded-on M6 stainless-steel earth stud in enclosure body and lid. | Earth, enclosure, external | Continuous M10 earth stud in body enclosure |
| Earth, enclosure, internal | Welded-on M6 stainless-steel earth stud in enclosure body and lid. |                            |   |

### horizontal assembly

|                             |      |                 |      |
|-----------------------------|------|-----------------|------|
| WDU 10 / ZDU 10             | 4x38 | WDU 16 / ZDU 16 | 3x32 |
| WDU 2,5 / ZDU 2,5 / IDU 2,5 | 5x78 | WDU 35 / ZDU 35 | 2x24 |
| WDU 4 / ZDU 4               | 5x65 | WDU 6 / ZDU 6   | 4x48 |

**KTB MH 625020 S4E0**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****vertical assembly**

|                             |       |                 |      |
|-----------------------------|-------|-----------------|------|
| WDU 10 / ZDU 10             | 3x49  | WDU 16 / ZDU 16 | 2x42 |
| WDU 2,5 / ZDU 2,5 / IDU 2,5 | 4x101 | WDU 35 / ZDU 35 | 2x31 |
| WDU 4 / ZDU 4               | 3x83  | WDU 6 / ZDU 6   | 3x62 |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002503    | ETIM 9.0    | EC002503    |
| ETIM 10.0   | EC002503    | ECLASS 14.0 | 27-18-05-02 |
| ECLASS 15.0 | 27-18-05-02 |             |             |