

MBGE ADPT IPC621,6 POLE TOP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Adapters for migration – IPC 621.

The front adapters with pre-assembled cables provide a safe migration from the IPC 621 cards to other PLC/DCS systems or the u-remote modules from Weidmüller.

General ordering data

Order No.	8000109239
Type	MBGE ADPT IPC621,6 POLE TOP
GTIN (EAN)	4099986623569
Qty.	1 items

MBGE ADPT IPC621,6 POLE TOP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data
Dimensions and weights

Depth	56.7 mm	Depth (inches)	2.2323 inch
Height	106 mm	Height (inches)	4.1732 inch
Width	30.6 mm	Width (inches)	1.2047 inch
Net weight	0.5 g		

Temperatures

Storage temperature	-20...70 °C	Operating temperature	-20...50 °C
---------------------	-------------	-----------------------	-------------

Rated data UL

Storage temperature UL, max.	70 °C	Operating temperature UL, min.	-20 °C
Operating temperature UL, max.	50 °C	Storage temperature UL, min.	-20 °C
Rated current I _{max}	20 A	Rated voltage UN	250 V

Connection data

Number of poles (control side)	6-pole	Connection (field side)	IPC 621 6 pole connector
--------------------------------	--------	-------------------------	--------------------------

Connection data

Connection (field side)	IPC 621 6 pole connector	Connection to PLC	New PLC terminal block or hardwired
Number of poles (field side)	6 P		

Ratings data

Operating voltage	250 V	Max. current per channel	6 A
Total operating current	20 A		

Insulation coordination (EN50178)

Rated insulation voltage	300 V	Surge voltage category	II
Pollution severity level	2	Pulse voltage test (1,2/50µs)	2.5 kV
Insulation test voltage AC	1.8 kV		

Classifications

ETIM 8.0	EC002584	ETIM 9.0	EC002584
ETIM 10.0	EC002584	ECLASS 14.0	27-33-02-92
ECLASS 15.0	27-33-02-92		

MBGE ADPT IPC621,6 POLE TOP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

