

KTB QL 626215 S4E0**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The Klippon® TB enclosure range provides excellent performance characteristics, even under the most difficult environmental conditions. In addition, it complies with the stricter requirements of potentially explosive atmospheres found specifically in the process or power generation industries. The Klippon® TB QL enclosure range offers further improvements to a product line that is already successfully leading the market.

The Klippon® TB QL enclosure series features the following advantages:

- Available in 19 sizes and 3 standard depths
- Equipped with up to 4 gland plates
- The gasket is protected against compression
- Quick-locking cover, comes with a slot as standard
- Improved temperature performance
- IP66 protection
- Earthing stud in the cover and base of the enclosure
- Welded mounting feet
- International approvals

General ordering data

Version	Klippon TB QL (Terminal Box - Quarter Lock), Empty enclosure, Height: 620 mm, Width: 620 mm, Depth: 150 mm, Basic material: Stainless steel 1.4404 (316L), electropolished, silver
Order No.	8000109914
Type	KTB QL 626215 S4E0
GTIN (EAN)	4099986760097
Qty.	1 items

KTB QL 626215 S4E0

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	150 mm	Depth (inches)	5.9055 inch
Height	620 mm	Height (inches)	24.4094 inch
Width	620 mm	Width (inches)	24.4094 inch
Net weight	22583.17 g		

Temperatures

Operating temperature	-60 °C...135 °C	Note: room temperature (service)	Limited to IP66 protection when used in temperatures greater than 105 °C.
-----------------------	-----------------	----------------------------------	---

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	64dfc213-93f0-4c79-8ffa-c97fa9dcb873

Cable glands, left

M63	5	M75	0
M12	75	M50	6
M16	60	M32	9
M25	26	M20	32
M40	8		

Cable glands, right

M25	26	M63	5
M75	0	M16	60
M40	8	M50	6
M32	9	M20	32
M12	75		

Cable glands, top/bottom

M20	34	M12	84
M63	5	M40	9
M32	11	M25	28
M50	7	M75	0
M16	63		

KTB QL 626215 S4E0

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Certificate numbers enclosure

Certificate No. UL Haz.Loc.	E223792	Declaration of Conformity No. (DoC LVD)	DE PS261X 160412 001ISS03
Certificate No. UL Ord.Loc.	E243298	Certificate No. UL 508A	E223801
Attestation of Conformity No. (AoC)	DE PS261X 160309 001ISS06	Certificate No. UL Terminal Box	E223792
Certificate no. empty enclosure (INMETRO)	LMP 21.0016U	Certificate no. Terminal Box (ATEX)	IBExU14ATEX1050
Certificate no. empty enclosure (ATEX)	IBExU14ATEX1028 U	Certificate no. Terminal Box (INMETRO)	LMP 21.0017
Certificate no. Terminal Box (IECEX)	IECEXIBE14.0013	Certificate no. empty enclosure (IECEX)	IECEX IBE 14.0004U
Approval conditions	ATEX, IECEX, INMETRO, cULus		

General information

Material thickness of cover	1.5 mm	Material thickness of flange	3 mm
Material thickness of enclosure	1.5 mm	Silicone	Yes
Operating temperature, max.	135 °C	Operating temperature, min.	-60 °C
Lid attachment	4 hinges and M6 hex-head slotted screws SW10	Standards	DIN EN 62208 - Empty enclosure standard, DIN EN 61373 Class 1B**, DIN EN 15085-2, EN 60079-0, EN 60079-7, EN 60079-31, IEC 60079-0, IEC 60079-7, IEC 60079-31
Surface finish	electropolished	Impact resistance	10 J version standard, 7 joules in acc. with IEC 60079-0
Protection degree	IP66, IP67	Basic material	Stainless steel 1.4404 (316L)
Seal material	Silicone	Integral fixing	4, 6 or 9 stud bolts M6 inner (female) thread
Seal material of cover	Silicone	Note: protection class	If used in temperature ranges above 105 °C, IP protection is limited to IP 66.
Flange plate mounting	M6 hexagonal head screws 10 SW	Seal material of flange plate	Silicone
Protection class (UL)	Type 3, Type 4X, Type 12	Opening angle lid	130.00 °
Flange plate	No	Lid	Yes
Position PE bolts	Enclosure side C	Areas of use	Explosive risk zone, Process industry, Oil and gas industry, Chemical industry, Offshore, Onshore

Housing earth

Earth, enclosure, cover	Welded-on M6 stainless-steel earth stud in enclosure body and lid.	Earth, enclosure, external	Continuous M10 earth stud in body enclosure
-------------------------	--	----------------------------	---

horizontal assembly

WDU 10 / ZDU 10	4x49	WDU 16 / ZDU 16	3x42
WDU 2,5 / ZDU 2,5 / IDU 2,5	5x101	WDU 35 / ZDU 35	2x31
WDU 4 / ZDU 4	5x83	WDU 6 / ZDU 6	4x62

Technical data**vertical assembly**

WDU 10 / ZDU 10	4x49	WDU 16 / ZDU 16	3x42
WDU 2,5 / ZDU 2,5 / IDU 2,5	5x101	WDU 35 / ZDU 35	2x31
WDU 4 / ZDU 4	5x83	WDU 6 / ZDU 6	4x62

Classifications

ETIM 8.0	EC002503	ETIM 9.0	EC002503
ETIM 10.0	EC002503	ECLASS 14.0	27-18-05-02
ECLASS 15.0	27-18-05-02		