


**DKZ DK5 24VDC 10-100MS**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Product image**



Similar to illustration

**General ordering data**

Version	DK-SERIES, Time module, Pull-in delay, , Number of contacts: 1, NO contact, Rated control voltage: 24 V DC $\pm 20\%$ , Continuous current: 0.1 A, Screw connection
Order No.	<a href="#">8228680000</a>
Type	DKZ DK5 24VDC 10-100MS
GTIN (EAN)	4008190193911
Qty.	10 items
Delivery status	Discontinued
Available until	2018-12-31T00:00:00+01:00

## DKZ DK5 24VDC 10-100MS

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

## Dimensions and weights

Depth	62 mm	Depth (inches)	2.4409 inch
Height	77 mm	Height (inches)	3.0315 inch
Width	6 mm	Width (inches)	0.2362 inch
Net weight	22.3 g		

## Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-25 °C...50
Humidity	40 °C / 93 % rel. humidity, no condensation		

## Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	No SVHC above 0.1 wt%

## Control side

Rated control voltage	24 V DC $\pm$ 20 %	Rated current DC	Approx. 12 mA
Power rating	290 mW	Time ranges	0.01 s - 0.1 s

## Load side

Continuous current	0.1 A	Max. switching current	100 mA
Max. switching voltage, DC	48 V	Switch-on delay	10...100 ms (adjustable)
Contact type	1 NO contact (Transistor)		

## General data

Version	Pull-in delay	Mounting rail	TS 32, TS 35
Test button available	No	Mechanical switch position indicator	No
Open sides	right	Colour	beige

## Insulation coordination

Rated voltage	300 V	Pollution severity	2
Surge voltage category	IV	Creepage and clearance distance input	$\geq$ 5.5 mm
Dielectric strength, Input/Output	4 kVeff	output	
		Impulse withstand voltage	6 kV

## Connection data

Wire connection method	Screw connection	Clamping range, rated connection	4 mm <sup>2</sup>
Clamping range, min.	0.5 mm <sup>2</sup>	Clamping range, max.	4 mm <sup>2</sup>
Wire connection cross section AWG, min.	AWG 22	Wire connection cross section AWG, max.	AWG 12
Wire cross-section, solid, min.	0.5 mm <sup>2</sup>	Wire cross-section, solid, max.	4 mm <sup>2</sup>

## DKZ DK5 24VDC 10-100MS

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

Wire connection cross section, finely stranded, min.	0.5 mm <sup>2</sup>	Wire connection cross section, finely stranded, max.	4 mm <sup>2</sup>
Blade size	0.4 x 2.5 mm		

## Classifications

ETIM 8.0	EC001439	ETIM 9.0	EC001439
ETIM 10.0	EC001439	ECLASS 14.0	27-37-16-05
ECLASS 15.0	27-37-16-05		