


DK NOR 35 24VDC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Only remaining stock
 available

Similar to illustration


Logic functions AND, NAND, OR and NOR in modular terminal format with a rated cross-section of 4 mm². They each have five inputs which are fed – with logic gating – via a 24 V/20 mA PNP output. The logic components can be used for many applications involving the coupling of digital sensor/actuator signals with automation devices.

General ordering data

Version	Function component, NOR Gate
Order No.	8248330000
Type	DK NOR 35 24VDC
GTIN (EAN)	4008 1904067 14
Qty.	5 items

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	65 mm	Depth (inches)	2.5591 inch
Height	57 mm	Height (inches)	2.2441 inch
Width	12 mm	Width (inches)	0.4724 inch
Length	65 mm	Length (inches)	2.5591 inch
Net weight	29 g		

Temperatures

Storage temperature	-40 °C...60 °C	Operating temperature	0 °C...50 °C
Humidity	40 °C / 93 % rel. humidity, no condensation		

Probability of failure

SIL in compliance with IEC 61508 None

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	7a, 7cI
REACH SVHC	Lead 7439-92-1
SCIP	35d83707-6a3b-45b5-b9f8-6ba8184c863e

Functions

Logic function NOR

General data

Protection degree	IP20	Supply voltage	24...30 V DC
Current consumption	<5 mA	Mounting rail	TS 35
Power consumption	30 mW	Nominal power consumption	0.03 VA

Insulation coordination

Galvanic isolation Without isolation

Input

Number inputs	5	Rated input level	24 V DC= High, 0 V = Low
Rated voltage	Max. 30 V	Input current	Approx. 1.5 mA per input (24 V)
Pulse duration	≥ 50 µs		

DK NOR 35 24VDC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Output

Number of outputs	8-bit (1-bit signed)	Load impedance current	≤ 600 Ω
Output level	PNP, Ub-1.8 V	Switching thresholds	High <15 V, low <9 V
Output current	max. 20 mA		

General data

Open sides	right	Type of connection	Screw connection
Humidity	40 °C / 93 % rel. humidity, no condensation	Input/Output	Logic module
Supply voltage	24...30 V DC	Galvanic isolation	Without isolation
Current consumption	<5 mA	Mounting rail	TS 35
Power consumption	30 mW		

Insulation coordination

Standards	EN 61000-6-2:2005, EN 61000-6-3:2007/ A1:2011, EN 61000-6-4:2007 + A1:2011, CE
-----------	--

Connection data

Type of connection	Screw connection	Clamping range, rated connection	4 mm ²
Clamping range, min.	0.5 mm ²	Clamping range, max.	4 mm ²

Classifications

ETIM 8.0	EC001417	ETIM 9.0	EC001417
ETIM 10.0	EC001417	ECLASS 14.0	27-24-22-16
ECLASS 15.0	27-24-22-16		

