


**PV 216SXFXCXXVXO1TA3PA15LWW**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com



**Intelligent product in a compact size**

PV retrofit monitoring boxes make it possible to obtain data at string level in PV systems with existing, unmonitored PV-DC generator combiner boxes. All without additional work such as trenching and cabling. Integrated power monitoring provided by our Solar SMS monitoring system allows to do the right surveillance of the PV site to guarantee the best performance of the system.

Additionally, our PV monitoring boxes fulfill the standard IEC/EN 61439-2:2020 to guarantee a high reliability of the supplied units.

**General ordering data**

Version	Photovoltaics, Assembled enclosure, 1500 V, WM4C, for wall mounting, Landscape, Digital signals, Monitoring components, Current monitoring, Voltage monitoring, Temperature monitoring, 16-channel
Order No.	<a href="#">8000112718</a>
Type	PV 216SXFXCXXVXO1TA3PA15LWW
GTIN (EAN)	4099986868601
Qty.	1 items

**PV 216SXFXCXXVXO1TA3PA15LWW**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

Depth	210 mm	Depth (inches)	8.2677 inch
Height	302 mm	Height (inches)	11.8897 inch
Width	558 mm	Width (inches)	21.9685 inch
Net weight	6150.1 g		

**Temperatures**

Ambient temperature	-20 °C...45 °C	Operating temperature	-20°C to +45 °C
---------------------	----------------	-----------------------	-----------------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6a1, 7a, 7c1
REACH SVHC	Lead 7439-92-1
SCIP	1d28ada4-1634-4382-8635-45f6353a6574

**DC electrical properties**

Rated voltage	1500 V	Surge protection DC side	No surge protection
---------------	--------	--------------------------	---------------------

**DC inputs**

Fuse protection	No	Number of DC inputs	16
Connection type, DC input cable	WM4 C field connector	Connection DC input cable (-)	WM4 C field connector
Number of inputs	16	Number of conduit inlets	0
Connection DC input cable (+)	WM4 C field connector	Fuse type	Neither fuse cartridge nor holder
Type of fuse	Neither fuse cartridge nor holder		

**DC outputs**

DC output cable connection	WM4 C field connector	Connection type, DC output cable	WM4 C field connector
Number of DC outputs	16		

**DC string monitoring**

Supply	Self-powered	Monitoring function	Solar SMS, Output voltage, current, temperature
Voltage monitoring	Solar SMS	Temperature monitoring	Solar SMS
Current monitoring	Solar SMS		

**Housing**

Type of mounting	Wall mounting	Protection degree	IP65
------------------	---------------	-------------------	------

## PV 216SFXCXXVXO1TA3PA15LWW

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Norms and standards

Standards	EN 61439-2:2020, IEC 61439-2 ed 3.0
-----------	-------------------------------------

### Guarantee

Time interval	5 years
---------------	---------

### Classifications

ETIM 8.0	EC003857	ETIM 9.0	EC003857
ETIM 10.0	EC003857	ECLASS 14.0	22-57-02-92
ECLASS 15.0	22-57-02-92		

PV 216SXFXCXXVXO1TA3PA15LWW

Weidmüller Interface GmbH & Co. KG  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

Drawings

www.weidmueller.com

