

**KTB MOPL 3535 S2N H****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Similar to illustration**

Abbildung ähnlich

Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

**Mounting plates**

Mounting plates, with and without hole patterns, for longitudinal and transverse mounting of DIN mounting rails or components directly onto the mounting plate.

**General ordering data**

Version	Klippon TB (Terminal Box), Mounting plate, Height: 259 mm, Width: 289 mm, Depth: 1.5 mm, Basic material: Stainless steel 1.4301 (304), untreated, silver
Order No.	<a href="#">8000115903</a>
Type	KTB MOPL 3535 S2N H
GTIN (EAN)	409998678292 1
Qty.	1 items

**KTB MOPL 3535 S2N H**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

Depth	1.5 mm	Depth (inches)	0.0591 inch
Height	259 mm	Height (inches)	10.1968 inch
Width	289 mm	Width (inches)	11.3779 inch
Mounting dimension - height	279 mm	Mounting dimension - width	273 mm
Net weight	980 g		

**Temperatures**

Operating temperature

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General information**

Material thickness of flange	3 mm	Material thickness of enclosure	1.5 mm
Material thickness	1.5 mm	Installation advice	Mounting plate
Surface finish	untreated	Protection degree	with corresponding enclosure
Basic material	Stainless steel 1.4301 (304)		

**General information on accessories**

Material thickness	1.5 mm	Surface finish	untreated
Basic material	Stainless steel 1.4301 (304)	Mounting dimension - width	273 mm
Mounting dimension - height	279 mm		

**Classifications**

ETIM 8.0	EC000213	ETIM 9.0	EC000213
ETIM 10.0	EC000213	ECLASS 14.0	27-40-06-39
ECLASS 15.0	27-40-06-39		