

## SAIBGS-M-4A-6/8-M12

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly.

Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems.

The screw connection can be used in a wide range of applications. With this technology the conductor, optionally with wire-end ferrules, can be plugged into connection elements and secured with a screw. It is the classic, cheapest form of connection technology that also supports multi-conductor connections.

### General ordering data

Version	Field attachable connector, M12
Order No.	<a href="#">8426220000</a>
Type	SAIBGS-M-4A-6/8-M12
GTIN (EAN)	4032248036516
Qty.	1 items

## SAIBGS-M-4A-6/8-M12

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E307231

### Dimensions and weights

Net weight 45.41 g

### Environmental Product Compliance

RoHS Compliance Status Compliant with exemption

RoHS Exemption (if applicable/known) 6c

REACH SVHC Lead 7439-92-1, Imidazolidine-2-thione 96-45-7

SCIP 0a173d67-76ea-4f49-a7f9-34c254e699e8

### Technical data customisable plug-in connectors

Number of poles	4	Coding	A-coded
Contact surface	Gold-plated	Type of connection	Screw connection
Housing main material	CuZn	Insulation resistance	1012 Ω
Cable diameter, max.	8 mm	Cable diameter, min.	6 mm
Conductor cross-section, max.	0.75 mm <sup>2</sup>	Conductor cross-section, min.	0.14 mm <sup>2</sup>
Nominal voltage	250 V	Nominal current	4 A
Protection degree	IP67	Pollution severity	3
Gender of contact	Female	Shield connection	Yes
Threaded ring material	Diecast zinc	Temperature range of housing	-40 ... +85 °C

### General Info

Number of poles	4	Connection 1	M12
Connection 2	Screw	UL 94 flammability rating	V-2
Housing main material	CuZn	Connection thread	M12
Contact surface	Gold-plated	Protection degree	IP67

### Standards

Connector standard IEC 61076-2-101

### Classifications

ETIM 8.0	EC002635	ETIM 9.0	EC002635
ETIM 10.0	EC002635	ECLASS 14.0	27-44-01-16
ECLASS 15.0	27-44-01-16		

**Pole scheme**

