

MBGE ADPT, ET200M, 40 POLE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Adapters for migration – Siemens ET200M/S7-300.
The front adapters with pre-assembled cables provide a safe migration from the ET200M/S7-300 cards to other PLC systems or the u-remote modules from Weidmüller.

General ordering data

Order No.	8000125284
Type	MBGE ADPT, ET200M, 40 POLE
GTIN (EAN)	4099986881587
Qty.	1 items

MBGE ADPT, ET200M, 40 POLE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	61.3 mm	Depth (inches)	2.4134 inch
Height	127 mm	Height (inches)	5 inch
Width	40.6 mm	Width (inches)	1.5984 inch
Net weight	122.5 g		

Temperatures

Storage temperature	-20...70 °C	Operating temperature	-20...50 °C
---------------------	-------------	-----------------------	-------------

Rated data UL

Storage temperature UL, max.	70 °C	Operating temperature UL, min.	-20 °C
Operating temperature UL, max.	50 °C	Storage temperature UL, min.	-20 °C
Rated current I _{max}	40 A	Rated voltage UN	250 V

Connection data

Number of poles (control side)	40-pole	Connection (field side)	Siemens ET200M / S7-300 40-pole connector
--------------------------------	---------	-------------------------	---

Connection data

Connection (field side)	Siemens ET200M / S7-300 40-pole connector	Connection to PLC	New PLC terminal block or hardwired
Number of poles (field side)	40 P		

Ratings data

Operating voltage	250 V	Max. current per channel	5.5 A
Total operating current	40 A		

Insulation coordination (EN50178)

Surge voltage category	II	Pollution severity level	2
Pulse voltage test (1,2/50µs)	2.5 kV	Insulation test voltage AC	1.8 kV

Classifications

ETIM 8.0	EC002584	ETIM 9.0	EC002584
ETIM 10.0	EC002584	ECLASS 14.0	27-33-02-92
ECLASS 15.0	27-33-02-92		

MBGE ADPT, ET200M, 40 POLE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

