

PV 212S0F3CXXV100TXPX15LWW

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



Standard portfolio for 1 MPPT string inverters
 Protect and monitor strings in solar parks with string inverters with 1 MPPT.
 The following PV DC combiner box portfolio is meant to be used with string inverters with one Maximum Power Point Tracker (MPPT) in order to bundle, protect and isolate the number of strings these inverters use. 1 MPPT

General ordering data

| | |
|------------|--|
| Version | Photovoltaics, Assembled enclosure, Combiner Box, 1500 V, With fuse holder, Surge protection II, Cable gland, for wall mounting, Switch disconnect, Landscape, String Inverter |
| Order No. | 8000125423 |
| Type | PV 212S0F3CXXV100TXPX15LWW |
| GTIN (EAN) | 4099986893146 |
| Qty. | 1 items |

PV 212S0F3CXXV100TXPX15LWW

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

| | | | |
|------------|---------|-----------------|--------------|
| Depth | 300 mm | Depth (inches) | 11.811 inch |
| Height | 636 mm | Height (inches) | 25.0393 inch |
| Width | 847 mm | Width (inches) | 33.3464 inch |
| Net weight | 30000 g | | |

Temperatures

| | | | |
|---------------------|----------------|-----------------------|-----------------|
| Ambient temperature | -20 °C...45 °C | Operating temperature | -20°C to +45 °C |
|---------------------|----------------|-----------------------|-----------------|

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 1d28ada4-1634-4382-8635-45f6353a6574 |

DC electrical properties

| | | | |
|---------------|---------------------|--------------------------|------------------------------------|
| Rated voltage | 1500 V | Switching capacity | 400 A (DC21B 1500 V) |
| Earthing | Directly at the VPU | Surge protection DC side | 1500 V type II with remote contact |

DC inputs

| | | | |
|--------------------------------------|------------------------------------|-------------------------|-----------------|
| Cartridge fuse | 10 x 85 mm | | |
| Fuse protection | 15 A, 16 A, 20 A, 25 A, 30 A, 32 A | | |
| Number of DC inputs | 12 | | |
| Fused poles of string | +/- | | |
| Connection type, DC input cable | Cable gland | | |
| Connection DC input cable (-) | Screw connection | | |
| Fuse-link standard | gPV (EN 60269-6) | | |
| Amount of maximum power points (MPP) | 1 | | |
| Functional earth connector | Cable entry | Number of cable entries | 1 |
| | | Cable diameter, min. | 6 mm |
| | | Cable diameter, max. | 12 mm |
| DC Input + & - | Wire connection | Type of connection | M20 Cable gland |
| | Wire connection | Type of connection | M16 Cable gland |
| | Cable entry | Number of cable entries | 24 |
| | | Cable diameter, min. | 5 mm |
| | | Cable diameter, max. | 10 mm |
| Connection DC input cable (+) | Screw connection | | |
| Fuse type | Empty fuse holder | | |
| Position of the fuses | positive and negative inputs | | |
| Type of fuse | Empty fuse holder | | |

PV 212S0F3CXXV100TXPX15LWW

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

DC outputs

| | | | | | |
|---|-----------------|--------------------------|---------------------|-----------------------------|--|
| DC output cable connection | | | | M10 bolt and nut connection | |
| Connection type, DC output cable | | | | Screw terminal connectors | |
| DC Output + & - | Wire connection | Type of connection | M40 Cable gland | | |
| | | Wire cross-section, min. | 150 mm ² | | |
| | | Wire cross-section, max. | 400 mm ² | | |
| Number of DC outputs | | 2 | | | |
| Load circuit breaker with auxiliary contact | | No | | | |

DC string monitoring

| | | | | | |
|---------------------|---------------|--|--|--|--|
| Monitoring function | Non monitored | | | | |
|---------------------|---------------|--|--|--|--|

Housing

| | | | | | |
|------------------|---------------|-------------------|------|--|--|
| Type of mounting | Wall mounting | Protection degree | IP65 | | |
|------------------|---------------|-------------------|------|--|--|

Norms and standards

| | | | | | |
|-----------|-------------------------------------|--|--|--|--|
| Standards | EN 61439-2:2011, IEC 61439-2 ed 3.0 | | | | |
|-----------|-------------------------------------|--|--|--|--|

Guarantee

| | | | | | |
|---------------|---------|--|--|--|--|
| Time interval | 5 years | | | | |
|---------------|---------|--|--|--|--|

Classifications

| | | | | | |
|-------------|-------------|-------------|-------------|--|--|
| ETIM 8.0 | EC003857 | ETIM 9.0 | EC003857 | | |
| ETIM 10.0 | EC003857 | ECLASS 14.0 | 22-57-02-92 | | |
| ECLASS 15.0 | 22-57-02-92 | | | | |

PV 212S0F3CXXV100TXPX15LWW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com



PV 212S0F3CXXV100TXPX15LWW

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Drawings

www.weidmueller.com

Combiner Box Name Description

PV 2 24 S0 FX CXX VX OX TXPX 15 P F ES

PV 1: PV DC L0 Industrial
PV 2: PV DC L1 Industrial
PV 3: PV DC L2 Industrial

Number of inputs (01-36)

S0: Switch-disconnector

- S0 → Switch-disconnector (SW)
- S1 → Switch-disconnector with remote disconnection (SW RD)
- S2 → Molded Case Circuit Breaker (MCCB)
- S3 → Motorized switch-disconnector (SW M)
- S4 → Switch-disconnector with Contactor (SW K)
- SX → No Switch-disconnector needed (N/A)

FX: Fuses / Fuseholders position

- F0 → Fuses Both Poles
- F1 → Only Positive Fuses
- F2 → Only Negative Fuses
- F3 → Only Fuse Holders
- F4 → Only fuse holder in positive (+)
- F5 → Only fuse holder in negative (-)
- FX → No Fuse holders needed (N/A)

CXX: CIL Fuses Type → C 10/15/16/20/25/30/40/50/55/60/63/80 - (Example C10)

NXX: NH Fuses Type → N 40/50/63/80/100/125/160/200/250/315/355/400 - (Example N40)

CXX → N/A, NXX → N/A

VX: SPD Type

- V0 → SPD Class II / V1 → SPD Class I+II / V2 → SPD Class I
- VX → No SPD needed (N/A)

Country / Whole World

Floating: YES (F) / NO

P: Portrait
L: Landscape

10: 1000v
15: 1500v

TX: Monitoring Device

- TX → No monitoring (N/A)
- T2 → TC 16i+ (1kV or 1.5kV)
- T5 → TC 2x16i+
- T7 → TC 16iH
- T8 → Others
- T9 → Fronrich
- TA1 → Solar SMS (25A)
- TA2 → Solar SMS (50A)
- TA3 → Solar SMS LoRaWAN (25A)
- TA4 → Solar SMS LoRaWAN (50A)

PX: Power Supply for (TX)

- PX → No Power Supply Needed (N/A)
- P0 → Self-Powered (BKE)
- P1 → External Power Supply (PS ACDC)
- PA → Self-Powered (EE)

OX: Output type

- OX → No holes needed (N/A)
- O0 → Cable Gland
- O1 → WMAC
- O2 → MCA
- O3 → Multivia CG

