

**HDC KIT HE-QT 16.121 M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



HDC kits are standardized kits for assembling complete plug-in connectors.

The HDC kits normally consist of a male insert, a female insert, a plug housing, a bulkhead housing and a cable gland. Weidmüller offers a range of standard connector combinations with metric or PG cable entry threads.

With the SNAP IN connection, the conductor connection level is already open, and the stripped conductor can be simply inserted. In the end position, the patented clamping mechanism closes automatically.

**General ordering data**

Order No.	8000134357
Type	<a href="#">HDC KIT HE-QT 16.121 M</a>
GTIN (EAN)	4099987015530
Qty.	1 items

**HDC KIT HE-QT 16.121 M**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



**Dimensions and weights**

Net weight 587 g

**Temperatures**

Limit temperature -40 °C ... 100 °C

**Environmental Product Compliance**

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1, Potassium perfluorobutane sulfonate 29420-49-3
SCIP	bfb1c983-6f18-4ba4-8907-38aad6aee076

**General data**

Surface finish	Powder coating	Protection degree	IP65
Series	HE		

**Version**

Number of cable glands	1	Size of cable entries	M 25
Number of cable entry on top	1	Number of cable entry sideways	0
Type of connection	SNAP IN	Installation size	6
Sealing	NBR	BG	6

**General data**

Number of poles	16	Connection type PE	Screw connection
Installation size	6	Basic material	diecast aluminium
Series	HE	Rated voltage (DIN EN 61984)	500 V
Rated current (DIN EN 61984)	16 A	BG	6

**Version**

Blade size, slotted (screw connection)	SD 0.6 x 3.5	Wire connection cross section AWG, max.	AWG 16
Stripping length, rated connection	10 mm	Type of connection	SNAP IN
Installation size	6	Wire connection cross section AWG, min.	AWG 20
Wire cross-section, solid, max.	2.5 mm <sup>2</sup>	Wire cross-section, solid, min.	1 mm <sup>2</sup>
Wire connection cross section, finely stranded, max.	2.5 mm <sup>2</sup>	Wire connection cross section, finely stranded, min.	1 mm <sup>2</sup>
Conductor cross-section, max.	2.5 mm <sup>2</sup>	Conductor cross-section, min.	1 mm <sup>2</sup>
Surface finish	Powder coating	Basic material	diecast aluminium
BG	6		

**HDC KIT HE-QT 16.121 M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**

**Classifications**

ETIM 8.0	EC002943	ETIM 9.0	EC002943
ETIM 10.0	EC002943	ECLASS 14.0	27-44-02-92
ECLASS 15.0	27-44-02-92		

**HDC KIT HE-QT 16.121 M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Accessories**

[www.weidmueller.com](http://www.weidmueller.com)

**SPB**

Various accessories are available for our inserts. This includes coding elements for the inserts.

**General ordering data**

Type	SPB-M 3	Version	
Order No.	<a href="#">120360000</a>	Heavy-duty connectors, Accessories, Lock bolts	
GTIN (EAN)	4008190120047		
Qty.	100 ST		