Data sheet

# TS35X7.5 ST 120 K42

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Similar to illustration



Similar to illustration

The system accessories for the Klippon® K enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application.

- DIN Rails TS 35 and TS15
- Mounting plates
- Hinges
- Wall-mounted holder

Weidmüller can manufacture and supply this enclosure - according to customer specifications - fitted with all necessary terminals and cable glands.

### General ordering data

| | |
|---|---|
| Version | Rail, TS 35 x 7.5, Width: 120 mm, with slot, Steel, galvanic zinc plated and passivated |
| Order No. | 8000135673 |
| Type | TS35X7.5 ST 120 K42 |
| GTIN (EAN) | 4099987090070 |
| Qty. | 1 items |

# Data sheet

## TS35X7.5 ST 120 K42

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

# Technical data

### Approvals

| | |
|---|---|
| ROHS | Conform |

### Dimensions and weights

| | | | |
|---|---|---|---|
| Depth | 7.5 mm | Depth (inches) | 0.2953 inch |
| Height | 35 mm | Height (inches) | 1.378 inch |
| Width | 120 mm | Width (inches) | 4.7244 inch |
| Length | 120 mm | Length (inches) | 4.7244 inch |
| Net weight | 43 g | | |

### Temperatures

| | |
|---|---|
| Operating temperature | |

### Environmental Product Compliance

| | |
|---|---|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

### General information

| | | | |
|---|---|---|---|
| Material thickness | 1 mm | Installation advice | Direct mounting |
| Standards | DIN EN 60715 | Surface finish | galvanic zinc plated and passivated |
| Basic material | Steel | | |

### General information on accessories

| | | | |
|---|---|---|---|
| Material thickness | 1 mm | Surface finish | galvanic zinc plated and passivated |
| Basic material | Steel | | |

### Classifications

| | | | |
|---|---|---|---|
| ETIM 8.0 | EC001285 | ETIM 9.0 | EC001285 |
| ETIM 10.0 | EC001285 | ECLASS 14.0 | 27-40-06-02 |
| ECLASS 15.0 | 27-40-06-02 | | |