Data sheet

CRIKIT S 12VDC 1CO L/D UL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Version	, Number of contacts: 1, CO contact AgNi, Rated control voltage: 12 V DC, Continuous current: 16 A, Screw connection, Test button available: No
Order No.	8000158744
Type	CRIKIT S 12VDC 1CO L/D UL
GTIN (EAN)	4099987368230
Qty.	10 items

Data sheet

CRIKIT S 12VDC 1CO L/D UL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals	
UL File Number Search	UL Website
Certificate No. (cURus)	E223474

Dimensions and weights

Depth	72.8 mm	Depth (inches)	2.8661 inch
Height	80 mm	Height (inches)	3.1496 inch
Width	15.8 mm	Width (inches)	0.622 inch
Net weight	475.2 g		

Temperatures

Storage temperature		Ambient temperature	-20 °C...70 °C
Operating temperature			

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Rated data UL

Certificate No. (cURus)	E223474

Control side

Rated control voltage	12 V DC	Rated current DC	33.3 mA
Power rating	565 mW	Coil resistance	1440 Ω ± 10 %
Status indicator	Green LED	Protective circuit	Free-wheeling diode
Coil voltage of the replacement relay deviating from the rated control voltage	No	Coil voltage of the replacement relay	12 V DC

Load side

Rated switching voltage	250 V AC	Continuous current	16 A @ 1CO with bridged output wire connections; 12 A; @ 1CO without bridged output wire connections
Max. switching frequency at rated load	0.1 Hz	Switching voltage (AC), max.	250 V
Switching voltage (DC), max.	250 V	AC switching capacity (resistive), max.	4000
DC switching capacity (resistive), max.	384 W @ 24 V	Switch-on delay	≤ 12 ms
Switch-off delay	≤ 6 ms	Contact type	1 CO contact (AgNi)
Mechanical service life	3 x 107 switching cycles	Min. switching power	10 mA @ 12 V, 100 mA @ 5 V

General data

Operating altitude	≤ 2000 m, above sea level	
Mounting rail	TS 35	
Test button available	No	
Colour	black	
UL94 flammability rating component	Component	Socket

CRIKIT S 12VDC 1CO L/D UL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

	UL94 flammability rating	V-2	
	Component	Relay cover	
	UL94 flammability rating	V-2	

Insulation coordination

Surge voltage category	II	Dielectric strength for control side - load side	5 kVeff / 1min
Dielectric strength of neighbouring contacts	3 KVeff / 1 Min.	Dielectric strength to mounting rail	5 kVeff / 1 min
Impulse withstand voltage	4 kV (1.2/50 µs)	Protection degree	IP20

Further details of approvals / standards

Certificate No. (cURus)	E223474

Connection data

Wire connection method	Screw connection	Stripping length, rated connection	8 mm
Tightening torque, min.	0.7 Nm	Clamping range, rated connection	2.5 mm²
Clamping range, min.	2.5 mm²	Clamping range, max.	4 mm²
Wire cross-section, solid, min.	2.5 mm²	Wire cross-section, solid, max.	4 mm²
Twin wire-end ferrules, min.	1.5 mm²	Twin wire-end ferrules, max.	2.5 mm²
Blade size	PZ 1		

Classifications

ETIM 8.0	EC001437	ETIM 9.0	EC001437
ETIM 10.0	EC001437	ECLASS 14.0	27-37-16-01
ECLASS 15.0	27-37-16-01		

CRIKIT S 12VDC 1CO L/D UL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Cross-connections



Cross-connection for the socktes in the CUBESERIES CRI.
- Versions with red and blue coloured plastic for potential coding

Versions for PUSH IN sockets:
- 8-pin cross connection for A1 and A2 of the coil
- 2-pin jumper to connect to the neighbored sockets
- 2-pin jumper to connect the output channels within one socket

Version for screw sockets:
- 8-pin cross connection to connect to the neighbored sockets

General ordering data

Type	CXI CCS 8P GY	Version
Order No.	3052620000	CUBESERIES, Cross-connector
GTIN (EAN)	4099987022446	
Qty.	2 ST	

Marker holder



General ordering data

Type	CXI LABEL FLAP S	Version
Order No.	3169130000	CUBESERIES, Label
GTIN (EAN)	4099987828048	
Qty.	100 ST	