

## CRIKIT S 24VAC 2CO L/PB UL

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

### General ordering data

Version	, Number of contacts: 2, CO contact AgNi, Rated control voltage: 24 V AC, Continuous current: 8 A, Screw connection, Test button available: Yes
Order No.	<a href="#">8000158767</a>
Type	CRIKIT S 24VAC 2CO L/PB UL
GTIN (EAN)	4099987368469
Qty.	10 items

## CRIKIT S 24VAC 2CO L/PB UL

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

Depth	72.8 mm	Depth (inches)	2.8661 inch
Height	80 mm	Height (inches)	3.1496 inch
Width	15.8 mm	Width (inches)	0.622 inch
Net weight	1025.2 g		

### Temperatures

Storage temperature		Ambient temperature	-40 °C...70 °C
Operating temperature			

### Control side

Rated control voltage	24 V AC	Rated current AC	35.9 mA
Power rating	0.9 VA	Coil resistance	350 Ω ± 10 %
Status indicator	Green LED	Coil voltage of the replacement relay deviating from the rated control voltage	No

### Load side

Rated switching voltage	250 V AC	Continuous current	8 A
Max. switching frequency at rated load	0.1 Hz	Max. switching voltage, AC	250 V
Max. switching voltage, DC	250 V	AC switching capacity (resistive), max.	2000 VA
DC switching capacity (resistive), max.	192 W @ 24 V	Switch-on delay	≤ 12 ms
Switch-off delay	≤ 20 ms	Contact type	2 CO contact (AgNi)
Mechanical service life	1 x 10 <sup>6</sup> switching cycles	Min. switching power	10 mA @ 12 V, 100 mA @ 5 V

### General data

Operating altitude	≤ 2000 m, above sea level		
Mounting rail	TS 35		
Test button available	Yes		
Version of test button	Lockable test button, Momentary test button		
Mechanical switch position indicator	No		
Colour	black		
UL94 flammability rating component	Component	Socket	
	UL94 flammability rating	V-2	
	Component	Relay cover	
	UL94 flammability rating	V-2	

### Insulation coordination

Surge voltage category	II	Dielectric strength for control side - load 5 kVeff / 1 min side	
Dielectric strength of neighbouring contacts	3 kVeff / 1 Min.	Dielectric strength of open contact	1 kVeff / 1 min
Dielectric strength to mounting rail	5 kVeff / 1 min	Impulse withstand voltage	6 kV (1.2/50 μs)
Protection degree	IP20		

### Connection data

Wire connection method	Screw connection	Stripping length, rated connection	8 mm
Tightening torque, min.	0.7 Nm	Clamping range, rated connection	2.5 mm <sup>2</sup>
Clamping range, min.	2.5 mm <sup>2</sup>	Clamping range, max.	4 mm <sup>2</sup>
Wire cross-section, solid, min.	2.5 mm <sup>2</sup>	Wire cross-section, solid, max.	4 mm <sup>2</sup>

## CRIKIT S 24VAC 2CO L/PB UL

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

Twin wire-end ferrules, min.	1.5 mm <sup>2</sup>	Twin wire-end ferrules, max.	2.5 mm <sup>2</sup>
Blade size	PZ 1		

### Classifications

ETIM 8.0	EC001437	ETIM 9.0	EC001437
ETIM 10.0	EC001437	ECLASS 14.0	27-37-16-01
ECLASS 15.0	27-37-16-01		