


FBCON PA CG 8WAY LIMITER

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Do not use product for
new developments



For standard industrial applications (non-hazardous areas), PROFIBUS PA junction boxes and limiters are available as 1-way, 2-way, 4-way, and 8-way distributors. FBCon limiters are designed to protect connected field devices from over voltages and short circuits. As voltage-limiting protective elements, suppressor diodes are used. Due to the integrated current limitation, the segment is also protected against short circuit on a spur line. EMC cable glands, protection class IP66 and a wide operating temperature range safely protect your connections in harsh environments.

Functionality

- EMC cable glands for trunk and spurs
- M12 connector for spurs
- External earthing stud
- Pressure equalizing element
- Protection class IP66
- Aluminium and stainless-steel versions
- Profibus PA / Foundation Fieldbus compatible

Note: The use of FBCon products with aluminum enclosures and / or M12 connectors is not recommended in strongly saline environments.

General ordering data

Version	Standard distributor with current limiting, 8-channel distributor LIMITER, IP66, Branch line M12, w. cable glands
Order No.	8714230000
Type	FBCON PA CG 8WAY LIMITER
GTIN (EAN)	4032248398331
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Available until	2024-01-14T00:00:00+01:00
Alternative product	FBCON PA CG 8WAY LIMITER

FBCON PA CG 8WAY LIMITER

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Height	58 mm	Height (inches)	2.2835 inch
Width	80 mm	Width (inches)	3.1496 inch
Length	175 mm	Length (inches)	6.8898 inch
Net weight	964 g		

Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...55 °C
---------------------	----------------	-----------------------	----------------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c, 7a, 7cl
REACH SVHC	Lead 7439-92-1
SCIP	3a5f5913-76fc-4ff5-8563-4463f80bbe02

Technical data

Cable glands	Brass cable gland	Connection type PE	Spur line with cable gland
Type of distribution	8-channel distributor LIMITER	Design of housing	With pressure compensation element
Housing main material	Aluminium, AlSi12	Cable entry	Branch line M12, w. cable glands
Type of mounting	surface-mounted	Protection degree	IP66
Bus system	Profibus-PA, Foundation Fieldbus	Current limiting	adjustable, 20 mA, 40 mA, 60 mA
Housing surface	powder coating	Operating voltage U _{max} , max.	18 V DC ±20%

Part description

Product description	The device is an active field distributor for the fieldbus systems Profibus PA and Foundation Fieldbus H1. The device complies with protection class IP66/IP67. Functional description The device connects up to eight field devices with one fieldbus segment. An adjustable current monitoring per spur line protects the trunk line from short circuits or overload (see figure B1). Suppressor diodes protect the connected field devices from surge voltages. A red LED indicates a short circuit or overload on the spur line. A green LED indicates sufficient voltage supply on the trunk line. The device supports earthing concepts with multi-point screen earthing or single-point screen earthing. The earthing concepts are explained in the Profibus PA and Foundation Fieldbus guidelines.
---------------------	--

Classifications

ETIM 8.0	EC001604	ETIM 9.0	EC001604
ETIM 10.0	EC001604	ECLASS 14.0	27-44-01-11
ECLASS 15.0	27-44-01-11		

FBCON PA CG 8WAY LIMITER

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

