

MBGE ADPT 1769, 32CH**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Adapters for migration – 1769 CompactLogix.

The front adapters with pre-assembled cables provide a safe migration from the 1769 CompactLogix cards to other PLC/DCS systems or the u-remote modules from Weidmüller.

General ordering data

Order No.	8000168693
Type	MBGE ADPT 1769, 32CH
GTIN (EAN)	4099987803519
Qty.	ST

MBGE ADPT 1769, 32CH

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data
Dimensions and weights

Depth	70.4 mm	Depth (inches)	2.7716 inch
Height	119.4 mm	Height (inches)	4.7008 inch
Width	52.3 mm	Width (inches)	2.0591 inch
Net weight	1000 g		

Temperatures

Storage temperature	-20...70 °C	Operating temperature	-20...50 °C
---------------------	-------------	-----------------------	-------------

Rated data UL

Storage temperature UL, max.	70 °C	Operating temperature UL, min.	-20 °C
Operating temperature UL, max.	50 °C	Storage temperature UL, min.	-20 °C
Rated current I _{max}	40 A	Rated voltage UN	250 V

Connection data

Connection (field side)	MBGE ADPT 1769,32CH (METAL)		
-------------------------	-----------------------------	--	--

Connection data

Connection (field side)	MBGE ADPT 1769,32CH (METAL)	Connection to PLC	New PLC terminal block or hardwired
-------------------------	-----------------------------	-------------------	-------------------------------------

Ratings data

Operating voltage	250 V	Max. current per channel	4 A
Total operating current	40 A		

Insulation coordination (EN50178)

Rated insulation voltage	300 V	Surge voltage category	II
Pollution severity level	2	Pulse voltage test (1,2/50µs)	2.5 kV
Insulation test voltage AC	1.8 kV		

Classifications

ETIM 8.0	EC002584	ETIM 9.0	EC002584
ETIM 10.0	EC002584	ECLASS 14.0	27-33-02-92
ECLASS 15.0	27-33-02-92		

MBGE ADPT 1769, 32CH

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

