

PAS CMR 4,5...10 A DC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Product image, Similar to illustration



The PLUGCONTROL PAS CMRs present a simple, cost-effective solution for monitoring DC currents up to 10 A.

The monitoring relay (REED contact) comes attached to a standard base so that it can be mounted on a TS35 DIN rail.

Current monitoring of valves, servo-controls and DC motors are typical applications for these modules.

General ordering data

Version	Current monitoring, 4.5...10 A DC, 1, Screw connection
Order No.	8742630000
Type	PAS CMR 4,5...10 A DC
GTIN (EAN)	4032248413942
Qty.	10 items

PAS CMR 4,5...10 A DC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E141197

Dimensions and weights

Depth	95 mm	Depth (inches)	3.7401 inch
Height	95 mm	Height (inches)	3.7401 inch
Width	15.3 mm	Width (inches)	0.6024 inch
Length	92 mm	Length (inches)	3.622 inch
Net weight	55 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...60 °C
Humidity at operating temperature	0...95 % (no condensation)	Humidity	5-95% relative humidity, Tu = 40°C, without condensation

Probability of failure

SIL in compliance with IEC 61508 None

Environmental Product Compliance

RoHS Compliance Status Compliant
 REACH SVHC No SVHC above 0.1 wt%

General data

Protection degree	IP20	Mounting rail	TS 35
Temperature coefficient	350 ppm/K	Nominal power consumption	1.5 VA
Configuration	none		

Insulation coordination

Impulse withstand voltage	6 kV	EMC standards	EN 55011, EN 61000-6-1, 2, 3, 4
Surge voltage category	III	Pollution severity	2
Galvanic isolation	between input / output / supply / relay	Insulation voltage	4 kVeff / 1 min.
Rated voltage	300 V		

Input

Making current threshold	≤ 4.5 A	Secure off	≤ 600 mA
Resistance of sensor circuit	50 Ω	Input current	4.5...10 A DC
Input resistance, current	<50 mΩ	Pulse duration	min. 1 ms
Max. current	30 A for 10 s		

PAS CMR 4,5...10 A DC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Output

Number of outputs	1	Continuous current	100 mA
Contact material	RH/Rd (Reed contact)*	Max. switching voltage, AC	250 V
Switching voltage AC, min.	1 V	Max. switching voltage, DC	100 V
Switching voltage DC, min.	1 V	Contact assembly	1 NO contact
Max. switching frequency	20 Hz	Temperature coefficient	350 ppm/K
Switching current	2 A		

Connection data

Type of connection	Screw connection	Clamping range, rated connection	1.5 mm ²
Clamping range, min.	2.5 mm ²	Clamping range, max.	2.5 mm ²

Classifications

ETIM 8.0	EC002654	ETIM 9.0	EC002654
ETIM 10.0	EC002654	ECLASS 14.0	27-21-01-22
ECLASS 15.0	27-21-01-22		

PAS CMR 4,5...10 A DC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

Electric symbol

