


POK COPL 081606 MSZN**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The Klippon® POK enclosure range is made from a high-quality glass fibre reinforced polyester and is ideal for applications and environments where corrosion resistance, impact resistance and a high IP protection class are a requirement.

Key features of the extensive product range:

- Available in 17 sizes
- Two standard finishes (colours): grey (similar to RAL 7001 for industrial use) and black (similar to RAL 9011 for harsh environments, Ex)
- Cover with stainless steel screws in cross-head / slotted design
- Moulded gasket made of silicone or chloroprene
- Fixing holes outside the sealed area to ensure high ingress protection of IP66
- Impact resistance up to 7 Joules
- Mounting directly in the enclosure or using an internal mounting plate
- Direct wall mounting possible using fixing holes or mounting feet
- Fastening thread to attach mounting rails and plates
- Up to E60 fire rating dependent on the configuration
- Weidmüller can manufacture and supply this enclosure to match customer specifications - fitted with all necessary terminals and cable glands.

General ordering data

Version	Klippon POK (polyester empty enclosure), Earthing plate, with functional earth connection, Height: 36.57 mm, Width: 180.11 mm, Depth: 0.75 mm, Basic material: Steel sheet zinc plated, galvanic zinc plated and passivated
Order No.	8000191931
Type	POK COPL 081606 MSZN
GTIN (EAN)	4069165099430
Qty.	5 items

POK COPL 081606 MSZN**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	0.75 mm	Depth (inches)	0.0295 inch
Height	36.57 mm	Height (inches)	1.4398 inch
Width	180.11 mm	Width (inches)	7.0909 inch
Net weight	33.3 g		

Temperatures

Operating temperature

General information

Surface finish	galvanic zinc plated and passivated	Basic material	Steel sheet zinc plated
----------------	-------------------------------------	----------------	-------------------------

Classifications

ETIM 8.0	EC002623	ETIM 9.0	EC002623
ETIM 10.0	EC002623	ECLASS 14.0	27-18-28-14
ECLASS 15.0	27-18-28-14		