

WDK 2.5 1D

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

Fuse terminal blocks and component terminal blocks allow protective and functional elements to be integrated directly into the terminal strip. Fuse terminal blocks include built-in fuse holders to reliably protect electrical circuits against overload —ideal for control and distribution systems. Component terminal blocks make it possible to incorporate electronic components such as diodes, resistors, or LEDs directly into the wiring. This enables space-saving and clearly arranged implementation of switching functions and signal separation. Both types of terminal blocks ensure higher safety, easy maintenance, and a compact, function-oriented installation.

General ordering data

| | |
|------------|--|
| Version | Component terminal block, Screw connection, dark beige, 2.5 mm ² , 400 V, 400 V, Number of connections: 4, Number of levels: 2, TS 35 |
| Order No. | 8025610000 |
| Type | WDK 2.5 1D |
| GTIN (EAN) | 4008190150495 |
| Qty. | 25 items |

WDK 2.5 1D

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



| | |
|-----------------------|----------------------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (UR) | E60693 |

Dimensions and weights

| | | | |
|--------------------------|-------------|----------------|-------------|
| Depth | 62.5 mm | Depth (inches) | 2.4606 inch |
| Depth including DIN rail | 63 mm | Height | 69 mm |
| Height (inches) | 2.7165 inch | Width | 5.1 mm |
| Width (inches) | 0.2008 inch | Net weight | 12.15 g |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|----------------|
| Storage temperature | -25 °C...55 °C | Ambient temperature | -50 °C...75 °C |
| Continuous operating temp., min. | -50 °C | Continuous operating temp., max. | 120 °C |

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 7a |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | a3090896-Of16-410d-aabb-617cfb571002 |

Material data

| | | | |
|---------------------------|-------|--------|------------|
| Basic material | Wemid | Colour | dark beige |
| UL 94 flammability rating | V-0 | | |

System specifications

| | | | |
|-------------------------------------|---|-----------------------------------|-------|
| Version | Screw connection, with diode, for screwable cross-connection, One end without connector | End cover plate required | Yes |
| Number of potentials | 2 | Number of levels | 2 |
| Number of clamping points per level | 2 | Levels cross-connected internally | Yes |
| PE connection | No | Mounting rail | TS 35 |
| PE function | No | PEN function | No |

Additional technical data

| | | | |
|------------------|-----------------|-----------------------------|----|
| Open sides | right | Number of similar terminals | 1 |
| Type of fixing | when screwed in | Explosion-tested version | No |
| Type of mounting | Snap-on | | |

Conductors for clamping (rated connection)

| | | | |
|----------------------|---------|---|--------|
| Gauge to IEC 60947-1 | A3 | Wire connection cross section AWG, max. | AWG 12 |
| Connection direction | on side | Tightening torque, max. | 0.6 Nm |

WDK 2.5 1D

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

| | | | |
|---|----------------------|---|----------------------|
| Tightening torque, min. | 0.4 Nm | Stripping length | 10 mm |
| Type of connection 2 | Screw connection | Type of connection | Screw connection |
| Number of connections | 4 | Clamping range, max. | 4 mm ² |
| Clamping range, min. | 0.05 mm ² | Clamping screw | M 2.5 |
| Blade size | 0.6 x 3.5 mm | Wire connection cross section AWG, min. | AWG 26 |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.05 mm ² | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 2.5 mm ² |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.05 mm ² | Wire connection cross section, finely stranded, max. | 4 mm ² |
| Wire connection cross section, finely stranded, min. | 0.05 mm ² | Connection cross-section, stranded, max. | 4 mm ² |
| Connection cross-section, stranded, min. 0.05 mm ² | | Wire connection cross-section, solid core, max. | 4 mm ² |
| Wire connection cross-section, solid core, min. | 0.05 mm ² | Connection cross-section, finely stranded, min. | 0.05 mm ² |

Dimensions

| | |
|--------------|---------|
| TS 35 offset | 35.5 mm |
|--------------|---------|

General

| | | | |
|---|--------|---|---------------|
| Number of poles | 1 | Wire connection cross section AWG, max. | AWG 12 |
| Wire connection cross section AWG, min. | AWG 26 | Standards | IEC 60947-7-1 |
| Mounting rail | TS 35 | | |

Rating data

| | | | |
|--|---------------------|---------------------------------|---------------|
| Rated cross-section | 2.5 mm ² | Rated voltage | 400 V |
| Rated DC voltage | 400 V | Nominal current | 0.5 A |
| Current at maximum wires | 0.5 A | Standards | IEC 60947-7-1 |
| Volume resistance according to IEC 60947-7-x | 1.33 mΩ | Rated impulse withstand voltage | 6 kV |
| Power loss in accordance with IEC 60947-7-x | 0.77 W | Pollution severity | 3 |

UL rating data

| | | | |
|---|--------|---|--------|
| Voltage size B (UR) | 300 V | Current size B (UR) | 20 A |
| Conductor size Factory wiring max. (UR) | 12 AWG | Current size C (UR) | 20 A |
| Voltage size C (UR) | 300 V | Conductor size Factory wiring min. (UR) | 22 AWG |
| Certificate No. (UR) | E60693 | Conductor size Field wiring min. (UR) | 22 AWG |
| Conductor size Field wiring max. (UR) | 12 AWG | | |

Important note

| | |
|---------------------|--|
| Product information | Rated current 10 A only for the continuous currentbar. Components may reduce the rated current and the rated voltage. The permissible continuous operating temperature must be observed. The allowed continuous operating temperature must be observed |
|---------------------|--|



Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000903 | ETIM 9.0 | EC000903 |
| ETIM 10.0 | EC000903 | ECLASS 14.0 | 27-25-01-14 |
| ECLASS 15.0 | 27-25-01-14 | | |

WDK 2.5 1D

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

WDK 2.5 1D

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Cross-connections



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | WQV 2.5/2 | Version |
| Order No. | 1053660000 | Cross-connector (terminal), when screwed in, yellow, 32 A, Number of |
| GTIN (EAN) | 4008190031121 | poles: 2, Pitch in mm (P): 5.10, Insulated: Yes, Width: 7 mm |
| Qty. | 50 ST | |
| Type | WQV 2.5/3 | Version |
| Order No. | 1053760000 | Cross-connector (terminal), when screwed in, yellow, 32 A, Number of |
| GTIN (EAN) | 4008190058999 | poles: 3, Pitch in mm (P): 5.10, Insulated: Yes, Width: 7 mm |
| Qty. | 50 ST | |
| Type | WQV 2.5/4 | Version |
| Order No. | 1053860000 | Cross-connector (terminal), when screwed in, yellow, 32 A, Number of |
| GTIN (EAN) | 4008190049706 | poles: 4, Pitch in mm (P): 5.10, Insulated: Yes, Width: 7 mm |
| Qty. | 50 ST | |
| Type | WQV 2.5/5 | Version |
| Order No. | 1053960000 | Cross-connector (terminal), when screwed in, yellow, 32 A, Number of |
| GTIN (EAN) | 4008190158446 | poles: 5, Pitch in mm (P): 5.10, Insulated: Yes, Width: 7 mm |
| Qty. | 10 ST | |
| Type | WQV 2.5/6 | Version |
| Order No. | 1054060000 | Cross-connector (terminal), when screwed in, yellow, 32 A, Number of |
| GTIN (EAN) | 4008190102272 | poles: 6, Pitch in mm (P): 5.10, Insulated: Yes, Width: 7 mm |
| Qty. | 10 ST | |
| Type | WQV 2.5/7 | Version |
| Order No. | 1054160000 | Cross-connector (terminal), when screwed in, yellow, 32 A, Number of |
| GTIN (EAN) | 4008190011246 | poles: 7, Pitch in mm (P): 5.10, Insulated: Yes, Width: 7 mm |
| Qty. | 10 ST | |
| Type | WQV 2.5/8 | Version |
| Order No. | 1054260000 | Cross-connector (terminal), when screwed in, yellow, 32 A, Number of |
| GTIN (EAN) | 4008190073572 | poles: 8, Pitch in mm (P): 5.10, Insulated: Yes, Width: 7 mm |
| Qty. | 10 ST | |
| Type | WQV 2.5/10 | Version |
| Order No. | 1054460000 | Cross-connector (terminal), when screwed in, yellow, 32 A, Number of |
| GTIN (EAN) | 4008190135089 | poles: 10, Pitch in mm (P): 5.10, Insulated: Yes, Width: 7 mm |
| Qty. | 20 ST | |
| Type | WQV 2.5/15 | Version |
| Order No. | 1059660000 | Cross-connector (terminal), when screwed in, yellow, 32 A, Number of |
| GTIN (EAN) | 4008190002411 | poles: 15, Pitch in mm (P): 5.10, Insulated: Yes, Width: 7 mm |
| Qty. | 10 ST | |
| Type | WQV 2.5/30 | Version |
| Order No. | 1067500000 | Cross-connector (terminal), when screwed in, yellow, 32 A, Number of |
| GTIN (EAN) | 4008190031107 | poles: 30, Pitch in mm (P): 5.10, Insulated: Yes, Width: 7 mm |
| Qty. | 10 ST | |

WDK 2.5 1D

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

| | | |
|------------|----------------------------|--|
| Type | WQV 2.5/20 | Version |
| Order No. | 1577570000 | Cross-connector (terminal), when screwed in, yellow, 32 A, Number of |
| GTIN (EAN) | 4008190125868 | poles: 20, Pitch in mm (P): 5.10, Insulated: Yes, Width: 7 mm |
| Qty. | 10 ST | |
| Type | WQV 2.5/32 | Version |
| Order No. | 1577600000 | Cross-connector (terminal), when screwed in, yellow, 32 A, Number of |
| GTIN (EAN) | 4008190154035 | poles: 32, Pitch in mm (P): 5.10, Insulated: Yes, Width: 7 mm |
| Qty. | 10 ST | |

End plates and partition plates




Partition plates and end plates are essential accessories for terminal blocks. Partition plates provide optical and electrical separation of different potentials and functional groups, increasing safety and ensuring a clear structure inside the control cabinet. End plates close the terminal block row on the sides, protect against contact with live parts, and ensure a clean, stable finish. Both components are precisely matched to the respective Weidmüller terminal block series, contributing to safe, compliant, and professional wiring.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | WAP WDK2.5 | Version |
| Order No. | 1059100000 | End plate for terminals, dark beige, Height: 69 mm, Width: 1.5 mm, |
| GTIN (EAN) | 4008190101954 | V-0, Wemid, Snap-on: No |
| Qty. | 20 ST | |
| Type | WAP WDK2.5 BL | Version |
| Order No. | 1059180000 | End plate for terminals, blue, Height: 69 mm, Width: 1.5 mm, V-0, |
| GTIN (EAN) | 4008190081089 | Wemid, Snap-on: No |
| Qty. | 20 ST | |
| Type | WAP WDK2.5 GN | Version |
| Order No. | 1059140000 | End plate for terminals, green, Height: 69 mm, Width: 1.5 mm, V-0, |
| GTIN (EAN) | 4008190901790 | Wemid, Snap-on: No |
| Qty. | 20 ST | |

End bracket



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | EW 35 | Version |
| Order No. | 0383560000 | End bracket, beige, TS 35, V-2, Wemid, Width: 8.5 mm, 100 °C |
| GTIN (EAN) | 4008190181314 | |
| Qty. | 50 ST | |

WDK 2.5 1D

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

| | | |
|------------|----------------------------|--|
| Type | WEW 35/2 | Version |
| Order No. | 1061200000 | End bracket, dark beige, TS 35, HB, Wemid, Width: 8 mm, 100 °C |
| GTIN (EAN) | 4008190030230 | |
| Qty. | 50 ST | |

Combined screwing and cutting tool "Swifty® CS"

Combined cutting/stripping tool Swifty® CS and Swifty® CS set for crimp-free cutting and stripping of copper cables up to 1.5 mm² solid and 2.5 mm² flexible.



General ordering data

| | | |
|------------|----------------------------|-------------------------------------|
| Type | SWIFTY CS | Version |
| Order No. | 9006020000 | Cutting tool for one-hand operation |
| GTIN (EAN) | 4032248257409 | |
| Qty. | 1 ST | |

Slotted screwdriver



Slotted screwdriver with rounded blade SD DIN 5265, ISO 2380/2, output to DIN 5264, ISO 2380/1. ChromTop tip, SoftFinish grip

General ordering data

| | | |
|------------|----------------------------|--------------------------|
| Type | SDS 0.6X3.5X100 | Version |
| Order No. | 9008330000 | Screwdriver, Screwdriver |
| GTIN (EAN) | 4032248056286 | |
| Qty. | 1 ST | |


WDK 2.5 1D

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

With lightning flash



The WAD connector marker is suitable for W-series terminals and for the WEW 35/2 and ZEW 35/2 end brackets. The markers are available as blank markers, with custom printing or standard print with lightning symbol. The WAD MultiCard markers are suitable for labelling with PrintJet CONNECT printers. For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | WAD 5 MC B GE/SW | Version |
| Order No. | 1120450000 | Group markers, Cover, 33.3 x 5 mm, Pitch in mm (P): 5.00 WDU 2.5, |
| GTIN (EAN) | 4032248901272 | WEW 35/2, ZEW 35/2, yellow |
| Qty. | 48 ST | |

Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | DEK 5/5 MC NE WS | Version |
| Order No. | 1609801044 | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4008190397111 | Weidmüller, white |
| Qty. | 1000 ST | |
| Type | WS 8/5 MC NE WS | Version |
| Order No. | 1640740000 | WS, Terminal marker, 8 x 5 mm, Pitch in mm (P): 5.00 Weidmüller, |
| GTIN (EAN) | 4008190279103 | Allen-Bradley, white |
| Qty. | 720 ST | |

WDK 2.5 1D

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Shield clamping saddle



With our wide range of KLBÜ shield connections, you can achieve flexible and self-adjusting shield contacting and ensure error-free plant operation.

General ordering data

| | | |
|------------|----------------------------|----------------------|
| Type | LS 2.8 WDU2.5-10 | Version |
| Order No. | 1056400000 | W-Series, Shield bus |
| GTIN (EAN) | 4008190036454 | |
| Qty. | 100 ST | |

Marker holder



The marker holder offer the possibility of additional mounting of standard markers with a pitch of 5 or 5.1 mm. The angled holders can be optionally snaped together and could be mounted in all standard marking channels of the Klippon® Connect modular terminal blocks. Fitting marker types could be found under the respective accessories of the designation marking holder.

General ordering data

| | | |
|------------|----------------------------|----------------------------|
| Type | BZT 1 WS 10/5 | Version |
| Order No. | 1805490000 | Accessories, Marker holder |
| GTIN (EAN) | 4032248270231 | |
| Qty. | 100 ST | |
| Type | BZT 1 ZA WS 10/5 | Version |
| Order No. | 1805520000 | Accessories, Marker holder |
| GTIN (EAN) | 4032248270248 | |
| Qty. | 100 ST | |