

## DK AND 35 24VDC



Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Logic functions AND, NAND, OR and NOR in modular terminal format with a rated cross-section of 4 mm<sup>2</sup>. They each have five inputs which are fed – with logic gating – via a 24 V/20 mA PNP output. The logic components can be used for many applications involving the coupling of digital sensor/actuator signals with automation devices.

## General ordering data

Version	Function component, AND gate
Order No.	<a href="#">8184040000</a>
Type	DK AND 35 24VDC
GTIN (EAN)	4008190121938
Qty.	5 items

## DK AND 35 24VDC

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

## Dimensions and weights

Depth	65 mm	Depth (inches)	2.5591 inch
Height	57 mm	Height (inches)	2.2441 inch
Width	12 mm	Width (inches)	0.4724 inch
Length	65 mm	Length (inches)	2.5591 inch
Net weight	22.2 g		

## Temperatures

Storage temperature	-40 °C...60 °C	Operating temperature	0 °C...50 °C
Humidity	40 °C / 93 % rel. humidity, no condensation		

## Probability of failure

SIL in compliance with IEC 61508 None

## Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	7a, 7cI
REACH SVHC	Lead 7439-92-1
SCIP	35d83707-6a3b-45b5-b9f8-6ba8184c863e

## Functions

Logic function and

## General data

Protection degree	IP20	Supply voltage	24...30 V DC
Current consumption	<5 mA	Mounting rail	TS 35
Power consumption	30 mW	Nominal power consumption	0.03 VA

## Insulation coordination

Galvanic isolation Without isolation

## Input

Number inputs	5	Rated input level	24 V DC= High, 0 V = Low
Rated voltage	Max. 30 V	Input current	Approx. 1.5 mA per input (24 V)
Pulse duration	≥ 50 µs		

## DK AND 35 24VDC

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Output

Number of outputs	8-bit (1-bit signed)	Load impedance current	≤ 600 Ω
Output level	PNP, Ub-1.8 V	Switching thresholds	High <15 V, low <9 V
Output current	max. 20 mA		

### General data

Open sides	right	Type of connection	Screw connection
Humidity	40 °C / 93 % rel. humidity, no condensation	Input/Output	Logic module
Supply voltage	24...30 V DC	Galvanic isolation	Without isolation
Current consumption	<5 mA	Mounting rail	TS 35
Power consumption	30 mW		

### Insulation coordination

Standards	EN 61000-6-2:2005, EN 61000-6-3:2007/ A1:2011, EN 61000-6-4:2007 + A1:2011, CE
-----------	--

### Connection data

Type of connection	Screw connection	Clamping range, rated connection	4 mm <sup>2</sup>
Clamping range, min.	0.5 mm <sup>2</sup>	Clamping range, max.	4 mm <sup>2</sup>

### Classifications


ETIM 8.0	EC001417	ETIM 9.0	EC001417
ETIM 10.0	EC001417	ECLASS 14.0	27-24-22-16
ECLASS 15.0	27-24-22-16		

**DK AND 35 24VDC**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)



## DK AND 35 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Cross-connections



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

## General ordering data

Type	VQB 1.5/50 SW	Version	
Order No.	<a href="#">1635120000</a>	Cross-connector (terminal), when screwed in, black, 17.5 A, Number of poles: 50, Pitch in mm (P): 6.20, Insulated: Yes, Width: 4.2 mm	
GTIN (EAN)	4008190262761		
Qty.	5 ST		

## Custom printing



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.


Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
  - Strips for fast installation
  - Terminal markers, suitable for all Weidmüller cable connectors
  - Available as blank MultiCard or with standard printing
- For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	DEK 5/5 MC SDR	Version	
Order No.	<a href="#">1609810000</a>	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00	
GTIN (EAN)	4008190456597	Weidmueller, To customer specification	
Qty.	200 ST		

## Logic modules



Logic functions AND, NAND, OR and NOR in modular terminal format with a rated cross-section of 4 mm<sup>2</sup>. They each have five inputs which are fed – with logic gating – via a 24 V/20 mA PNP output. The logic components can be used for many applications involving the coupling of digital sensor/actuator signals with automation devices.

## DK AND 35 24VDC

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### General ordering data

Type	AP DKT4 PA	Version	
Order No.	<a href="#">0687560000</a>	End plate for terminals, beige, Height: 65 mm, Width: 1.5 mm, V-2,	
GTIN (EAN)	4008190009465	PA 66, Snap-on: Yes	
Qty.	20 ST		