

MCZ OVP SL 24VUC 1,25A

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (UL) E311081

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 63.5 mm | Depth (inches) | 2.5 inch |
| Height | 91 mm | Height (inches) | 3.5827 inch |
| Width | 6 mm | Width (inches) | 0.2362 inch |
| Net weight | 25.2 g | | |

Temperatures

| | | | |
|---------------------|----------------|-----------------------|-------------|
| Storage temperature | -40 °C...85 °C | Operating temperature | -40 °C...60 |
|---------------------|----------------|-----------------------|-------------|

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 7a |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | c9db83e7-2b25-44e1-8d26-da64d426373f |

Rated data UL

| | |
|----------------------|---------|
| Certificate No. (UL) | E311081 |
|----------------------|---------|

General data

| | | | |
|---------------|---------------------------------------|---------------------------|---|
| Segment | Measurement - Monitoring - Setting | Version | Surge protection for measurement and control |
| Design | Terminal | UL 94 flammability rating | V-0 |
| Colour | black | Protection degree | IP20 |
| Mounting rail | TS 35 | Height with TS 35 | 63.5 mm |

Insulation coordination acc. to EN 50178

| | | | |
|------------------------|-----|--------------------|---|
| Surge voltage category | III | Pollution severity | 2 |
|------------------------|-----|--------------------|---|

Rated data IEC / EN

| | | | |
|---|----------------------------|---|-----------------------------|
| Discharge current, I _{imp} (10/350 μs) | 1 kA | Rated voltage (AC) | 24 V |
| Rated voltage (DC), max. | 38 V | Rated voltage (DC) | 24 V |
| Rated current I _N | 1.25 A | Protection level on output side Wire-wire | 80 V 1 kV/μs, typically |
| Protection level on output side Wire-PE | 40 V 1kV/μs, typically | Protection level on output side Wire-wire | 130 V 8/20 μs, typically |
| Protection level on output side Wire-PE | 65 V 8/20 μs, typically | Voltage type | AC/DC |
| Fuse protection | 1.3 A | Response time / fallback time | ≤ 100 ps |
| Operating voltage | 34 V | Volume resistance | 1.00 Ω |
| Operating current, I _{max} . | 1.25 A | Lightning test current I _{imp} (10/350 μs) | 1 kA |

MCZ OVP SL 24VUC 1,25A

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

| | | | |
|--|-------|---|---------------|
| Discharge current, max. (8/20 µs) | 5 kA | Requirements category acc. to IEC 61643-21 | D1 |
| Load resistance (for limiting frequency) | 240 Ω | Limiting frequency (-3 dB) at load resistance | 500 kHz 240 Ω |
| Max. continuous voltage, U _c (AC) | 28 V | Inductance L and L1 | 35 µH |

Connection data

| | | | |
|---|---------------------|---|--------------------------|
| Stripping length | 8 mm | Cross-section | 1.5 mm ² |
| Wire connection method | Spring connection | Type of connection | Tension-clamp connection |
| Stripping length, rated connection | 8 mm | Clamping range, rated connection | 1.5 mm ² |
| Clamping range, min. | 0.5 mm ² | Clamping range, max. | 1.5 mm ² |
| Wire connection cross section AWG, min. | AWG 26 | Wire connection cross section AWG, max. | AWG 16 |
| Wire cross-section, solid, min. | 0.5 mm ² | Wire cross-section, solid, max. | 1.5 mm ² |
| Wire cross-section, solid, min. (AWG) | AWG 26 | Wire cross-section, solid, max. (AWG) | AWG 16 |
| Wire connection cross section, finely stranded, min. | 0.5 mm ² | Wire connection cross section, finely stranded, max. | 1.5 mm ² |
| Wire cross-section, finely stranded, min. (AWG) | AWG 26 | Wire cross-section, finely stranded, max. (AWG) | AWG 16 |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.5 mm ² | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 1.5 mm ² |
| Conductor cross-section, flexible, AEH (DIN 46228-1), min. | 0.5 mm ² | Conductor cross-section, flexible, AEH (DIN 46228-1), max. | 1.5 mm ² |
| Blade size | 0.6 x 3.5 mm | | |

Electrical data

| | |
|--------------|-------|
| Voltage type | AC/DC |
|--------------|-------|

General data

| | | | |
|-------------------|------|--------|-------|
| Protection degree | IP20 | Colour | black |
|-------------------|------|--------|-------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000943 | ETIM 9.0 | EC000943 |
| ETIM 10.0 | EC000943 | ECLASS 14.0 | 27-17-15-01 |
| ECLASS 15.0 | 27-17-15-01 | | |


MCZ OVP SL 24VUC 1,25A

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Electric symbol



Circuit diagram

MCZ OVP SL 24VUC 1,25A

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Steel



Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

General ordering data

| | | | |
|------------|----------------------------|---|--|
| Type | TS 35X7.5 2M/ST/ZN | Version | |
| Order No. | 0383400000 | Terminal rail, Accessories, Steel, galvanic zinc plated and passivated, | |
| GTIN (EAN) | 4008190088026 | Width: 2000 mm, Height: 35 mm, Depth: 7.5 mm | |
| Qty. | 40 M | | |

End bracket



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

| | | | |
|------------|----------------------------|--|--|
| Type | EW 35 | Version | |
| Order No. | 0383560000 | End bracket, beige, TS 35, V-2, Wemid, Width: 8.5 mm, 100 °C | |
| GTIN (EAN) | 4008190181314 | | |
| Qty. | 50 ST | | |

Steel



Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

General ordering data

| | | | |
|------------|----------------------------|---|--|
| Type | TS 35X15/2.3 2M/ST/ZN | Version | |
| Order No. | 0498000000 | Terminal rail, Accessories, Steel, galvanic zinc plated and passivated, | |
| GTIN (EAN) | 4008190042493 | Width: 2000 mm, Height: 35 mm, Depth: 15 mm | |
| Qty. | 20 M | | |

MCZ OVP SL 24VUC 1,25A

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

AP MCZ 1.5 - End plate



Open miniature housing in modular terminal format with five tension clamp connections. A transparent hinged top plate can be used for labelling and provides access to potentiometer and status displays. Plug-in cross-connectors can be used to interconnect the three top connections. A cover plate for closing off the housing is also available.

General ordering data

| | | | |
|------------|----------------------------|---|--|
| Type | AP MCZ1.5 SW 1683 | Version | |
| Order No. | 1046410000 | End plate, OMNIMATE Housing - TERMINALBOX black, End plate, | |
| GTIN (EAN) | 4032248782246 | Width: 1.5 mm | |
| Qty. | 50 ST | | |

Slotted screwdriver



VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip

General ordering data

| | | | |
|------------|----------------------------|--------------------------|--|
| Type | SDIS 0.6X3.5X100 | Version | |
| Order No. | 9008390000 | Screwdriver, Screwdriver | |
| GTIN (EAN) | 4032248056354 | | |
| Qty. | 1 ST | | |