

RS SD15 BZ

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration

Passive interfaces for signal transmission on a SubD connector equipped with a tension-clamp connection in accordance with IEC 807-2 / DIN 41652. The main features include:

- Group with 9-, 15-, 37- and 50-pole male and female connectors.
- One-to-one electrical connection between controller and field connections.
- Extremely compact modules for attachment to standard TS35 or TS32 rail.

General ordering data

| | |
|-----------------|------------------------------------------------------------------------------------------------------------|
| Version | Interface, RSSD, D-sub connectors, acc. to IEC 60807 / DIN 41652, 15-pole female, Tension-clamp connection |
| Order No. | 8537400000 |
| Type | RS SD15 BZ |
| GTIN (EAN) | 4032248173082 |
| Qty. | 1 items |
| Delivery status | This article will no longer be available in the future. |
| Last order date | 2026-02-10T00:00:00+01:00 |

RS SD15 BZ

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



| | |
|-----------------------|----------------------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (UR) | E141197 |

Dimensions and weights

| | | | |
|------------|-------|-----------------|-------------|
| Depth | 64 mm | Depth (inches) | 2.5197 inch |
| Height | 87 mm | Height (inches) | 3.4252 inch |
| Width | 60 mm | Width (inches) | 2.3622 inch |
| Net weight | 120 g | | |

Temperatures

| | | | |
|---------------------|-------------|-----------------------|-----------|
| Storage temperature | -40...70 °C | Operating temperature | 0...55 °C |
|---------------------|-------------|-----------------------|-----------|

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6aI, 6c |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 7b5ffb72-271d-4c73-8b09-bd0aaee3697a |

Rated data UL

| | | | |
|--------------------------------|-------|--------------------------------|-------|
| Rated current IN | 1 A | Operating temperature UL, min. | 0 °C |
| Operating temperature UL, max. | 25 °C | Rated voltage UN | 100 V |

Connection Data

| | | | |
|----------------------------|-------------------------------------------------|--------------------------------|----------------|
| Design of locking system | UNC 4/40 | Number of poles (control side) | 15-pole female |
| Connection (field side) | LM2NZF 5.08mm | Earthing | No |
| Connection on control side | D-sub connectors, acc. to IEC 60807 / DIN 41652 | | |

Rating data

| | | | |
|---------------|-------|------------------------------|-------|
| Rated voltage | 100 V | Rated current per connection | 1.5 A |
|---------------|-------|------------------------------|-------|

Insulation coordination (EN50178)

| | | | |
|-------------------------------|--------------|--------------------------|-------|
| According to | DIN EN 50178 | Rated insulation voltage | 100 V |
| Surge voltage category | II | Pollution severity level | 2 |
| Pulse voltage test (1,2/50µs) | 0.8 kV | | |

Connection field

| | | | |
|----------------------------------|---------------------|----------------------------|--------------------------|
| Min. wire cross-section, AWG | AWG 24 | Type of connection | Tension-clamp connection |
| Sleeve with plastic collar, max. | 1.5 mm ² | Flexible with sleeve, min. | 0.25 mm ² |
| Flexible with sleeve, max. | 1.5 mm ² | Flexible, max. H05(07) V-K | 1.5 mm ² |
| Flexible, min. H05(07) V-K | 0.2 mm ² | Solid, max. H05(07) V-U | 2.5 mm ² |

RS SD15 BZ

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

| | | | |
|------------------------------|---------------------|----------------------|----------------------|
| Solid, min. H05(07) V-U | 0.2 mm ² | Stripping length | 7.5 mm |
| Clamping range, max. | 2.5 mm ² | Clamping range, min. | 0.13 mm ² |
| Max. wire cross-section, AWG | AWG 14 | | |

Standard features

| | |
|--------|------------------|
| Design | Socket connector |
|--------|------------------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002780 | ETIM 9.0 | EC002780 |
| ETIM 10.0 | EC002780 | ECLASS 14.0 | 27-14-11-52 |
| ECLASS 15.0 | 27-14-11-52 | | |



N: Number of poles

RS SD15 BZ

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Steel



Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

General ordering data

| | | | |
|------------|----------------------------|-------------------------------------------------------------------------|--|
| Type | TS 32X15 2M/ST/ZN | Version | |
| Order No. | 0122800000 | Terminal rail, Accessories, Steel, galvanic zinc plated and passivated, | |
| GTIN (EAN) | 4008190066307 | Width: 2000 mm, Height: 33 mm, Depth: 15 mm | |
| Qty. | 20 M | | |

End bracket



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

| | | | |
|------------|----------------------------|-------------------------------------------------------------|--|
| Type | EWK 2 | Version | |
| Order No. | 0199360000 | End bracket, beige, TS 32, V-0, Wemid, Width: 15 mm, 100 °C | |
| GTIN (EAN) | 4008190023546 | | |
| Qty. | 50 ST | | |

Steel



Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

General ordering data

| | | | |
|------------|----------------------------|-------------------------------------------------------------------------|--|
| Type | TS 35X7.5 2M/ST/ZN | Version | |
| Order No. | 0383400000 | Terminal rail, Accessories, Steel, galvanic zinc plated and passivated, | |
| GTIN (EAN) | 4008190088026 | Width: 2000 mm, Height: 35 mm, Depth: 7.5 mm | |
| Qty. | 40 M | | |

RS SD15 BZ

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

End bracket



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

| | | | |
|------------|----------------------------|--------------------------------------------------------------|--|
| Type | EW 35 | Version | |
| Order No. | 0383560000 | End bracket, beige, TS 35, V-2, Wemid, Width: 8.5 mm, 100 °C | |
| GTIN (EAN) | 4008190181314 | | |
| Qty. | 50 ST | | |

Steel



Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

General ordering data

| | | | |
|------------|----------------------------|-------------------------------------------------------------------------|--|
| Type | TS 35X15/2.3 2M/ST/ZN | Version | |
| Order No. | 0498000000 | Terminal rail, Accessories, Steel, galvanic zinc plated and passivated, | |
| GTIN (EAN) | 4008190042493 | Width: 2000 mm, Height: 35 mm, Depth: 15 mm | |
| Qty. | 20 M | | |