

CP M SNT 70W 24V 3A

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



PRO-M = Power-Reliable-Optimized

The perfectly reliable power supply for automation technology.

The ten different versions for the 24V-DC power supply all feature a solid but thin metal housing which enables them to be installed without any side gaps. This results in less space required on the mounting rail. Wide range of AC/DC inputs and a wide temperature range enable them to be used anywhere. Because of its high efficiency, resistance to overloads and high power reserves, the PRO-M is a trusted power supply for use in any application. The three-phase PRO-M power supply modules continue to function reliably when one phase fails (i.e., in two-phase mode).

General ordering data

Version	Power supply, switch-mode power supply unit, 24 V
Order No.	8951330000
Type	CP M SNT 70W 24V 3A
GTIN (EAN)	4032248742547
Qty.	1 items
Delivery status	Discontinued
Available until	2022-03-30T00:00:00+02:00
Alternative product	PRO MAX 72W 24V 3A

CP M SNT 70W 24V 3A

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E255651
Certificate no. (cULus)	E258476

Dimensions and weights

Depth	125 mm	Depth (inches)	4.9212 inch
Height	130 mm	Height (inches)	5.1181 inch
Width	33 mm	Width (inches)	1.2992 inch
Net weight	588 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-25 °C...70
---------------------	----------------	-----------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1

Rated data UL

Certificate No. (cURus)	E255651
-------------------------	---------

Input

Connection system	Screw connection	AC input voltage range	85...264 V AC (derating at 100 V AC)
Recommended back-up fuse	2 A / DI, safety fuse 6 A, Char. B, circuit breaker 2...4 A, Char. C circuit breaker	Frequency range AC	47...63 Hz
Rated input voltage	100...240 V AC (wide-range input)	Input fuse	Yes
Wire connection method	Screw connection	Input fuse (internal)	Yes
AC current consumption	0.6 A @ 230 V AC / 1.1 A @ 115 V AC	DC current consumption	0.25 A @ 370 V DC / 0.7 A @ 120 V DC
DC input voltage range	80...370 V DC (Derating @ 120 V DC)	Inrush current	max. 40 A

Output

Output power	70 W	Rated output voltage	24 V DC \pm 1 %
Residual ripple, breaking spikes	< 50 mVPP @ 24 V DC, IN	Parallel connection option	yes, max. 5
Overload protection	Yes	Output voltage, max.	29.5 V
Output voltage, min.	22.5 V	Wire connection method	Screw connection
Output voltage type	DC	Output voltage, note	(adjustable via potentiometer on front)
Nominal output current for Unom	3 A @ 60 °C	Output current	3 A
Continuous output current @ UNominal	3.6 A @ 45 °C, 3.2 A @ 55 °C, 2.3 A @ 70 °C		

CP M SNT 70W 24V 3A

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

General data

Power factor (approx.)	> 0.6 @ 230 V AC / > 0.65 @ 115 V AC	AC failure bridging time @ Inom	> 20 ms @ 230 V AC / > 20 ms @ 115 V AC
Degree of efficiency	90 % @ 230 V AC / 88 % @ 115 V AC	Protection degree	IP20
Mounting position, installation notice	Horizontal on TS35 mounting rail. 50 mm of clearance at top & bottom for air circ. Can mount side by side with no space in between.	Housing version	Metal, corrosion resistant
Protection against reverse voltages from the load	30...35 V DC	Indication	Operation, green LED
Current limiting	> 120% IN	Short-circuit protection	Yes
Protection against over-heating	Yes	Shock wall acc. to IEC 68227	30 g

EMC / shock / vibration

Limiting of mains voltage harmonic currents	According to EN 61000-3-2	Shock resistance IEC 60068-2-27	30 g in all directions
Noise emission in accordance with EN55032	Class B	Interference immunity test acc. to	EN 61000-4-2 (ESD) EN 61000-4-3 and EN 61000-4-8 (fields) EN 61000-4-4 (burst) EN 61000-4-5 (surge) EN 61000-4-6 (conducted) EN 61000-4-11 (dips)
Vibration resistance IEC 60068-2-6	Acc. to EN50178, shock: 5g in all directions		

Insulation coordination

Pollution severity	2	Insulation voltage	3 kV input/output; 2 kV input/earth; 0.5 kV output/earth
electrical isolation, output-earth	0.5 kV	electrical isolation, input-output	3 kV
electrical isolation, input-earth	2 kV	Protection class	I, with PE connection

Electrical safety (applied standards)

For use with electronic equipment	Acc. to EN50178 / VDE0160	Electrical machine equipment	Acc. to EN60204
Protection against dangerous shock currents	Acc. to VDE0106-101	Protective separation / protection against electrical shock	VDE0100-410 / acc. to DIN57100-410
Safety transformers for switch-mode power supplies	According to EN 61558-2-16		

Connection data (input)

Connection system	Screw connection	Number of terminals	3 for L/N/PE
Conductor cross-section, AWG/kcmil, max.	12	Conductor cross-section, AWG/kcmil, min.	26
Wire connection cross section, flexible (input), max.	2.5 mm ²	Conductor cross-section, flexible, min.	0.5 mm ²
Conductor cross-section, rigid, max.	6 mm ²	Conductor cross-section, rigid, min.	0.5 mm ²
Tightening torque, min.	0.5 Nm	Tightening torque, max.	0.6 Nm

CP M SNT 70W 24V 3A

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data


Connection data (output)

Number of terminals	4 (++) / -)	Conductor cross-section, AWG/kcmil , max.	12
Conductor cross-section, AWG/kcmil , min.	26	Conductor cross-section, flexible , max.	2.5 mm ²
Conductor cross-section, flexible , min.	0.5 mm ²	Conductor cross-section, rigid , max.	6 mm ²
Conductor cross-section, rigid , min.	0.5 mm ²	Tightening torque, min.	0.5 Nm
Tightening torque, max.	0.6 Nm		

Classifications

ETIM 8.0	EC002540	ETIM 9.0	EC002540
ETIM 10.0	EC002540	ECLASS 14.0	27-04-07-01
ECLASS 15.0	27-04-07-01		

Electric symbol



With DC connection, note polarity