


MEHA KP GN M-D-SPX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- Flexible and solid wire with PVC, Teflon (PTFE) and silicone insulation
- No damage to the wire thanks to specially shaped blade
- No splicing of individual wires
- Blade inserts are easy to replace
- All inserts fit one housing
- Guide bars in the blade cassettes facilitate correct positioning of the wire in the tool

General ordering data

| | |
|------------|-----------------------------|
| Version | Accessories, Set of cutters |
| Order No. | 9003620000 |
| Type | MEHA KP GN M-D-SPX |
| GTIN (EAN) | 4008 190130527 |
| Qty. | 1 items |

MEHA KP GN M-D-SPX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 16 mm | Depth (inches) | 0.6299 inch |
| Height | 11.5 mm | Height (inches) | 0.4528 inch |
| Width | 26 mm | Width (inches) | 1.0236 inch |
| Length | 26 mm | Length (inches) | 1.0236 inch |
| Net weight | 3.68 g | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------|
| RoHS Compliance Status | Not affected |
| REACH SVHC | No SVHC above 0.1 wt% |

Technical data

| | |
|------------------------|-----------------------------------------------------------|
| Description of article | Set of blades for Mini-Duro-Stripax up to AWG 20 for PTFE |
|------------------------|-----------------------------------------------------------|

Stripping tools

| | | | |
|-------------------------|----------------------------------|-------------------------|--------|
| Cable type | Conductor with custom insulation | Max. conductor diameter | 0.8 mm |
| Min. conductor diameter | 0.55 mm | Stripping length, max. | 7 mm |
| Stripping length, min. | 3 mm | Colour | green |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001509 | ETIM 9.0 | EC001509 |
| ETIM 10.0 | EC001509 | ECLASS 14.0 | 21-04-48-91 |
| ECLASS 15.0 | 21-04-48-91 | | |