

H16,0/32

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



For conductors from 10.0 to 185.0 mm² (AWG 7 - 350 MCM)

tin-plated copper

dimensional tolerances to DIN 46228 part 1

- supplied loose in poly-bag

General ordering data

| | |
|------------|--|
| Version | Wire-end ferrule, Standard, 32 mm, 32 mm, No |
| Order No. | 9004160000 |
| Type | H16,0/32 |
| GTIN (EAN) | 4008190084004 |
| Qty. | 100 items |
| Packaging | loose |

H16,0/32

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



| | |
|-------------------------|----------------------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate no. (cULus) | E499744 |

Dimensions and weights

| | |
|------------|-------|
| Net weight | 0.9 g |
|------------|-------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Technical data

| | | | |
|------------------------|--|---------|----------|
| Description of article | Wire end ferrule without plastic collar, (2)Wire-end ferrule | Version | Standard |
|------------------------|--|---------|----------|

Wire-end ferrules

| | | | |
|---|--------------------|-----------------------------|----------|
| Contact surface diameter (D1) | 5.8 mm | Contact surface length (L2) | 32 mm |
| Collar diameter (D2) | 7.5 mm | L1 in mm | 32.00 mm |
| Wire connection cross section AWG, max. | AWG 6 | Stripping length | 32 mm |
| Conductor cross-section | 16 mm ² | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000005 | ETIM 9.0 | EC000005 |
| ETIM 10.0 | EC000005 | ECLASS 14.0 | 27-40-02-01 |
| ECLASS 15.0 | 27-40-02-01 | | |

Drawings

