

## CRIMPFIX LZ

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

### General ordering data

Version	Automatic stripper and crimper
Order No.	<a href="#">9027310000</a>
Type	CRIMPFIX LZ
GTIN (EAN)	4032248285440
Qty.	1 items

## CRIMPFIX LZ

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS Conform

### Dimensions and weights

Depth	330 mm	Depth (inches)	12.9921 inch
Height	460 mm	Height (inches)	18.1102 inch
Width	390 mm	Width (inches)	15.3543 inch
Net weight	31000 g		

### Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c, 7a, 7cl
REACH SVHC	Lead 7439-92-1
SCIP	d2df479e-2b79-4e98-adc7-b03577df98ae

### PW65 maintenance - automatic stripping/crimping

Stripping range	2 x 0.5 - 2 x 1.5 mm <sup>2</sup> (~AWG 2x20 - 2x16)	Drive	Electropneumatic
Pulse time	approx. 1 s	Wire end ferrules cross-section, max.	1.5 mm <sup>2</sup>
Wire end ferrules cross-section, min.	0.5 mm <sup>2</sup>	Crimping length	8 mm
Consumables	Twin wire-end ferrules	Length of wire-end ferrule	14 mm
Compressed-air connection	5 - 5.5 bar	Electrical connection	100-240 V / 50/60 Hz / 110 VA

### Classifications

ETIM 8.0	EC002778	ETIM 9.0	EC002778
ETIM 10.0	EC002778	ECLASS 14.0	17-13-01-01
ECLASS 15.0	17-13-01-01		

Drawings

