


## H1,5/26D ZH SW

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code

### General ordering data

|            |  |
|------------|--|
| Version    | Wire-end ferrule, Twin wire-end ferrule, 21 mm, 18 mm, black |
| Order No.  | <a href="#">9037490000</a>                                   |
| Type       | H1,5/26D ZH SW   |
| GTIN (EAN) | 4008 190493066   |
| Qty.       | 100 items  |
| Packaging  | loose  |

## H1,5/26D ZH SW

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E499744

## Dimensions and weights

Net weight 0.26 g

## Environmental Product Compliance

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

## Technical data

| Description of article | Twin wire end ferrule, black | Version | Twin wire-end ferrule |
|------------------------|------------------------------|---------|-----------------------|
|------------------------|------------------------------|---------|-----------------------|

## Wire-end ferrules

|   |        |                             |                     |
|---|--------|-----------------------------|---------------------|
| Contact surface diameter (D1)           | 2.2 mm | Contact surface length (L2) | 18 mm               |
| Collar width (B)                        | 3.6 mm | Collar height (A)           | 6.5 mm              |
| Plastic collar thickness (S2)           | 0.3 mm | L1 in mm                    | 26.00 mm            |
| Wire connection cross section AWG, max. | AWG 16 | Metal sleeve thickness (S1) | 0.15 mm             |
| Stripping length                        | 21 mm  | Conductor cross-section     | 1.5 mm <sup>2</sup> |
| Colour code                             | DIN    |                             |                     |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000005    | ETIM 9.0    | EC000005    |
| ETIM 10.0   | EC000005    | ECLASS 14.0 | 27-40-02-01 |
| ECLASS 15.0 | 27-40-02-01 |             |             |

Drawing

