

STRIPPER 6

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

General ordering data

Version	Stripping and cutting tool
Order No.	9046240000
Type	STRIPPER 6
GTIN (EAN)	4032248298648
Qty.	1 items

STRIPPER 6

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	19 mm	Depth (inches)	0.748 inch
Height	87 mm	Height (inches)	3.4252 inch
Width	200 mm	Width (inches)	7.874 inch
Net weight	158.4 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

Technical data

Description of article	Stripping tool for wires up to 6 mm ² / with integrated cable cutter
------------------------	---------------------------------------------------------------------------------

Stripping tools

Cable type	Flexible and solid conductors with PVC insulation	Stripping range AWG, max.	10 AWG
Stripping range AWG, min.	28 AWG	Stripping length, max.	20 mm
Conductor cross-section, max.	6 mm ²	Conductor cross-section, min.	0.08 mm ²

Classifications

ETIM 8.0	EC002109	ETIM 9.0	EC002109
ETIM 10.0	EC002109	ECLASS 14.0	21-04-37-06
ECLASS 15.0	21-04-37-06		