



Insulated ring-cable connector made from PVC

- Commercially available designs
- Not soldered
- With conical entry funnel

### General ordering data

Version	cable lug, terminal end, Insulated cable connector, 1.5 mm <sup>2</sup> , 0.5 mm <sup>2</sup> - 1.5 mm <sup>2</sup>
Order No.	<a href="#">9200080000</a>
Type	LIR 1,5M3,5 V
GTIN (EAN)	4032248409846
Qty.	100 items

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	5.8 mm	Depth (inches)	0.2283 inch
Width	20.4 mm	Width (inches)	0.8031 inch
Net weight	0.4 g		

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Technical data

Description of article	Insulated ring-cable connector 1.5 mm <sup>2</sup> / M3.5
------------------------	---

### Connectors

Conductor cross-section, max.	1.5 mm <sup>2</sup>	Conductor cross-section, min.	0.5 mm <sup>2</sup>
Conductor cross-section	1.5 mm <sup>2</sup>	Insulation	PVC, Available
Dimension (bolt)	M 3.5	Dimension	M 3.5
Material/plastic	PVC	Identification colour	red
Connection density (S1)	0.75 mm	Connection length (l)	16.05 mm
Inside diameter (d1)	3.7 mm	Plastic collar length (b)	11.3 mm
Plastic collar diameter (D)	4 mm	Outside diameter (d)	5.5 mm

### Classifications

ETIM 8.0	EC001059	ETIM 9.0	EC001059
ETIM 10.0	EC001059	ECLASS 14.0	27-40-02-92
ECLASS 15.0	27-40-02-92		