

KT 55**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Cutting tools in mechanical ratchet version. Suitable for non-pinch cutting of copper and aluminium conductors. Easy operation thanks to optimum leverage and a cleverly engineered cam mechanism.

General ordering data

Version	Cutting tools, Circular cable cutter
Order No.	9202060000
Type	KT 55
GTIN (EAN)	4032248482191
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Available until	2024-10-28T00:00:00+01:00
Alternative product	KT 50

KT 55

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	45 mm	Depth (inches)	1.7716 inch
Height	115 mm	Height (inches)	4.5275 inch
Width	365 mm	Width (inches)	14.3701 inch
Net weight	1486.7 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

Technical data

Description of article	Front cable cutter up to 55 mm outer diameter	Version	One-hand mechanical
------------------------	---	---------	---------------------

Cutting tools




Copper sector cable	3 x 150 SM	Copper cable - flexible, max. (kcmil)	1000 kcmil
Copper cable - flexible, max.	500 mm ²	Copper cable - stranded, max. (kcmil)	1000 kcmil
Copper cable - stranded, max.	500 mm ²	Copper cable, max. diameter	55 mm
Data / telephone / control cable, max. Ø	55 mm	Aluminium sector cable	4 x 150 SE
Stranded aluminium cable, max. (kcmil)	1000 kcmil	Stranded aluminium cable, max (mm ²)	500 mm ²
Stranded aluminium cable, max. diameter	55 mm		

Classifications

ETIM 8.0	EC000142	ETIM 9.0	EC000142
ETIM 10.0	EC000142	ECLASS 14.0	21-04-47-01
ECLASS 15.0	21-04-47-01		

Drawings

Example of use

-  Cu + Al: max. 80 mm
-  Cu: max. 630 mm²
Al: max. 1000 mm²
-  Cu: max. 630 mm²



KT 55

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

KT 55



Cutting tools in mechanical ratchet version. Suitable for non-pinch cutting of copper and aluminium conductors. Easy operation thanks to optimum leverage and a cleverly engineered cam mechanism.

General ordering data

Type	ERME KT 55	Version
Order No.	9204280000	Replacement parts
GTIN (EAN)	4032248640997	
Qty.	1 ST	
Type	ERTE BAGR 11 KT 55	Version
Order No.	4316210000	Cutting tool, Replacement part
GTIN (EAN)	4032248788217	
Qty.	1 ST	
Type	ERTE BAGR 4 KT 55	Version
Order No.	4316130000	Cutting tool, Replacement part
GTIN (EAN)	4032248787944	
Qty.	1 ST	
Type	ERTE BAGR 5 KT 55	Version
Order No.	4316140000	Cutting tool, Replacement part
GTIN (EAN)	4032248787951	
Qty.	1 ST	
Type	ERTE BAGR 6 KT 55	Version
Order No.	4316150000	Cutting tool, Replacement part
GTIN (EAN)	4032248787968	
Qty.	1 ST	
Type	ERTE BAGR 7 KT 55	Version
Order No.	4316160000	Cutting tool, Replacement part
GTIN (EAN)	4032248787975	
Qty.	1 ST	
Type	ERTE BAGR 9 KT 55	Version
Order No.	4316180000	Cutting tool, Replacement part
GTIN (EAN)	4032248787999	
Qty.	1 ST	
Type	ERME KT 55	Version
Order No.	9204280000	Replacement parts
GTIN (EAN)	4032248640997	
Qty.	1 ST	
Type	ERTE BAGR 11 KT 55	Version
Order No.	4316210000	Cutting tool, Replacement part
GTIN (EAN)	4032248788217	
Qty.	1 ST	
Type	ERTE BAGR 4 KT 55	Version
Order No.	4316130000	Cutting tool, Replacement part
GTIN (EAN)	4032248787944	
Qty.	1 ST	

KT 55

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Type	ERTE BAGR 5 KT 55	Version
Order No.	4316140000	Cutting tool, Replacement part
GTIN (EAN)	4032248787951	
Qty.	1 ST	
Type	ERTE BAGR 6 KT 55	Version
Order No.	4316150000	Cutting tool, Replacement part
GTIN (EAN)	4032248787968	
Qty.	1 ST	
Type	ERTE BAGR 7 KT 55	Version
Order No.	4316160000	Cutting tool, Replacement part
GTIN (EAN)	4032248787975	
Qty.	1 ST	
Type	ERTE BAGR 9 KT 55	Version
Order No.	4316180000	Cutting tool, Replacement part
GTIN (EAN)	4032248787999	
Qty.	1 ST	