

**MULTI-STRIPAX 6-16****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



- For flexible and solid conductors with special insulating materials
- High-quality stripping for industrial applications (complies with aircraft industry requirements)
- Specially shaped blades enable stripping of special types of insulation and conductor configurations
- Stripping length adjustable via end stop
- Very versatile thanks to interchangeable stripping units
- Stripping results reproduced accurately over and over again
- No damage to the conductor
- A long-lasting, reliable tool thanks to its sturdy design
- Integrated cutting function

**General ordering data**

Version	Tools, Stripping and cutting tool
Order No.	<a href="#">9202210000</a>
Type	MULTI-STRIPAX 6-16
GTIN (EAN)	4032248486144
Qty.	1 items

## MULTI-STRIPAX 6-16

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	40 mm	Depth (inches)	1.5748 inch
Height	85 mm	Height (inches)	3.3464 inch
Width	250 mm	Width (inches)	9.8425 inch
Net weight	509.1 g		

## Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

## Technical data

Description of article	Stripping and cutting tool for 6, 10 and 16 mm <sup>2</sup> ; PVC-insulated conductors with special configurations
------------------------	--

## Stripping tools

Cable type	Flexible and solid conductors with PVC insulation	Conductor cross-section (cutting capacity)	6 mm <sup>2</sup>
max. cutting capacity, solid	2.5 mm <sup>2</sup>	max. cutting capacity, fine-strand	6 mm <sup>2</sup>
max. cutting capacity, ribbon	10,2 mm x 4 mm	Stripping range AWG, max.	6 AWG
Stripping range AWG, min.	10 AWG	Stripping length, min.	2 mm
Conductor cross-section, max.	16 mm <sup>2</sup>	Conductor cross-section, min.	6 mm <sup>2</sup>

## Classifications

ETIM 8.0	EC002109	ETIM 9.0	EC002109
ETIM 10.0	EC002109	ECLASS 14.0	21-04-37-06
ECLASS 15.0	21-04-37-06		