

CTI 6 G**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Crimping tools for insulated connectors
cable lugs, terminal pins, parallel and serial connectors,
plug-in connectors

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With stop for exact positioning of the contacts.
- Tested to DIN EN 60352 part 2

General ordering data

Version	Pressing tool, Tool for insulated cable connectors, 0.5mm ² , 6mm ² , Oval crimping, Parallel crimp
Order No.	9202850000
Type	CTI 6 G
GTIN (EAN)	4032248517855
Qty.	1 items

CTI 6 G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Width	250 mm	Width (inches)	9.8425 inch
Net weight	689.78 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

Technical data

Description of article	Crimping tool for insulated connectors, 0.5-6 mm ²	Version	Mechanical, without interchangeable inserts
------------------------	---	---------	---

Description of contact

Type of contact	Insulated connector	Conductor cross-section, max. AWG	AWG 10
Conductor cross-section, min. AWG	AWG 21	Crimping range, max.	6 mm ²
Crimping range, min.	0.5 mm ²		

tool data crimping

Wire end ferrules cross-section, max.	6 mm ²																																				
Crimping type/profile	Oval crimping, Parallel crimp																																				
Crimping station	<table border="1"> <tr> <td>Crimping station number</td> <td>1</td> </tr> <tr> <td>Conductor cross-section, min.</td> <td>0.5 mm²</td> </tr> <tr> <td>Conductor cross-section, max.</td> <td>1.5 mm²</td> </tr> <tr> <td>Conductor cross-section AWG, min.</td> <td>20 AWG</td> </tr> <tr> <td>Conductor cross-section AWG, max.</td> <td>16 AWG</td> </tr> <tr> <td>Colour of crimping station</td> <td>Red</td> </tr> <tr> <td>Crimping station number</td> <td>2</td> </tr> <tr> <td>Conductor cross-section, min.</td> <td>1.5 mm²</td> </tr> <tr> <td>Conductor cross-section, max.</td> <td>2.5 mm²</td> </tr> <tr> <td>Conductor cross-section AWG, min.</td> <td>16 AWG</td> </tr> <tr> <td>Conductor cross-section AWG, max.</td> <td>14 AWG</td> </tr> <tr> <td>Colour of crimping station</td> <td>Blue</td> </tr> <tr> <td>Crimping station number</td> <td>3</td> </tr> <tr> <td>Conductor cross-section, min.</td> <td>4 mm²</td> </tr> <tr> <td>Conductor cross-section, max.</td> <td>6 mm²</td> </tr> <tr> <td>Conductor cross-section AWG, min.</td> <td>12 AWG</td> </tr> <tr> <td>Conductor cross-section AWG, max.</td> <td>10 AWG</td> </tr> <tr> <td>Colour of crimping station</td> <td>Yellow</td> </tr> </table>	Crimping station number	1	Conductor cross-section, min.	0.5 mm ²	Conductor cross-section, max.	1.5 mm ²	Conductor cross-section AWG, min.	20 AWG	Conductor cross-section AWG, max.	16 AWG	Colour of crimping station	Red	Crimping station number	2	Conductor cross-section, min.	1.5 mm ²	Conductor cross-section, max.	2.5 mm ²	Conductor cross-section AWG, min.	16 AWG	Conductor cross-section AWG, max.	14 AWG	Colour of crimping station	Blue	Crimping station number	3	Conductor cross-section, min.	4 mm ²	Conductor cross-section, max.	6 mm ²	Conductor cross-section AWG, min.	12 AWG	Conductor cross-section AWG, max.	10 AWG	Colour of crimping station	Yellow
Crimping station number	1																																				
Conductor cross-section, min.	0.5 mm ²																																				
Conductor cross-section, max.	1.5 mm ²																																				
Conductor cross-section AWG, min.	20 AWG																																				
Conductor cross-section AWG, max.	16 AWG																																				
Colour of crimping station	Red																																				
Crimping station number	2																																				
Conductor cross-section, min.	1.5 mm ²																																				
Conductor cross-section, max.	2.5 mm ²																																				
Conductor cross-section AWG, min.	16 AWG																																				
Conductor cross-section AWG, max.	14 AWG																																				
Colour of crimping station	Blue																																				
Crimping station number	3																																				
Conductor cross-section, min.	4 mm ²																																				
Conductor cross-section, max.	6 mm ²																																				
Conductor cross-section AWG, min.	12 AWG																																				
Conductor cross-section AWG, max.	10 AWG																																				
Colour of crimping station	Yellow																																				


Important note

Product information	Not suitable for solid conductors. Insulation on the contact is pressed conically.
---------------------	--

Classifications

ETIM 8.0	EC000168	ETIM 9.0	EC000168
ETIM 10.0	EC000168	ECLASS 14.0	21-04-38-11
ECLASS 15.0	21-04-38-11		

Drawings



CTI 6 G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Accessories

www.weidmueller.com

Cable-lug connector



Insulated tab connector made from PVC with copper sleeve

- Commercially available designs
- Not soldered
- With conical entry funnel

General ordering data

Type	FSKI/0,5-1,0/288	Version
Order No.	1491790000	cable lug, terminal end, Insulated cable connector, 0,5 mm ² , 0,5 mm ² -
GTIN (EAN)	4050118301540	1 mm ² , red
Qty.	100 ST	
Type	FSKI/0,5-1,0/488	Version
Order No.	1491810000	cable lug, terminal end, Insulated cable connector, 0,5 mm ² , 0,5 mm ² -
GTIN (EAN)	4050118301380	1 mm ² , red
Qty.	100 ST	
Type	FSKI/0,5-1,0/638	Version
Order No.	1491820000	cable lug, terminal end, Insulated cable connector, 0,5 mm ² , 0,5 mm ² -
GTIN (EAN)	4050118301670	1 mm ² , red
Qty.	100 ST	
Type	FSKI/1,5-2,5/488	Version
Order No.	1491850000	cable lug, terminal end, Insulated cable connector, 2,5 mm ² , 1,5 mm ² -
GTIN (EAN)	4050118301687	2,5 mm ² , blue
Qty.	100 ST	
Type	FSKI/1,5-2,5/638	Version
Order No.	1491830000	cable lug, terminal end, Insulated cable connector, 2,5 mm ² , 1,5 mm ² -
GTIN (EAN)	4050118301830	2,5 mm ² , blue
Qty.	100 ST	
Type	FSKI/4,0-6,0/638	Version
Order No.	1491840000	cable lug, terminal end, Insulated cable connector, 6 mm ² , 4 mm ² - 6
GTIN (EAN)	4050118301823	mm ² , yellow
Qty.	100 ST	
Type	LIF 1,5M638 R	Version
Order No.	9200580000	cable lug, terminal end, Insulated cable connector, 0,5 mm ² - 1,5
GTIN (EAN)	4032248410422	mm ² , red
Qty.	100 ST	
Type	LIF 2,5M638 R	Version
Order No.	9200590000	cable lug, terminal end, Insulated cable connector, 1,5 mm ² - 2,5
GTIN (EAN)	4032248410439	mm ² , blue
Qty.	100 ST	
Type	LIF 6M638 R	Version
Order No.	9200600000	cable lug, terminal end, Insulated cable connector, 4 mm ² - 6
GTIN (EAN)	4032248410446	mm ² , yellow
Qty.	100 ST	

CTI 6 G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Accessories

www.weidmueller.com

Cable-lug sleeves



Insulated tab-connector sleeves made from PVC with copper sleeve

- Commercially available designs
- Not soldered
- With conical entry funnel

General ordering data

Type	LIF 1,5F288 R	Version
Order No.	9200520000	cable lug, terminal end,Insulated cable connector,1.5 mm ² ,0.5 mm ² -
GTIN (EAN)	4032248410361	1.5 mm ² ,red
Qty.	100 ST	
Type	LIF 1,5F488 R	Version
Order No.	9200530000	cable lug, terminal end,Insulated cable connector,1.5 mm ² ,0.5 mm ² -
GTIN (EAN)	4032248410378	1.5 mm ² ,red
Qty.	100 ST	
Type	LIF 1,5F638 R	Version
Order No.	9200540000	cable lug, terminal end,Insulated cable connector,1.5 mm ² ,0.5 mm ² -
GTIN (EAN)	4032248410385	1.5 mm ² ,red
Qty.	100 ST	
Type	LIF 2,5F488 R	Version
Order No.	9200550000	cable lug, terminal end,Insulated cable connector,1.5 mm ² ,1.5 mm ² -
GTIN (EAN)	4032248410392	2.5 mm ² ,blue
Qty.	100 ST	
Type	LIF 2,5F638 R	Version
Order No.	9200560000	cable lug, terminal end,Insulated cable connector,2.5 mm ² ,1.5 mm ² -
GTIN (EAN)	4032248410408	2.5 mm ² ,blue
Qty.	100 ST	
Type	LIF 6F638 R	Version
Order No.	9200570000	cable lug, terminal end,Insulated cable connector,6 mm ² ,4 mm ² - 6
GTIN (EAN)	4032248410415	mm ² ,yellow
Qty.	100 ST	
Type	VFSKHI/0,1-0,5/285	Version
Order No.	1491620000	cable lug, terminal end,Insulated cable connector,0.5 mm ² ,0.1 mm ² -
GTIN (EAN)	4050118301526	0.5 mm ² ,yellow
Qty.	100 ST	
Type	VFSKHI/0,1-0,5/288	Version
Order No.	1491630000	cable lug, terminal end,Insulated cable connector,0.5 mm ² ,0.1 mm ² -
GTIN (EAN)	4050118301489	0.5 mm ² ,yellow
Qty.	100 ST	
Type	VFSKHI/0,5-1,0/288	Version
Order No.	1491650000	cable lug, terminal end,Insulated cable connector,1 mm ² ,0.5 mm ² - 1
GTIN (EAN)	4050118301519	mm ² ,red
Qty.	100 ST	
Type	VFSKHI/0,5-1,0/485	Version
Order No.	1491660000	cable lug, terminal end,Insulated cable connector,1 mm ² ,0.5 mm ² - 1
GTIN (EAN)	4050118301410	mm ² ,red
Qty.	100 ST	

CTI 6 G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type	VFSKHI/0,5-1,0/488	Version
Order No.	1491670000	cable lug, terminal end, Insulated cable connector, 1 mm ² , 0.5 mm ² - 1
GTIN (EAN)	4050118301502	mm ² , red
Qty.	100 ST	
Type	VFSKHI/0,5-1,0/638	Version
Order No.	1491680000	cable lug, terminal end, Insulated cable connector, 1 mm ² , 0.5 mm ² - 1
GTIN (EAN)	4050118301618	mm ² , red
Qty.	100 ST	
Type	VFSKHI/0,5-1,0/285	Version
Order No.	1491640000	cable lug, terminal end, Insulated cable connector, 1 mm ² , 0.5 mm ² - 1
GTIN (EAN)	4050118301557	mm ² , red
Qty.	100 ST	
Type	VFSKHI/1,5-2,5/285	Version
Order No.	1491730000	cable lug, terminal end, Insulated cable connector, 2.5 mm ² , 1.5 mm ² -
GTIN (EAN)	4050118301700	2.5 mm ² , blue
Qty.	100 ST	
Type	VFSKHI/1,5-2,5/288	Version
Order No.	1491740000	cable lug, terminal end, Insulated cable connector, 2.5 mm ² , 1.5 mm ² -
GTIN (EAN)	4050118301472	2.5 mm ² , blue
Qty.	100 ST	
Type	VFSKHI/1,5-2,5/485	Version
Order No.	1491690000	cable lug, terminal end, Insulated cable connector, 2.5 mm ² , 1.5 mm ² -
GTIN (EAN)	4050118301717	2.5 mm ² , blue
Qty.	100 ST	
Type	VFSKHI/1,5-2,5/488	Version
Order No.	1491710000	cable lug, terminal end, Insulated cable connector, 2.5 mm ² , 1.5 mm ² -
GTIN (EAN)	4050118301663	2.5 mm ² , blue
Qty.	100 ST	
Type	VFSKHI/1,5-2,5/638	Version
Order No.	1491720000	cable lug, terminal end, Insulated cable connector, 2.5 mm ² , 1.5 mm ² -
GTIN (EAN)	4050118301564	2.5 mm ² , blue
Qty.	100 ST	
Type	VFSKHI/4,0-6,0/638	Version
Order No.	1491750000	cable lug, terminal end, Insulated cable connector, 6 mm ² , 4 mm ² - 6
GTIN (EAN)	4050118301816	mm ² , yellow
Qty.	100 ST	
Type	VFSKHI/4,0-6,0/9512	Version
Order No.	1491760000	cable lug, terminal end, Insulated cable connector, 6 mm ² , 4 mm ² - 6
GTIN (EAN)	4050118301588	mm ² , yellow
Qty.	100 ST	

Cable-lug sleeves with bifurcation



Insulated tab-connector sleeves with branch, made from PVC with copper sleeve

- Commercially available designs
- Not soldered
- With conical entry funnel

CTI 6 G

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

General ordering data

Type	LIF 1,5T638 R	Version
Order No.	9200610000	cable lug, terminal end,Insulated cable connector,0.5 mm ² - 1.5
GTIN (EAN)	4032248410453	mm ² ,red
Qty.	100 ST	
Type	LIF 2,5T638 R	Version
Order No.	9200620000	cable lug, terminal end,Insulated cable connector,1.5 mm ² - 2.5
GTIN (EAN)	4032248410460	mm ² ,blue
Qty.	100 ST	
Type	LIF 6T638 R	Version
Order No.	9200630000	cable lug, terminal end,Insulated cable connector,4 mm ² - 6
GTIN (EAN)	4032248410477	mm ² ,yellow
Qty.	100 ST	

Cable-lug sleeves, fully insulated



Fully-insulated tab-connector sleeves made from PVC with copper sleeve

- Commercially available designs
- Not soldered
- With conical entry funnel

General ordering data

Type	LIF 1,5F638 RF	Version
Order No.	9200640000	cable lug, terminal end,Insulated cable connector,0.5 mm ² - 1.5
GTIN (EAN)	4032248410484	mm ² ,red
Qty.	100 ST	
Type	LIF 2,5F638 RF	Version
Order No.	9200650000	cable lug, terminal end,Insulated cable connector,1.5 mm ² - 2.5
GTIN (EAN)	4032248410491	mm ² ,blue
Qty.	100 ST	
Type	LIF 6F638 RF	Version
Order No.	9200660000	cable lug, terminal end,Insulated cable connector,4 mm ² - 6
GTIN (EAN)	4032248410507	mm ² ,yellow
Qty.	100 ST	
Type	VFSKHV/0,5-1,0/285	Version
Order No.	1491860000	cable lug, terminal end,Insulated cable connector,1 mm ² ,0.5 mm ² - 1
GTIN (EAN)	4050118301915	mm ² ,red
Qty.	100 ST	
Type	VFSKHV/0,5-1,0/288	Version
Order No.	1491870000	cable lug, terminal end,Insulated cable connector,1 mm ² ,0.5 mm ² - 1
GTIN (EAN)	4050118301908	mm ² ,red
Qty.	100 ST	
Type	VFSKHV/0,5-1,0/485	Version
Order No.	1491880000	cable lug, terminal end,Insulated cable connector,1 mm ² ,0.5 mm ² - 1
GTIN (EAN)	4050118301748	mm ² ,red
Qty.	100 ST	

CTI 6 G

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Type	VFSKHV/0,5-1,0/488	Version
Order No.	1491890000	cable lug, terminal end, Insulated cable connector, 1 mm ² , 0.5 mm ² - 1
GTIN (EAN)	4050118301786	mm ² , red
Qty.	100 ST	
Type	VFSKHV/0,5-1,0/638	Version
Order No.	1491910000	cable lug, terminal end, Insulated cable connector, 1 mm ² , 0.5 mm ² - 1
GTIN (EAN)	4050118301847	mm ² , red
Qty.	100 ST	
Type	VFSKHV/1,5-2,5/485	Version
Order No.	1491920000	cable lug, terminal end, Insulated cable connector, 2.5 mm ² , 1.5 mm ² -
GTIN (EAN)	4050118301694	2.5 mm ² , blue
Qty.	100 ST	
Type	VFSKHV/1,5-2,5/488	Version
Order No.	1491930000	cable lug, terminal end, Insulated cable connector, 2.5 mm ² , 1.5 mm ² -
GTIN (EAN)	4050118301762	2.5 mm ² , blue
Qty.	100 ST	
Type	VFSKHV/1,5-2,5/638	Version
Order No.	1491940000	cable lug, terminal end, Insulated cable connector, 2.5 mm ² , 1.5 mm ² -
GTIN (EAN)	4050118301922	2.5 mm ² , blue
Qty.	100 ST	
Type	VFSKHV/4,0-6,0/638	Version
Order No.	1491950000	cable lug, terminal end, Insulated cable connector, 6 mm ² , 4 mm ² - 6
GTIN (EAN)	4050118301946	mm ² , yellow
Qty.	100 ST	

Crimp cable lugs



Insulated cable connector in PVC or PC/PA

- Conventional designs
- Not soldered
- With conical entry funnel, except for joint connector

General ordering data

Type	KQI-M10/-1	Version
Order No.	1492130000	cable lug, terminal end, Insulated cable connector, 1 mm ² , 0.5 mm ² - 1
GTIN (EAN)	4050118302158	mm ²
Qty.	100 ST	
Type	KQI-M10/-2,5	Version
Order No.	1492340000	cable lug, terminal end, Insulated cable connector, 2.5 mm ² , 1.5 mm ² -
GTIN (EAN)	4050118302295	2.5 mm ²
Qty.	100 ST	
Type	KQI-M10/-6	Version
Order No.	1492410000	cable lug, terminal end, Insulated cable connector, 6 mm ² , 4 mm ² - 6
GTIN (EAN)	4050118302363	mm ²
Qty.	100 ST	

CTI 6 G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type	KQI-M12/-2,5	Version
Order No.	1492350000	cable lug, terminal end,Insulated cable connector,2.5 mm ² ,1.5 mm ² -
GTIN (EAN)	4050118302059	2.5 mm ²
Qty.	100 ST	
Type	KQI-M12/-6	Version
Order No.	1492420000	cable lug, terminal end,Insulated cable connector,6 mm ² ,4 mm ² - 6
GTIN (EAN)	4050118302189	mm ²
Qty.	100 ST	
Type	KQI-M2,5/-1	Version
Order No.	1492150000	cable lug, terminal end,Insulated cable connector,1 mm ² ,0.5 mm ² - 1
GTIN (EAN)	4050118302028	mm ²
Qty.	100 ST	
Type	KQI-M2/-0,5	Version
Order No.	1492090000	cable lug, terminal end,Insulated cable connector,0.5 mm ² ,0.1 mm ² -
GTIN (EAN)	4050118301892	0.5 mm ²
Qty.	100 ST	
Type	KQI-M2/-1	Version
Order No.	1492140000	cable lug, terminal end,Insulated cable connector,1 mm ² ,0.5 mm ² - 1
GTIN (EAN)	4050118302127	mm ²
Qty.	100 ST	
Type	KQI-M3,5/-1	Version
Order No.	1492180000	cable lug, terminal end,Insulated cable connector,1 mm ² ,0.5 mm ² - 1
GTIN (EAN)	4050118302080	mm ²
Qty.	100 ST	
Type	KQI-M3,5/-2,5	Version
Order No.	1492270000	cable lug, terminal end,Insulated cable connector,2.5 mm ² ,1.5 mm ² -
GTIN (EAN)	4050118302134	2.5 mm ²
Qty.	100 ST	
Type	KQI-M3/-0,5	Version
Order No.	1492100000	cable lug, terminal end,Insulated cable connector,0.5 mm ² ,0.1 mm ² -
GTIN (EAN)	4050118302011	0.5 mm ²
Qty.	100 ST	
Type	KQI-M3/-1	Version
Order No.	1492170000	cable lug, terminal end,Insulated cable connector,1 mm ² ,0.5 mm ² - 1
GTIN (EAN)	4050118302035	mm ²
Qty.	100 ST	
Type	KQI-M3/-2,5	Version
Order No.	1492250000	cable lug, terminal end,Insulated cable connector,2.5 mm ² ,1.5 mm ² -
GTIN (EAN)	4050118302073	2.5 mm ²
Qty.	100 ST	
Type	KQI-M4/-0,5	Version
Order No.	1492110000	cable lug, terminal end,Insulated cable connector,0.5 mm ² ,0.1 mm ² -
GTIN (EAN)	4050118302103	0.5 mm ²
Qty.	100 ST	
Type	KQI-M4/-1	Version
Order No.	1492200000	cable lug, terminal end,Insulated cable connector,1 mm ² ,0.5 mm ² - 1
GTIN (EAN)	4050118302301	mm ²
Qty.	100 ST	
Type	KQI-M4/-2,5	Version
Order No.	1492290000	cable lug, terminal end,Insulated cable connector,2.5 mm ² ,1.5 mm ² -
GTIN (EAN)	4050118302172	2.5 mm ²
Qty.	100 ST	

CTI 6 G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type	KQI-M4/-6	Version
Order No.	1492370000	cable lug, terminal end,Insulated cable connector,6 mm ² ,4 mm ² - 6
GTIN (EAN)	4050118302264	mm ²
Qty.	100 ST	
Type	KQI-M4/S/-1	Version
Order No.	1492190000	cable lug, terminal end,Insulated cable connector,1 mm ² ,0.5 mm ² - 1
GTIN (EAN)	4050118302165	mm ²
Qty.	100 ST	
Type	KQI-M4/S/-2,5	Version
Order No.	1492280000	cable lug, terminal end,Insulated cable connector,2.5 mm ² ,1.5 mm ² -
GTIN (EAN)	4050118302141	2.5 mm ²
Qty.	100 ST	
Type	KQI-M5/-0,5	Version
Order No.	1492120000	cable lug, terminal end,Insulated cable connector,0.5 mm ² ,0.1 mm ² -
GTIN (EAN)	4050118302042	0.5 mm ²
Qty.	100 ST	
Type	KQI-M5/-1	Version
Order No.	1492220000	cable lug, terminal end,Insulated cable connector,1 mm ² ,0.5 mm ² - 1
GTIN (EAN)	4050118302110	mm ²
Qty.	100 ST	
Type	KQI-M5/-2,5	Version
Order No.	1492310000	cable lug, terminal end,Insulated cable connector,2.5 mm ² ,1.5 mm ² -
GTIN (EAN)	4050118302271	2.5 mm ²
Qty.	100 ST	
Type	KQI-M5/-6	Version
Order No.	1492380000	cable lug, terminal end,Insulated cable connector,6 mm ² ,4 mm ² - 6
GTIN (EAN)	4050118302219	mm ²
Qty.	100 ST	
Type	KQI-M5/S/-1	Version
Order No.	1492210000	cable lug, terminal end,Insulated cable connector,1 mm ² ,0.5 mm ² - 1
GTIN (EAN)	4050118302004	mm ²
Qty.	100 ST	
Type	KQI-M5/S/2,5	Version
Order No.	1492300000	cable lug, terminal end,Insulated cable connector,2.5 mm ² ,1.5 mm ² -
GTIN (EAN)	4050118302332	2.5 mm ²
Qty.	100 ST	
Type	KQI-M6/-1	Version
Order No.	1492230000	cable lug, terminal end,Insulated cable connector,1 mm ² ,0.5 mm ² - 1
GTIN (EAN)	4050118302400	mm ²
Qty.	100 ST	
Type	KQI-M6/-2,5	Version
Order No.	1492320000	cable lug, terminal end,Insulated cable connector,2.5 mm ² ,1.5 mm ² -
GTIN (EAN)	4050118302417	2.5 mm ²
Qty.	100 ST	
Type	KQI-M6/-6	Version
Order No.	1492390000	cable lug, terminal end,Insulated cable connector,6 mm ² ,4 mm ² - 6
GTIN (EAN)	4050118302509	mm ²
Qty.	100 ST	
Type	KQI-M8/-1	Version
Order No.	1492240000	cable lug, terminal end,Insulated cable connector,1 mm ² ,0.5 mm ² - 1
GTIN (EAN)	4050118302066	mm ²
Qty.	100 ST	

CTI 6 G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type	KQI-M8/-2,5	Version
Order No.	1492330000	cable lug, terminal end, Insulated cable connector, 2.5 mm ² , 1.5 mm ² -
GTIN (EAN)	4050118302325	2.5 mm ²
Qty.	100 ST	
Type	KQI-M8/-6	Version
Order No.	1492400000	cable lug, terminal end, Insulated cable connector, 6 mm ² , 4 mm ² - 6
GTIN (EAN)	4050118302257	mm ²
Qty.	100 ST	

Forked cable lugs



Insulated forked-cable connector made from PVC or PC/PA

- Conventional designs
- Not soldered
- With conical entry funnel

General ordering data

Type	KQIG-M10/-6	Version
Order No.	1491320000	cable lug, terminal end, Insulated cable connector, 6 mm ² , 4 mm ² - 6
GTIN (EAN)	4050118301199	mm ²
Qty.	100 ST	
Type	KQIG-M3,5/-1	Version
Order No.	1492530000	cable lug, terminal end, Insulated cable connector, 1 mm ² , 0.5 mm ² - 1
GTIN (EAN)	4050118302370	mm ²
Qty.	100 ST	
Type	KQIG-M3,5/-2,5	Version
Order No.	1492610000	cable lug, terminal end, Insulated cable connector, 2.5 mm ² , 1.5 mm ² -
GTIN (EAN)	4050118302097	2.5 mm ²
Qty.	100 ST	
Type	KQIG-M3/-1	Version
Order No.	1492520000	cable lug, terminal end, Insulated cable connector, 1 mm ² , 0.5 mm ² - 1
GTIN (EAN)	4050118302431	mm ²
Qty.	100 ST	
Type	KQIG-M3/-2,5	Version
Order No.	1492600000	cable lug, terminal end, Insulated cable connector, 2.5 mm ² , 1.5 mm ² -
GTIN (EAN)	4050118302202	2.5 mm ²
Qty.	100 ST	
Type	KQIG-M4/-1	Version
Order No.	1492550000	cable lug, terminal end, Insulated cable connector, 1 mm ² , 0.5 mm ² - 1
GTIN (EAN)	4050118302240	mm ²
Qty.	100 ST	
Type	KQIG-M4/-2,5	Version
Order No.	1492630000	cable lug, terminal end, Insulated cable connector, 2.5 mm ² , 1.5 mm ² -
GTIN (EAN)	4050118302424	2.5 mm ²
Qty.	100 ST	

CTI 6 G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type	KQIG-M4/-6	Version
Order No.	1491270000	cable lug, terminal end,Insulated cable connector,6 mm ² ,4 mm ² - 6
GTIN (EAN)	4050118301342	mm ²
Qty.	100 ST	
Type	KQIG-M4/S/-1	Version
Order No.	1492540000	cable lug, terminal end,Insulated cable connector,1 mm ² ,0.5 mm ² - 1
GTIN (EAN)	4050118302523	mm ²
Qty.	100 ST	
Type	KQIG-M4/S/-2,5	Version
Order No.	1492620000	cable lug, terminal end,Insulated cable connector,2.5 mm ² ,1.5 mm ² -
GTIN (EAN)	4050118302387	2.5 mm ²
Qty.	100 ST	
Type	KQIG-M5/-1	Version
Order No.	1492580000	cable lug, terminal end,Insulated cable connector,1 mm ² ,0.5 mm ² - 1
GTIN (EAN)	4050118301793	mm ²
Qty.	100 ST	
Type	KQIG-M5/-2,5	Version
Order No.	1492640000	cable lug, terminal end,Insulated cable connector,2.5 mm ² ,1.5 mm ² -
GTIN (EAN)	4050118302448	2.5 mm ²
Qty.	100 ST	
Type	KQIG-M5/-6	Version
Order No.	1491280000	cable lug, terminal end,Insulated cable connector,6 mm ² ,4 mm ² - 6
GTIN (EAN)	4050118301311	mm ²
Qty.	100 ST	
Type	KQIG-M6/-1	Version
Order No.	1492590000	cable lug, terminal end,Insulated cable connector,1 mm ² ,0.5 mm ² - 1
GTIN (EAN)	4050118302318	mm ²
Qty.	100 ST	
Type	KQIG-M6/-2,5	Version
Order No.	1491260000	cable lug, terminal end,Insulated cable connector,1.5 mm ² ,1.5 mm ² -
GTIN (EAN)	4050118301182	2.5 mm ²
Qty.	100 ST	
Type	KQIG-M6/-6	Version
Order No.	1491290000	cable lug, terminal end,Insulated cable connector,4 mm ² ,4 mm ² - 6
GTIN (EAN)	4050118301328	mm ²
Qty.	100 ST	
Type	KQIG-M8/-6	Version
Order No.	1491310000	cable lug, terminal end,Insulated cable connector,6 mm ² ,4 mm ² - 6
GTIN (EAN)	4050118301298	mm ²
Qty.	100 ST	
Type	LIS 1,5M3 V	Version
Order No.	9200290000	cable lug, terminal end,Insulated cable connector,0.5 mm ² - 1.5
GTIN (EAN)	4032248410118	mm ² ,red
Qty.	100 ST	
Type	LIS 1,5M3,5 V	Version
Order No.	9200300000	cable lug, terminal end,Insulated cable connector,0.5 mm ² - 1.5
GTIN (EAN)	4032248410125	mm ² ,red
Qty.	100 ST	
Type	LIS 1,5M4 V	Version
Order No.	9200310000	cable lug, terminal end,Insulated cable connector,0.5 mm ² - 1.5
GTIN (EAN)	4032248410132	mm ² ,red
Qty.	100 ST	

CTI 6 G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type	LIS 1,5M5 V	Version
Order No.	9200320000	cable lug, terminal end,Insulated cable connector,0,5 mm ² - 1,5
GTIN (EAN)	4032248410149	mm ² ,red
Qty.	100 ST	
Type	LIS 1,5M6 V	Version
Order No.	9200330000	cable lug, terminal end,Insulated cable connector,0,5 mm ² - 1,5
GTIN (EAN)	4032248410156	mm ² ,red
Qty.	100 ST	
Type	LIS 2,5M3 V	Version
Order No.	9200350000	cable lug, terminal end,Insulated cable connector,1,5 mm ² - 2,5
GTIN (EAN)	4032248410170	mm ² ,blue
Qty.	100 ST	
Type	LIS 2,5M3,5 V	Version
Order No.	9200360000	cable lug, terminal end,Insulated cable connector,1,5 mm ² - 2,5
GTIN (EAN)	4032248410187	mm ² ,blue
Qty.	100 ST	
Type	LIS 2,5M4 V	Version
Order No.	9200370000	cable lug, terminal end,Insulated cable connector,1,5 mm ² - 2,5
GTIN (EAN)	4032248410194	mm ² ,blue
Qty.	100 ST	
Type	LIS 2,5M5 V	Version
Order No.	9200380000	cable lug, terminal end,Insulated cable connector,1,5 mm ² - 2,5
GTIN (EAN)	4032248410224	mm ² ,blue
Qty.	100 ST	
Type	LIS 2,5M6 V	Version
Order No.	9200390000	cable lug, terminal end,Insulated cable connector,1,5 mm ² - 2,5
GTIN (EAN)	4032248410231	mm ² ,blue
Qty.	100 ST	
Type	LIS 6M10 V	Version
Order No.	9200450000	cable lug, terminal end,Insulated cable connector,4 mm ² - 6
GTIN (EAN)	4032248410293	mm ² ,yellow
Qty.	50 ST	
Type	LIS 6M4 V	Version
Order No.	9200410000	cable lug, terminal end,Insulated cable connector,4 mm ² - 6
GTIN (EAN)	4032248410255	mm ² ,yellow
Qty.	100 ST	
Type	LIS 6M5 V	Version
Order No.	9200420000	cable lug, terminal end,Insulated cable connector,4 mm ² - 6
GTIN (EAN)	4032248410262	mm ² ,yellow
Qty.	100 ST	
Type	LIS 6M6 V	Version
Order No.	9200430000	cable lug, terminal end,Insulated cable connector,4 mm ² - 6
GTIN (EAN)	4032248410279	mm ² ,yellow
Qty.	100 ST	
Type	LIS 6M8 V	Version
Order No.	9200440000	cable lug, terminal end,Insulated cable connector,4 mm ² - 6
GTIN (EAN)	4032248410286	mm ² ,yellow
Qty.	50 ST	


CTI 6 G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Accessories

www.weidmueller.com

Hook-type cable lugs



The use of insulated connectors guarantees users a permanent and consistent quality for their electrical connections. In addition, they bring advantages during installation.

General ordering data

Type	HBT 1,5 - 3,0 RT	Version
Order No.	1312440000	cable lug, terminal end, Insulated cable connector, 1,5 mm ² , 1,5 mm ² - 3 mm ² , red
GTIN (EAN)	4050118115055	
Qty.	100 ST	
Type	HBT 1,5 - 4,6 RT	Version
Order No.	1233340000	cable lug, terminal end, Insulated cable connector, 1,5 mm ² , 1,5 mm ² - 4,6 mm ² , red
GTIN (EAN)	4050118210972	
Qty.	100 ST	
Type	HBT 2,5 - 3,0 BL	Version
Order No.	1312450000	cable lug, terminal end, Insulated cable connector, 2,5 mm ² , 2,5 mm ² - 3 mm ² , blue
GTIN (EAN)	4050118115130	
Qty.	100 ST	
Type	HBT 2,5 - 4,6 BL	Version
Order No.	1233330000	cable lug, terminal end, Insulated cable connector, 2,5 mm ² , 2,5 mm ² - 4,6 mm ² , blue
GTIN (EAN)	4050118016901	
Qty.	100 ST	
Type	HBT 6,0 - 3,0 GE	Version
Order No.	1312470000	cable lug, terminal end, Insulated cable connector, 3 mm ² , 3 mm ² - 6 mm ² , yellow
GTIN (EAN)	4050118114980	
Qty.	100 ST	
Type	HBT 6,0 - 4,6 GE	Version
Order No.	1216230000	cable lug, terminal end, Insulated cable connector, 4,6 mm ² , 4,6 mm ² - 6 mm ² , yellow
GTIN (EAN)	4050118000337	
Qty.	100 ST	
Type	HOOKBLA 0,25-1,5 SW	Version
Order No.	9036290000	cable lug, terminal end, Insulated cable connector, 1,5 mm ² , 0,25 mm ² - 1,5 mm ² , 16,75 mm, black
GTIN (EAN)	4032248175925	
Qty.	100 ST	
Type	HOOKBLA 1,0-2,5 SW	Version
Order No.	9036300000	cable lug, terminal end, Insulated cable connector, 2,5 mm ² , 1 mm ² - 2,5 mm ² , 16,75 mm, black
GTIN (EAN)	4032248175932	
Qty.	100 ST	

CTI 6 G

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Joint connector




Fully-insulated joint connector made from PVC or PC/PA

- Conventional designs
- Not soldered

General ordering data

Type	LIB 1,5B25 VF	Version
Order No.	9200490000	cable lug, terminal end, Insulated cable connector, 0,5 mm ² - 1,5
GTIN (EAN)	4032248410330	mm ² , red
Qty.	100 ST	
Type	LIB 2,5B25 VF	Version
Order No.	9200500000	cable lug, terminal end, Insulated cable connector, 1,5 mm ² - 2,5
GTIN (EAN)	4032248410347	mm ² , blue
Qty.	100 ST	
Type	LIB 6B26 VF	Version
Order No.	9200510000	cable lug, terminal end, Insulated cable connector, 4 mm ² - 6
GTIN (EAN)	4032248410354	mm ² , yellow
Qty.	100 ST	
Type	VSTI/0,1-0,5	Version
Order No.	1491540000	cable lug, terminal end, Insulated cable connector, 0,5 mm ² , 0,1 mm ² -
GTIN (EAN)	4050118301649	0,5 mm ² , yellow
Qty.	100 ST	
Type	VSTI/0,5-1,0	Version
Order No.	1491550000	cable lug, terminal end, Insulated cable connector, 1 mm ² , 0,5 mm ² - 1
GTIN (EAN)	4050118301731	mm ² , red
Qty.	100 ST	
Type	VSTI/1,5-2,5	Version
Order No.	1491560000	cable lug, terminal end, Insulated cable connector, 2,5 mm ² , 1,5 mm ² -
GTIN (EAN)	4050118301656	2,5 mm ² , blue
Qty.	100 ST	
Type	VSTI/4,0-6,0	Version
Order No.	1491570000	cable lug, terminal end, Insulated cable connector, 6 mm ² , 4 mm ² - 6
GTIN (EAN)	4050118301809	mm ² , yellow
Qty.	100 ST	

Parallel connectors



Insulated cable connector in PVC or PC/PA

- Conventional designs
- Not soldered
- With conical entry funnel, except for joint connector

CTI 6 G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

General ordering data

Type	VPLI/0,1-0,5	Version
Order No.	1491450000	cable lug, terminal end, Insulated cable connector, 0.5 mm ² , 0.1 mm ² -
GTIN (EAN)	4050118301595	0.5 mm ² , yellow
Qty.	100 ST	
Type	VPLI/0,5-1,0	Version
Order No.	1491460000	cable lug, terminal end, Insulated cable connector, 1 mm ² , 0.5 mm ² - 1
GTIN (EAN)	4050118301366	mm ² , red
Qty.	100 ST	
Type	VPLI/1,5-2,5	Version
Order No.	1491470000	cable lug, terminal end, Insulated cable connector, 2.5 mm ² , 1.5 mm ² -
GTIN (EAN)	4050118301571	2.5 mm ² , blue
Qty.	100 ST	
Type	VPLI/4,0-6,0	Version
Order No.	1491480000	cable lug, terminal end, Insulated cable connector, 6 mm ² , 4 mm ² - 6
GTIN (EAN)	4050118301359	mm ² , yellow
Qty.	100 ST	

Pin cable lugs



Insulated pin-cable connector made from PVC or PC/PA

- Conventional designs
- Not soldered
- With conical entry funnel

General ordering data

Type	KSI/0,1-0,5	Version
Order No.	1491370000	cable lug, terminal end, Insulated cable connector, 0.5 mm ² , 0.1 mm ² -
GTIN (EAN)	4050118301625	0.5 mm ²
Qty.	100 ST	
Type	KSI/0,5-1,0	Version
Order No.	1491380000	cable lug, terminal end, Insulated cable connector, 1 mm ² , 0.5 mm ² - 1
GTIN (EAN)	4050118301441	mm ²
Qty.	100 ST	
Type	KSI/1,5-2,5	Version
Order No.	1491390000	cable lug, terminal end, Insulated cable connector, 2.5 mm ² , 1.5 mm ² -
GTIN (EAN)	4050118301458	2.5 mm ²
Qty.	100 ST	
Type	KSI/1,5-2,5	Version
Order No.	1491410000	cable lug, terminal end, Insulated cable connector, 2.5 mm ² , 1.5 mm ² -
GTIN (EAN)	4050118301632	2.5 mm ²
Qty.	100 ST	
Type	KSI/4,0-6,0	Version
Order No.	1491420000	cable lug, terminal end, Insulated cable connector, 6 mm ² , 4 mm ² - 6
GTIN (EAN)	4050118300994	mm ²
Qty.	100 ST	

CTI 6 G


Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type	LIP 1,5R12 V	Version
Order No.	9200460000	cable lug, terminal end, Insulated cable connector, 0,5 mm ² - 1,5 mm ² , red
GTIN (EAN)	4032248410309	
Qty.	100 ST	
Type	LIP 2,5R12 V	Version
Order No.	9200470000	cable lug, terminal end, Insulated cable connector, 1,5 mm ² - 2,5 mm ² , blue
GTIN (EAN)	4032248410316	
Qty.	100 ST	
Type	LIP 6R14 V	Version
Order No.	9200480000	cable lug, terminal end, Insulated cable connector, 4 mm ² - 6 mm ² , yellow
GTIN (EAN)	4032248410323	
Qty.	100 ST	

Plug-in distributor




Insulated cable connector in PVC or PC/PA

- Conventional designs
- Not soldered
- With conical entry funnel, except for joint connector

General ordering data

Type	VSTVI/0,5-1,0	Version
Order No.	1491770000	cable lug, terminal end, Insulated cable connector, 1 mm ² , 0,5 mm ² - 1 mm ² , red
GTIN (EAN)	4050118301465	
Qty.	100 ST	
Type	VSTVI/1,5-2,5	Version
Order No.	1491780000	cable lug, terminal end, Insulated cable connector, 2,5 mm ² , 1,5 mm ² - 2,5 mm ² , blue
GTIN (EAN)	4050118301373	
Qty.	100 ST	

Ring cable lugs



Insulated ring-cable connector made from PVC

- Commercially available designs
- Not soldered
- With conical entry funnel

General ordering data

Type	LIR 1,5M3 V	Version
Order No.	9200070000	cable lug, terminal end, Insulated cable connector, 1,5 mm ² , 0,5 mm ² - 1,5 mm ²
GTIN (EAN)	4032248409839	
Qty.	100 ST	

CTI 6 G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type	LIR 1,5M3,5 V	Version
Order No.	9200080000	cable lug, terminal end,Insulated cable connector,1,5 mm ² ,0,5 mm ² -
GTIN (EAN)	4032248409846	1,5 mm ²
Qty.	100 ST	
Type	LIR 1,5M4 V	Version
Order No.	9200090000	cable lug, terminal end,Insulated cable connector,1,5 mm ² ,0,5 mm ² -
GTIN (EAN)	4032248409853	1,5 mm ²
Qty.	100 ST	
Type	LIR 1,5M5 V	Version
Order No.	9200100000	cable lug, terminal end,Insulated cable connector,1,5 mm ² ,0,5 mm ² -
GTIN (EAN)	4032248409860	1,5 mm ²
Qty.	100 ST	
Type	LIR 1,5M6 V	Version
Order No.	9200110000	cable lug, terminal end,Insulated cable connector,1,5 mm ² ,0,5 mm ² -
GTIN (EAN)	4032248409730	1,5 mm ²
Qty.	100 ST	
Type	LIR 1,5M8 V	Version
Order No.	9200120000	cable lug, terminal end,Insulated cable connector,1,5 mm ² ,0,5 mm ² -
GTIN (EAN)	4032248409747	1,5 mm ²
Qty.	100 ST	
Type	LIR 2,5M10 V	Version
Order No.	9200210000	cable lug, terminal end,Insulated cable connector,2,5 mm ² ,1,5 mm ² -
GTIN (EAN)	4032248410033	2,5 mm ²
Qty.	100 ST	
Type	LIR 2,5M3 V	Version
Order No.	9200150000	cable lug, terminal end,Insulated cable connector,2,5 mm ² ,1,5 mm ² -
GTIN (EAN)	4032248409778	2,5 mm ²
Qty.	100 ST	
Type	LIR 2,5M3,5 V	Version
Order No.	9200160000	cable lug, terminal end,Insulated cable connector,2,5 mm ² ,1,5 mm ² -
GTIN (EAN)	4032248409785	2,5 mm ²
Qty.	100 ST	
Type	LIR 2,5M4 V	Version
Order No.	9200170000	cable lug, terminal end,Insulated cable connector,2,5 mm ² ,1,5 mm ² -
GTIN (EAN)	4032248409792	2,5 mm ²
Qty.	100 ST	
Type	LIR 2,5M5 V	Version
Order No.	9200180000	cable lug, terminal end,Insulated cable connector,2,5 mm ² ,1,5 mm ² -
GTIN (EAN)	4032248409808	2,5 mm ²
Qty.	100 ST	
Type	LIR 2,5M6 V	Version
Order No.	9200190000	cable lug, terminal end,Insulated cable connector,2,5 mm ² ,1,5 mm ² -
GTIN (EAN)	4032248410019	2,5 mm ²
Qty.	100 ST	
Type	LIR 2,5M8 V	Version
Order No.	9200200000	cable lug, terminal end,Insulated cable connector,2,5 mm ² ,1,5 mm ² -
GTIN (EAN)	4032248410026	2,5 mm ²
Qty.	100 ST	
Type	LIR 6M10 V	Version
Order No.	9200270000	cable lug, terminal end,Insulated cable connector,6 mm ² ,4 mm ² - 6
GTIN (EAN)	4032248410095	mm ²
Qty.	100 ST	

CTI 6 G


Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type	LIR 6M4 V	Version
Order No.	9200230000	cable lug, terminal end, Insulated cable connector, 6 mm ² , 4 mm ² - 6
GTIN (EAN)	4032248410057	mm ²
Qty.	100 ST	
Type	LIR 6M5 V	Version
Order No.	9200240000	cable lug, terminal end, Insulated cable connector, 6 mm ² , 4 mm ² - 6
GTIN (EAN)	4032248410064	mm ²
Qty.	100 ST	
Type	LIR 6M6 V	Version
Order No.	9200250000	cable lug, terminal end, Insulated cable connector, 6 mm ² , 4 mm ² - 6
GTIN (EAN)	4032248410071	mm ²
Qty.	100 ST	
Type	LIR 6M8 V	Version
Order No.	9200260000	cable lug, terminal end, Insulated cable connector, 6 mm ² , 4 mm ² - 6
GTIN (EAN)	4032248410088	mm ²
Qty.	100 ST	

Round plug



- Insulated circular plug made from PVC with copper sleeve
- Commercially available designs
 - Not soldered
 - With conical entry funnel

General ordering data

Type	LID 1,5M4 R	Version
Order No.	9200670000	cable lug, terminal end, Insulated cable connector, 0,5 mm ² - 1,5
GTIN (EAN)	4032248410514	mm ² , red
Qty.	100 ST	
Type	LID 2,5M5 R	Version
Order No.	9200680000	cable lug, terminal end, Insulated cable connector, 1,5 mm ² - 2,5
GTIN (EAN)	4032248410521	mm ² , blue
Qty.	100 ST	
Type	LID 6M5 R	Version
Order No.	9200690000	cable lug, terminal end, Insulated cable connector, 4 mm ² - 6
GTIN (EAN)	4032248410538	mm ² , yellow
Qty.	100 ST	
Type	VRSTI/0,5-1,0	Version
Order No.	1492040000	cable lug, terminal end, Insulated cable connector, 1 mm ² , 0,5 mm ² - 1
GTIN (EAN)	4050118301779	mm ² , red
Qty.	100 ST	
Type	VRSTI/1,5-2,5	Version
Order No.	1492050000	cable lug, terminal end, Insulated cable connector, 2,5 mm ² , 1,5 mm ² -
GTIN (EAN)	4050118301861	2,5 mm ² , blue
Qty.	100 ST	

CTI 6 G


Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type	VRSTI/4,0-6,0	Version
Order No.	1492060000	cable lug, terminal end, Insulated cable connector, 6 mm ² , 4 mm ² - 6
GTIN (EAN)	4050118301885	mm ² , yellow
Qty.	100 ST	

Round-plug sleeves



Fully-insulated round-plug sleeves made from PVC with copper sleeve

- Commercially available designs
- Not soldered
- With conical entry funnel

General ordering data

Type	LID 1,5F4 RF	Version
Order No.	9200700000	cable lug, terminal end, Insulated cable connector, 0,5 mm ² - 1,5
GTIN (EAN)	4032248410545	mm ² , red
Qty.	100 ST	
Type	LID 2,5F5 RF	Version
Order No.	9200710000	cable lug, terminal end, Insulated cable connector, 1,5 mm ² - 2,5
GTIN (EAN)	4032248410552	mm ² , blue
Qty.	100 ST	
Type	LID 6,0F5 RF	Version
Order No.	9200720000	cable lug, terminal end, Insulated cable connector, 4 mm ² - 6
GTIN (EAN)	4032248410569	mm ² , yellow
Qty.	100 ST	
Type	VRSHV/0,5-1,0	Version
Order No.	1491980000	cable lug, terminal end, Insulated cable connector, 1 mm ² , 0,5 mm ² - 1
GTIN (EAN)	4050118301939	mm ² , red
Qty.	100 ST	
Type	VRSHVI/1,5-2,5	Version
Order No.	1491990000	cable lug, terminal end, Insulated cable connector, 2,5 mm ² , 1,5 mm ² - 2,5 mm ² , blue
GTIN (EAN)	4050118301878	
Qty.	100 ST	
Type	VRSHVI/4,0-6,0	Version
Order No.	1492010000	cable lug, terminal end, Insulated cable connector, 6 mm ² , 4 mm ² - 6
GTIN (EAN)	4050118301960	mm ² , yellow
Qty.	100 ST	

CTI 6 G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Round-plug sleeves, fully insulated




Insulated cable connector in PVC or PC/PA

- Conventional designs
- Not soldered
- With conical entry funnel, except for joint connector

General ordering data

Type	VRSHVI/0,5-1,0	Version	
Order No.	1492020000	Version	cable lug, terminal end, Insulated cable connector, 1 mm ² , 0.5 mm ² - 1 mm ² , red
GTIN (EAN)	4050118301984		
Qty.	100 ST		
Type	VRSHVI/1,5-2,5	Version	
Order No.	1492030000	Version	cable lug, terminal end, Insulated cable connector, 2.5 mm ² , 1.5 mm ² - 2.5 mm ² , blue
GTIN (EAN)	4050118301854		
Qty.	100 ST		

Ring cable lugs



Insulated ring-cable connector made from PVC

- Commercially available designs
- Not soldered
- With conical entry funnel

General ordering data

Type	LIR 1,5M10 V	Version	
Order No.	2792000000	Version	cable lug, terminal end, Insulated cable connector, 1.5 mm ² , 0.5 mm ² - 1.5 mm ²
GTIN (EAN)	4064675073192		
Qty.	100 ST		

Accessorieswww.weidmueller.com**Replacement parts**

After stripping the insulation, a suitable contact or wire end ferrule can be crimped onto the end of the cable. Crimping forms a secure connection between conductor and contact and has largely replaced soldering. Crimping denotes the creation of a homogeneous, permanent connection between conductor and connecting element. The connection can be made only with high-quality precision tools. The result is a secure and reliable connection both in mechanical and electrical terms. Weidmüller offers a wide range of mechanical crimping tools. Integral ratchets with release mechanisms guarantee optimum crimping. Crimped connections made with Weidmüller tools comply with international standards and regulations.

General ordering data

Type	ERTE GRIFFE CTO	Version
Order No.	1121010000	Pressing tool, Replacement part
GTIN (EAN)	4032248902118	
Qty.	1 ST	