

LSP 4L**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The main function of the voltage tester is to establish if voltage is present. A 2-pole voltage tester is the only approved testing instrument that fulfils the requirements of work protection regulations.

- with LCD-Display
- acc. to VDE standard,
- high peak voltage strength
- the right tester for every application

General ordering data

Version	Testing tools, 2-pole voltage tester type 1153
Order No.	9205050000
Type	LSP 4L
GTIN (EAN)	4032248697311
Qty.	1 items
Delivery status	Discontinued
Available until	2024-02-21T00:00:00+01:00

LSP 4L

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS

Conform

Dimensions and weights

Depth	48 mm	Depth (inches)	1.8898 inch
Height	37 mm	Height (inches)	1.4567 inch
Width	231 mm	Width (inches)	9.0945 inch
Net weight	173.5 g		

Environmental Product Compliance

RoHS Compliance Status

Compliant

REACH SVHC

Lead 7439-92-1

Technical data

Description of article

Two-pole voltage and continuity tester for up to 690 V

Measuring and testing devices

Measuring range category	CAT III – 690V/CAT IV – 600V	Rated voltage, max.	690 V AC/DC
Rated voltage, min.	12 V AC/DC	AC voltage measuring range	12-690 V
DC voltage measuring range	690 V	Working temperature, max.	45 °C
Working temperature, min.	-15 °C	Frequency range, max.	500 Hz
Frequency range, min.	0 Hz	Display	digital
Protection degree	IP65	Continuity test	Yes
Peak voltage resistance	8 kV	Tested and approved according to	EN/IEC 61243-3 :2010-10 (VDE 0682 Part 401)

Classifications

ETIM 8.0	EC000494	ETIM 9.0	EC000494
ETIM 10.0	EC000494	ECLASS 14.0	27-20-03-08
ECLASS 15.0	27-20-03-08		